

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1212030001](#)
Status: **Active**
Overview: [mpm_connectors](#)
Description: mPm® DIN Valve Connector, Type B, ISO Terminal No Tails, Black, Nitrile Gasket

Documents:

[Drawing \(PDF\)](#) [Test Summary STR-1251 \(PDF\)](#)
[Product Specification PS-121201-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-121201-001 \(PDF\)](#)

General

Product Family Field Attachable / Accessories
Series [121203](#)
IP Rating IP67
Overview [mpm_connectors](#)
Product Name mPm®
Type Field Attachable Connector

Physical

Cable Diameter N/A
Coupling Type External Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polypropylene
Material - Contact N/A
Material - Coupling Nut N/A
Material - Plating Mating n/a
Orientation 90° Angle
Poles N/A
Temperature Range - Operating -25°C to +75°C
Wire Size AWG N/A

Electrical

Current - Maximum per Contact 16A
Voltage - Maximum 250V AC/DC

Material Info

Old Part Number C92200N0T

Reference - Drawing Numbers

Packaging Specification PK-121201-001
Product Specification PS-121201-001
Sales Drawing SD-121203-001
Test Summary STR-1251



image - Reference only

EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[121203Series](#)