

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1212070004](#)  
**Status:** **Active**  
**Overview:** [mpm\\_connectors](#)  
**Description:** mPm® DIN Valve Connector, Type A with circuit C4, 24V RED LED, 2 Pole, Terminal No Tails, Nitrile Gasket with IP67 Screw

**Documents:**

[Drawing \(PDF\)](#) [Test Summary STR-1251 \(PDF\)](#)  
[Product Specification PS-121201-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-121201-001 \(PDF\)](#)

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">121207</a>
IP Rating	IP67
Overview	<a href="#">mpm_connectors</a>
Product Name	mPm®
Type	Field Attachable Connector

**Physical**

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Orientation	90° Angle
Poles	2
Temperature Range - Operating	-25°C to +75°C
Wire Size AWG	N/A

**Electrical**

Current - Maximum per Contact	16A
Voltage - Maximum	250V AC/DC

**Material Info**

Old Part Number	S28200TC420R
-----------------	--------------

**Reference - Drawing Numbers**

Packaging Specification	PK-121201-001
Product Specification	PS-121201-001
Sales Drawing	SD-121207-001
Test Summary	STR-1251



*image - Reference only*

**EU RoHS**

**RoHS Compliant by Exemption**  
**REACH SVHC**  
**Contains SVHC: No**  
**Low-Halogen Status**  
**Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[121207Series](#)