

Bubblemat



- Comfortable standing surface – reduces fatigue
- Bubble surface stimulates blood circulation to feet
- Protects operators from cold concrete floors
- Ideal for use where operatives stand in static positions
- Standard mat (with safety bevelled edges) or middle and end sections for longer runs

Technical Specifications:

- Manufactured from a hard wearing rubber compound
- Product height: 14mm

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.6 x 0.9 (edged all round)	5	17.5 x 17.5 x 75	Boxed	1	42	Black	BF010001
0.9 x 1.2m (edged all round)	10	17.5 x 17.5 x 105	Boxed	1	30	Black	BF010002
0.6 x 0.9 (end piece)	5	17.5 x 17.5 x 75	Boxed	1	42	Black	BF010003
0.6 x 0.9 (middle)	5	17.5 x 17.5 x 75	Boxed	1	42	Black	BF010004

Material: Natural rubber
 Surface Finish: Bubble shaped
 Product Height: 18 mm nominal

Operating Temperature: - 20° - + 160°

Resistance to Chemicals: Resistant to water and most mild acids
 Environmental Resistance: Use predominantly in dry areas.
 UV Resistance: N/A

Typical Applications: Ideal for manufacturing production areas where employees are standing in static positions. Bubble surface constantly stimulates blood circulation to reduce fatigue.

Installation Method: Individual components that lock together to cover any desired length or individual mats complete with bevel edge all round

Cleaning method: Hose down or pressure wash using a mild detergent.

Product Performance: Fatigue: ●●●●
 Slip Resistance: ●●
 Wear: ●●●●
 Low ‡ High ● → ●●●●●

Flame Retardancy: N/A

Country of Origin: Sri Lanka

Other: Silicone is used in the production process of the mats and a residue will possibly be left on the product.

End of document