


Ty-Fast® Cable Ties



- MINIATURE
- HEAVY DUTY
- INTERMEDIATE
- EXTRA HEAVY DUTY
- STANDARD
- RELEASABLE TIES
- MOUNTING HEAD
- STRIPED TIES
- RESTRICTED BUNDLE
- IDENTIFICATION TIES
- MIL-SPEC TIES


Ty-Fast® Cable Ties are available in lengths from 4" to our exclusive 48" strap. Cable Ties will satisfy bundling requirements from 1/16" to 15" and loop tensile strengths from 18 to 175 pounds.

Cable Ties are stocked in materials and colors as listed. Contact your Ty-Fast® Distributor or Customer Service Representative for availability in special materials and colors.


Where applicable, Ty-Fast® Cable Ties are UL Recognized, Mil-Spec Approved and/or QPL Listed.

State-of-the-art robotic and raw material handling equipment assures product and material integrity throughout the manufacturing process. Overall quality is achieved through statistical analysis and quality driven operator objectives. Ty-Fast® has attained Mil-Spec I-45208 quality ratings from a number of equipment manufacturers.

Ty-Fast® products are sold through stocking T&B Distributors.



Ty-Rap®/Ty-Fast®





Thomas & Betts

Ty-Fast®

Cable Ties

Part Number Construction



Product Prefix

MP - Mounting Pad
ID - Identification
S# - Strapping Thickness
MC - Mounting Cradle
PM - Push Mounts
SM - Screw Mounts
N# - Plain-Edged Cable Clamps / Width
W# - Self-Aligning Cable Clamps / Dia.
UL -
GG - Gator Grip
FA - Flat Adhesive Clip
FS - Flat Screw Clip
FR - Flat Rubber Adhesive Clip
MS - Snap Mount
RA - Round Adhesive Clip
SR - Spiral Wrap
GS - Grommating
GR - Extruded Grommating
GRU - Extruded Grommating Uncut

Color Table

0 - Black (Weather Resistant)	7 - Purple
1 - Brown	8 - Gray
2 - Red	9 - Natural
3 - Orange	11 - Fluorescent Pink
4 - Yellow	16 - Fluorescent Orange
5 - Green	17 - Fluorescent Yellow
6 - Blue	18 - Fluorescent Green
	20 - Fluorescent Blue



Ty-Rap®/Ty-Fast®