

M30 Connectors

Female Crimp Housings and Contacts


- ❖ Single or double row options.
- ❖ Loose or reeled contacts.
- ❖ Suitable for use with male connectors shown on pages 88 to 89.
- ❖ Pre-crimped contacts or cable assembly service, contact technical@harwin.com.

1.25mm (.049") PITCH

SINGLE ROW

CALCULATION


A	$B + 2.9$
B	$1.25 \times (\text{No. of ways per row} - 1)$




DOUBLE ROW

CALCULATION

A	$B + 4.0$
B	$1.25 \times (\text{No. of ways per row} - 1)$



CONTACTS



TYPE	AWG	ORDER CODE
Reeled	26 - 30	M30-10000XX
Loose	26 - 30	M30-10100XX

- ❖ Order codes for reeled contacts refer to one reel of 20,000 contacts.
- ❖ Order codes for loose contacts refer to one strip of 100 contacts.


TOOLS

Hand Crimp Tool - Z30-020

See page 90

- ❖ Instruction sheets available at www.harwin.com/downloads/instructions

WIRE STRIPPING DETAILS



HOW TO ORDER

M30 - 1 XX XX XX

SERIES CODE

TYPE	
00	Reeled contact
01	Loose contact
10	Single Row Housing
20	Double Row Housing

NO. OF WAYS PER ROW

02 to 15	Single Row Housing
10, 15, 20, 21	Double Row Housing
00	Contacts

FINISH

00	Housings	
46	Tin (Contacts)	

www.harwin.com

All dimensions in mm.



HARWIN