

TECHNICAL DATA SHEET

C5351/12

Digital Day/Night Short Bodied Camera, DC 12V



KEY FEATURES

- 1/3" Sony Super HAD CCD
- Super High Resolution, 540 TVL
- Digital Noise Reduction (DNR)
- Save Up To 70% HDD Storage Using MPEG Format with DNR
- Digital Day/Night
- Maximum 128x Sens-Up
- On Screen Display (O.S.D.)
- Selectable Electronic Shutter Control
- Selectable White Balance
- Selectable Back Light Compensation
- Selectable Gain Control
- Privacy Masking
- Motion Detection
- Mirror Function
- DC 12V

TECHNICAL DATA SHEET

TECHNICAL SPECIFICATION

Model Number	C5351/12
Image Sensor	Sony 1/3
Horizontal Resolution	540 TVL (Colour) 570 TVL (Mono)
Sensitivity (F1.2)	0.3 Lux (Colour) 0.1 Lux (Mono) 0.002 Lux (Sens-Up)
Scanning System	2:1 Interlace
Effective Pixels (H x V)	752 x 582 (440K Pixels)
Video Format	PAL
Synchronisation	INT/LL Selectable
Frequency	Horizontal: 15.625 KHz Vertical; 50.00Hz
Shutter Speed	Auto / Manual 1/50 ~ 1/120,000 Seconds
Video Output	1.0Vp-p / 75 Ohm
IR Cut Filter	No
Gain Control	OFF / LOW / MIDDLE / HIGH
Back Light Compensation	ON / OFF
White Balance	ATW / AWC / MANUAL / (1800° K~10500° K)
S/N Ratio	>50dB (AGC Off)
Sens-Up	OFF / AUTO
O.S.D.	Yes Built-In
Motion Detection	ON / OFF (4 Programmable Zones)
DNR	OFF / LOW / MIDDLE / HIGH
Mirror	Built-In (Horizontal Image Inversion)
Privacy Function	ON / OFF (4 Programmable Zones)
Colour	AUTO
Sharpness	Adjustable 0 ~ 31
Iris Control	DC / VIDEO
Lens Mount	CS Mount (C Mount Is Mountable By Using Adaptor)
Power Consumption	160mA
Power Supply	DC 12V
Operating Conditions	Temperature: -10°C ~ +50°C, Humidity: 30% ~ 80% RH
Dimensions (W x H x D)	69 x 69 x 60 mm
Weight	410g

Features and specification are subject to change for further improvement without any notice.