



**SPECIFICATIONS:**

- Material Thickness: .003" (.0762mm) nominal, +/- 10%
- Surface Resistance:
  - Outer Layer: <10E11 ohms per ANSI/ESD S11.11
  - Inner Layer: <10E11 ohms per ANSI/ESD S11.11
- Static Shielding: < 50 nJ per ANSI/ESD S11.31
- Light Transmission: >40% per ASTM 1003

**PACKAGING:**

- Bags are packed in Multicomp packaging


Item #	Multicomp #	Size (W x L)	Approval
CMG-10833	MC35821	2" x 3"	
CMG-10834	MC35822	3" x 5"	
CMG-10835	MC35823	4" x 6"	
CMG-10836	MC35824	5" x 8"	
CMG-10837	MC35825	6" x 8"	
CMG-10838	MC35826	6" x 10"	
CMG-10839	MC35827	8" x 10"	
CMG-10840	MC35828	8" x 12"	
CMG-10841	MC35829	10" x 12"	
CMG-10842	MC35830	10" x 14"	
CMG-10919	MC36360	11" x 15"	
CMG-10921	MC36361	12" x 16"	
CMG-10923	MC36364	12" x 18"	
CMG-10925	MC36365	18" x 18"	

See Page 2 for additional bag sizes

Multicomp packaging label

**RoHS Compliance Statement**

None of the following materials are intentionally added in manufacturing this product: lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB) or polybrominated diphenyl ethers (PBDE) as outlined in the Directive 2002/95/EC Article 4.1



Side Seam is 3/8" (+/- .10")  
 Tolerance L: +/- 0.250" / Tolerance W: +/- 0.250"  
 Special manufactured items are not returnable for credit

**BAGS, ESD SHIELDING, METAL IN, TRANSPARENT, PACKAGED IN MULTICOMP PACKAGING**

3651 WALNUT AVE., CHINO, CA 91710  
 PHONE (909) 627-9634 FAX (909) 363-7322  
 WEBSITE: www.CMG-Sales.com

**DRAWING NUMBER**  
 CMG-10833

**DATE**  
 April 2011

**CMG**



Item #	Multicomp #	Size (W x L)	Approval
CMG-10965	MC36463	3" x 4"	
CMG-10966	MC36464	3" x 7"	
CMG-10967	MC36465	4" x 4"	
CMG-10968	MC36466	4" x 8"	
CMG-10969	MC36467	4" x 9"	
CMG-10970	MC36468	4" x 24"	
CMG-10971	MC36469	4" x 25"	
CMG-10972	MC36470	5" x 7"	
CMG-10973	MC36471	5" x 10"	
CMG-10974	MC36472	6" x 6"	
CMG-10975	MC36473	6" x 9"	
CMG-10976	MC36474	6" x 12"	
CMG-10977	MC36475	6" x 14"	
CMG-10978	MC36476	6" x 18"	
CMG-10979	MC36477	7" x 15"	
CMG-10980	MC36478	8" x 8"	
CMG-10981	MC36479	8" x 14"	
CMG-10982	MC36480	8" x 16"	
CMG-10983	MC36481	8" x 18"	
CMG-10984	MC36482	8" x 24"	
CMG-10985	MC36483	10" x 16"	
CMG-10986	MC36484	10" x 18"	
CMG-10987	MC36485	10" x 24"	
CMG-10988	MC36486	10" x 30"	
CMG-10989	MC36487	12" x 25"	
CMG-10990	MC36488	14" x 18"	
CMG-10991	MC36489	15" x 18"	
CMG-10992	MC36490	15" x 19"	
CMG-10993	MC36491	16" x 18"	
CMG-10994	MC36492	16" x 20"	
CMG-10995	MC36493	16" x 24"	
CMG-10996	MC36494	18" x 24"	
CMG-10997	MC36495	22" x 23"	
CMG-10998	MC36496	22" x 25"	
CMG-10999	MC36497	22" x 28"	
CMG-11000	MC36498	24" x 30"	
CMG-11001	MC36499	30" x 30"	

Special manufactured items are not returnable for credit

RoHS Compliance Statement  
None of the following materials are intentionally added in manufacturing this product: lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB) or polybrominated diphenyl ethers (PBDE) as outlined in the Directive 2002/95/EC Article 4.1



MADE IN AMERICA

# CMG

3651 WALNUT AVE., CHINO, CA 91710  
PHONE (909) 627-9634 FAX (909) 363-7322  
WEBSITE: www.CMG-Sales.com

**DRAWING NUMBER**  
CMG-10833

**DATE**  
April 2011