


Crimp Contacts

CB/CT MIL-DTL-5015 MS-E/FR VG 95 234 CA-Bayonet


CB Series

Contact Size		CB Crimp Pins			CB Crimp Sockets			
CONTACT SIZE	WIRE GAUGE (AWG)	PART NUMBER			PART NUMBER		WIRE STRIP LENGTHS	
		SILVER	GOLD		SILVER	GOLD		
16S	16-18♣	CB16S-16P♣	CB16S-16PG♣		CB16S-16S♣	CB16S-16SG♣	.245 (6.2)	
	20-22	CB16S-20P	CB16S-20PG	G5	CB16S-20S	CB16S-20SG		G5
	22-26	CB16S-22P	CB16S-22PG	G6	CB16S-22S	CB16S-22SG		G6
16	12-14	CB16-12P	CB16-12PG	G13	CB16-12S	CB16-12SG	G13	
	14-16	CB16-14P	CB16-14PG	G12	CB16-14S	CB16-14SG	G12	
	16-18♣	CB16-16P♣	CB16-16PG♣		CB16-16S♣	CB16-16SG♣		
	20-22	CB16-20P	CB16-20PG	G9	CB16-20S	CB16-20SG	G9	
	22-26	CB16-22P	CB16-22PG	G10	CB16-22S	CB16-22SG	G10	
12	12-14♣	CB12-12P♣	CB12-12PG♣		CB12-12S♣	CB12-12SG♣	.245 (6.2)	
	16-18	CB12-16P	CB12-16PG	G16	CB12-16S	CB12-16SG		G16
8	8-10♣	CB8-8P♣	-		CB8-8S♣	-	.465 (11.8)	
	10	CB8-10P	-	G42	CB8-10S	-		G42
	12-14	CB8-12P	-	G40	CB8-12S	-		G40
4	4♣	CB4-4P♣	-		CB4-4S♣	-	.465 (11.8)	
	6	CB4-6P	-	G44	CB4-6S	-		G44
0	0♣	CB0-0P♣	-		CB0-0S♣	-	.540 (13.7)	
	2	CB0-2P	-	G48	CB0-2S	-		G48
	4	CB0-4P	-	G47	CB0-4S	-		G47

Part Numbers marked with ♣ are the standard for that contact size

CT Series

CONTACT SIZE	WIRE GAUGE (AWG)	PART NUMBER		PART NUMBER		WIRE STRIP LENGTHS
		SILVER	GOLD	SILVER	GOLD	
16S	16-18	CT16S-16P	CT16S-16PG	CT16S-16S	CT16S-16SG	.250 (6.4)
16	16-20	CT16-16P	CT16-16PG	CT16-16S	CT16-16SG	.250 (6.4)
12	12-14	CT12-12P	CT12-12PG	CT12-12S	CT12-12SG	.250 (6.4)
8	8-10	CT8-8P	-	CT8-8S	CT8-8SG	.438 (11.1)
4	4	CT4-4P	-	CT4-4S	-	.625 (15.9)
0	0	CT0-0P	-	CT0-0S	-	.688 (17.5)



Crimp Contacts

CB Series

Wire Range		Accessories		Tools						
INSULATION O.D. MIN	INSULATION O.D. MAX	WIRE HOLE FILLERS	HOLE FILLER COLOR	HAND CRIMP TOOL	HAND TOOL TURRET	USE LOCATOR COLOR	POWER CRIMP TOOL	POWER CRIMP LOCATOR	INSERTION/EXTRACTION TOOL	INSERTION GUIDE PINS
.089 (2.2)	.110 (2.8)	225-0017-000	BLUE	AF8	TH452	BLUE△/GREEN◆	WA27F		Use hand tool turret with power tool.	226-1017-000
.089 (2.2)	.110 (2.8)	225-0017-000	BLUE	AF8	TH452	BLUE△/GREEN◆	WA27F	226-1017-000		
.089 (2.2)	.110 (2.8)	225-0017-000	BLUE	AF8	TH452	BLUE△/GREEN◆	WA27F	226-1017-000		
.089 (2.2)	.110 (2.8)	225-0017-000	BLUE	AF8	TH452	GREEN△/RED◆	WA27F	CIT-F80-16*		226-1017-000
.089 (2.2)	.110 (2.8)	225-0017-000	BLUE	AF8	TH452	GREEN△/RED◆	WA27F	CET-F80-16†		226-1017-000
.089 (2.2)	.110 (2.8)	225-0017-000	BLUE	AF8	TH452	GREEN△/RED◆	WA27F			226-1017-000
.089 (2.2)	.110 (2.8)	225-0017-000	BLUE	AF8	TH452	GREEN△/RED◆	WA27F			226-1017-000
.089 (2.2)	.110 (2.8)	225-0017-000	BLUE	AF8	TH452	GREEN△/RED◆	WA27F			226-1017-000
.122 (3.1)	.138 (3.5)	225-0018-000	YELLOW	AF8	TH452	RED	WA27F		CIT-F80-12*	226-1018-000
.122 (3.1)	.138 (3.5)	225-0018-000	YELLOW	AF8	TH452	RED	WA27F		CET-F80-12†	226-1018-000
.220 (5.6)	.256 (6.5)	MS27488-8-3	RED	N/A	N/A	N/A	400BHD	CCH8-KIT	CIT-8*	N/A
.220 (5.6)	.256 (6.5)	MS27488-8-3	RED	N/A	N/A	N/A	400BHD	CCH8-KIT	CET-8†	N/A
.220 (5.6)	.256 (6.5)	MS27488-8-3	RED	N/A	N/A	N/A	400BHD	CCH8-KIT		N/A
.335 (8.5)	.370 (9.4)	MS27488-4-3	BLUE	N/A	N/A	N/A	400BHD	CCH4-KIT	CIT-4*	N/A
.335 (8.5)	.370 (9.4)	MS27488-4-3	BLUE	N/A	N/A	N/A	400BHD	CCH4-KIT	CET-4†	N/A
.452 (11.5)	.512 (13.0)	MS27488-0-3	YELLOW	N/A	N/A	N/A	400BHD	CCH0-KIT	CIT-0*	N/A
.452 (11.5)	.512 (13.0)	MS27488-0-3	YELLOW	N/A	N/A	N/A	400BHD	CCH0-KIT	CET-0†	N/A
.452 (11.5)	.512 (13.0)	MS27488-0-3	YELLOW	N/A	N/A	N/A	400BHD	CCH0-KIT		N/A

*Insertion Tool †Extraction Tool △ Pin ◆ Socket

CT Series

INSULATION O.D. MIN	INSULATION O.D. MAX	WIRE HOLE FILLERS	HOLE FILLER COLOR	HAND CRIMP TOOL	HAND TOOL TURRET	USE LOCATOR COLOR	POWER CRIMP TOOL	POWER CRIMP LOCATOR	INSERTION/EXTRACTION TOOL	INSERTION GUIDE PINS
.064 (1.6)	.130 (3.3)	225-0017-000	BLUE	AF8	TH70-1	BLUE△/RED◆	WA27F	Use hand tool turret with power tool.	CIT-F80-16*	226-1017-000
.064 (1.6)	.130 (3.3)	225-0017-000	BLUE	AF8	TH70-1	RED△/GREEN◆	WA27F		CET-F80-16†	226-1017-000
.114 (2.9)	.170 (4.3)	225-0018-000	YELLOW	AF8	TP567	-	WA27F		CIT-F80-12*/CET-F80-12†	226-1018-000
.164 (4.2)	.255 (6.5)	MS27488-8-3	RED	N/A	N/A	N/A	400BHD	CCH8-KIT	CIT-8*/CET-8†	N/A
.272 (6.9)	.370 (9.4)	MS27488-4-3	BLUE	N/A	N/A	N/A	400BHD	CCH4-KIT	CIT-4*/CET-4†	N/A
.415 (10.5)	.550 (14.0)	MS27488-0-3	YELLOW	N/A	N/A	N/A	400BHD	CCH0-KIT	CIT-0*/CET-0†	N/A

*Insertion Tool †Extraction Tool



Crimp kits are available for 16S & 16 size contacts - CAB16KIT. (Call for CT16KIT)

- Kit includes:
- Crimp Tool
 - Locator
 - Insertion Tool
 - Insertion Guide Pins
 - Extraction Tool
 - Contact Insertion Lubricant
 - Assembly Instructions
 - Rugged Case