

## Twist-Lock® Devices

# 30 Ampere, 3Ø Y 120/208, 277/480 and 347/600 Volts AC

4 Pole, 5 Wire Grounding

## Insulgrip® Plugs and Flanged Inlets




**30A 3ØY  
120/208V AC  
NEMA L21-30P  
UL/CSA  
3 HP**



**30A 3ØY  
277/480V AC  
NEMA L22-30P  
UL/CSA  
10 HP**



**30A 3ØY  
347/600V AC  
NEMA L23-30P  
UL/CSA**



**HBL2811SW**




**HBL2811S**



**HBL2811**



**HBL2815SW**



**HBL2815**

## Plugs

### Watertight Safety-Shroud®

**IP66 SUITABILITY**

Description	Cord Dia.	Catalog Numbers	
Black Valox® housing, white Valox® clamps.	.35"-1.15" (9-29)	<b>HBL2811SW</b>	-

### Safety-Shroud

**IP20 SUITABILITY**

Description	Cord Dia.	Catalog Numbers	
Black and white nylon body, white Valox® shroud. Can be used with the Insulgrip Connector Bodies.	.35"-1.15" (9-29)	<b>HBL2811S</b>	-

Accessories on page B-40.

### Insulgrip

**IP20 SUITABILITY**

Description	Cord Dia.	Catalog Numbers		
Black and white nylon.	.35"-1.15" (9-29)	<b>HBL2811</b>	<b>HBL2821</b>	<b>HBL2831</b>
Corrosion resistant, yellow nylon.	.35"-1.15" (9-29)	<b>HBL28CM11</b>	-	-
Black and white for flat cable.	.35"-1.15" (9-29)	<b>HBL2811FC</b>	-	-
All black nylon.	.35"-1.15" (9-29)	<b>HBL2811BK</b>	-	-

Accessories on page B-53.

## Flanged Inlets

### Watertight Safety-Shroud

**IP66 SUITABILITY**

Description	Catalog Numbers	
Gray Valox® housing and flange.	<b>HBL2815SW</b>	-

Accessories on page B-54.

### Insulgrip

**IP20 SUITABILITY**

Description	Catalog Numbers		
Nylon casing, back wired.	<b>HBL2815</b>	<b>HBL2825</b>	<b>HBL2835</b>

Accessories on page B-52.

Notes: For technical information on Twist-Lock® and Watertight Safety-Shroud Devices see pages B-69 and 70.



**HBLMITL** - For use with Watertight Safety-Shroud receptacles, see page B-39.

Valox® is a trademark of SABIC Innovative Plastics, acquired from General Electric Company.