

High-Density Connections



Item #	Description	1-9	10-24	25-99	100-249	250-499
<b>✓RoHS Deluxe High-Density 15 Pin D-Sub Cables - Fully Populated and Completely Shielded</b>						
High-density D-Sub connectors are used in a number of PC and network applications. This type of connector can usually be recognized because they have three rows of smaller pins versus the larger pins used in conventional D-Subs. Fully populated with stranded conductors and aluminum mylar shielding. Hex nuts on female connectors are removable to expose 4-40 thumbscrews.						
<a href="#">CHD15MM-2.5</a>	Deluxe Molded Cable, HD15 Male / Male, 2.5 ft	10.90	10.25	9.59	8.94	8.28
<a href="#">CHD15MM-5</a>	Deluxe Molded Cable, HD15 Male / Male, 5.0 ft	11.75	11.04	10.34	9.64	8.93
<a href="#">CHD15MM-7.5</a>	Deluxe Molded Cable, HD15 Male / Male, 7.5 ft	12.65	11.89	11.13	10.37	9.61
<a href="#">CHD15MM-10</a>	Deluxe Molded Cable, HD15 Male / Male, 10.0 ft	13.50	12.69	11.88	11.07	10.26
<a href="#">CHD15MM-15</a>	Deluxe Molded Cable, HD15 Male / Male, 15.0 ft	15.25	14.33	13.42	12.51	11.59
<a href="#">CHD15MM-25</a>	Deluxe Molded Cable, HD15 Male / Male, 25.0 ft	17.00	15.98	14.96	13.94	12.92
<a href="#">CHD15MF-2.5</a>	Deluxe Molded Cable, HD15 Male / Female, 2.5 ft	10.90	10.25	9.59	8.94	8.28
<a href="#">CHD15MF-5</a>	Deluxe Molded Cable, HD15 Male / Female, 5.0 ft	11.75	11.04	10.34	9.64	8.93
<a href="#">CHD15MF-7.5</a>	Deluxe Molded Cable, HD15 Male / Female, 7.5 ft	12.65	11.89	11.13	10.37	9.61
<a href="#">CHD15MF-10</a>	Deluxe Molded Cable, HD15 Male / Female, 10.0 ft	13.50	12.69	11.88	11.07	10.26
<a href="#">CHD15MF-15</a>	Deluxe Molded Cable, HD15 Male / Female, 15.0 ft	15.25	14.33	13.42	12.51	11.59
<a href="#">CHD15MF-25</a>	Deluxe Molded Cable, HD15 Male / Female, 25.0 ft	17.00	15.98	14.96	13.94	12.92

Note: Most monitor manufacturers recommend using premium grade VGA cables that utilize 75 Ohm coaxial lines.

<b>✓RoHS Deluxe High-Density 26 Pin Molded Cables - Ready Made, Fully Populated for Many Applications</b>						
Fully molded data cables equipped with high-density D-Sub connectors. Fully populated with 26 AWG stranded conductors and aluminum mylar shielding. They are equipped with readily accessible thumbscrew type hold downs. Hex nuts on female connectors are removable to expose 4-40 thumbscrews.						
<a href="#">CHD26MM-2.5</a>	Deluxe Molded Cable, HD26 Male / Male, 2.5 ft	24.90	23.41	21.91	20.42	18.92
<a href="#">CHD26MM-5</a>	Deluxe Molded Cable, HD26 Male / Male, 5.0 ft	26.75	25.14	23.54	21.94	20.33
<a href="#">CHD26MM-10</a>	Deluxe Molded Cable, HD26 Male / Male, 10.0 ft	30.50	28.67	26.84	25.01	23.18
<a href="#">CHD26MM-15</a>	Deluxe Molded Cable, HD26 Male / Male, 15.0 ft	34.25	32.20	30.14	28.09	26.03
<a href="#">CHD26MF-2.5</a>	Deluxe Molded Cable, HD26 Male / Female, 2.5 ft	24.90	23.41	21.91	20.42	18.92
<a href="#">CHD26MF-5</a>	Deluxe Molded Cable, HD26 Male / Female, 5.0 ft	26.75	25.14	23.54	21.94	20.33
<a href="#">CHD26MF-10</a>	Deluxe Molded Cable, HD26 Male / Female, 10.0 ft	30.50	28.67	26.84	25.01	23.18
<a href="#">CHD26MF-15</a>	Deluxe Molded Cable, HD26 Male / Female, 15.0 ft	34.25	32.20	30.14	28.09	26.03
<a href="#">CHD26MF-25</a>	Deluxe Molded Cable, HD26 Male / Female, 25.0 ft	41.75	39.24	36.74	34.23	31.73
<a href="#">CHD26MF-50</a>	Deluxe Molded Cable, HD26 Male / Female, 50.0 ft	60.50	56.87	53.24	49.61	45.98

<b>✓RoHS Deluxe High-Density 44 Pin Molded Cables - Fully Populated and Shielded</b>						
Injection molded cable assemblies with HD44 terminations. Fully populated with 24 AWG stranded conductors and aluminum mylar and braided shielding. 4-40 metal thumbscrews molded into the strain relief. Hex nuts on female connectors are removable to expose 4-40 thumbscrews.						
<a href="#">CHD44MM-2.5</a>	Deluxe Molded Cable, HD44 Male / Male, 2.5 ft	40.50	38.07	35.64	33.21	30.78
<a href="#">CHD44MM-5</a>	Deluxe Molded Cable, HD44 Male / Male, 5.0 ft	48.00	45.12	42.24	39.36	36.48
<a href="#">CHD44MM-10</a>	Deluxe Molded Cable, HD44 Male / Male, 10.0 ft	63.00	59.22	55.44	51.66	47.88
<a href="#">CHD44MM-15</a>	Deluxe Molded Cable, HD44 Male / Male, 15.0 ft	78.00	73.32	68.64	63.96	59.28
<a href="#">CHD44MM-25</a>	Deluxe Molded Cable, HD44 Male / Male, 25.0 ft	108.00	101.52	95.04	88.56	82.08
<a href="#">CHD44MM-50</a>	Deluxe Molded Cable, HD44 Male / Male, 50.0 ft	183.00	172.02	161.04	150.06	139.08
<a href="#">CHD44MF-2.5</a>	Deluxe Molded Cable, HD44 Male / Female, 2.5 ft	40.50	38.07	35.64	33.21	30.78
<a href="#">CHD44MF-5</a>	Deluxe Molded Cable, HD44 Male / Female, 5.0 ft	48.00	45.12	42.24	39.36	36.48
<a href="#">CHD44MF-10</a>	Deluxe Molded Cable, HD44 Male / Female, 10.0 ft	63.00	59.22	55.44	51.66	47.88
<a href="#">CHD44MF-15</a>	Deluxe Molded Cable, HD44 Male / Female, 15.0 ft	78.00	73.32	68.64	63.96	59.28
<a href="#">CHD44MF-25</a>	Deluxe Molded Cable, HD44 Male / Female, 25.0 ft	108.00	101.52	95.04	88.56	82.08
<a href="#">CHD44MF-50</a>	Deluxe Molded Cable, HD44 Male / Female, 50.0 ft	183.00	172.02	161.04	150.06	139.08

<b>✓RoHS Deluxe High-Density 62 Pin Molded Cables - 31 Twisted Pairs and Full Shielding</b>						
Fully molded data cables with HD62 D-Sub connectors. Fully shielded with aluminum mylar shielding and fully populated with 28 AWG twisted pairs. Straight-thru pinning. Equipped with 4-40 thumbscrews. Hex nuts on female connectors are removable to expose 4-40 thumbscrews.						
<a href="#">CHD62MM-2.5</a>	Deluxe Molded Cable, HD62 Male / Male, 2.5 ft	52.50	49.35	46.20	43.05	39.90
<a href="#">CHD62MM-5</a>	Deluxe Molded Cable, HD62 Male / Male, 5.0 ft	62.50	58.75	55.00	51.25	47.50
<a href="#">CHD62MM-10</a>	Deluxe Molded Cable, HD62 Male / Male, 10.0 ft	82.50	77.55	72.60	67.65	62.70
<a href="#">CHD62MM-15</a>	Deluxe Molded Cable, HD62 Male / Male, 15.0 ft	102.50	96.35	90.20	84.05	77.90
<a href="#">CHD62MM-25</a>	Deluxe Molded Cable, HD62 Male / Male, 25.0 ft	122.50	115.15	107.80	100.45	93.10
<a href="#">CHD62MM-50</a>	Deluxe Molded Cable, HD62 Male / Male, 50.0 ft	222.50	209.15	195.80	182.45	169.10
<a href="#">CHD62MF-2.5</a>	Deluxe Molded Cable, HD62 Male / Female, 2.5 ft	52.50	49.35	46.20	43.05	39.90
<a href="#">CHD62MF-5</a>	Deluxe Molded Cable, HD62 Male / Female, 5.0 ft	62.50	58.75	55.00	51.25	47.50
<a href="#">CHD62MF-10</a>	Deluxe Molded Cable, HD62 Male / Female, 10.0 ft	82.50	77.55	72.60	67.65	62.70
<a href="#">CHD62MF-15</a>	Deluxe Molded Cable, HD62 Male / Female, 15.0 ft	102.50	96.35	90.20	84.05	77.90
<a href="#">CHD62MF-25</a>	Deluxe Molded Cable, HD62 Male / Female, 25.0 ft	122.50	115.15	107.80	100.45	93.10
<a href="#">CHD62MF-50</a>	Deluxe Molded Cable, HD62 Male / Female, 50.0 ft	222.50	209.15	195.80	182.45	169.10

<b>✓RoHS Deluxe High-Density 78 Pin Molded Cables - 39 Twisted Pairs and Double Shielded</b>						
Fully molded data cables equipped with HD78 D-Sub connectors. Fully shielded with aluminum mylar and braided shielding and fully populated with 28 AWG twisted pairs. Straight-thru pinning. Equipped with 4-40 thumbscrews. Hex nuts on female connectors are removable to expose 4-40 thumbscrews.						
<a href="#">CHD78MM-2.5</a>	Deluxe Molded Cable, HD78 Male / Male, 2.5 ft	57.50	54.05	50.60	47.15	43.70
<a href="#">CHD78MM-5</a>	Deluxe Molded Cable, HD78 Male / Male, 5.0 ft	70.00	65.80	61.60	57.40	53.20
<a href="#">CHD78MM-10</a>	Deluxe Molded Cable, HD78 Male / Male, 10.0 ft	95.00	89.30	83.60	77.90	72.20
<a href="#">CHD78MM-25</a>	Deluxe Molded Cable, HD78 Male / Male, 25.0 ft	170.00	159.80	149.60	139.40	129.20
<a href="#">CHD78MM-50</a>	Deluxe Molded Cable, HD78 Male / Male, 50.0 ft	295.00	277.30	259.60	241.90	224.20
<a href="#">CHD78MF-2.5</a>	Deluxe Molded Cable, HD78 Male / Female, 2.5 ft	57.50	54.05	50.60	47.15	43.70
<a href="#">CHD78MF-5</a>	Deluxe Molded Cable, HD78 Male / Female, 5.0 ft	70.00	65.80	61.60	57.40	53.20
<a href="#">CHD78MF-10</a>	Deluxe Molded Cable, HD78 Male / Female, 10.0 ft	95.00	89.30	83.60	77.90	72.20
<a href="#">CHD78MF-25</a>	Deluxe Molded Cable, HD78 Male / Female, 25.0 ft	170.00	159.80	149.60	139.40	129.20
<a href="#">CHD78MF-50</a>	Deluxe Molded Cable, HD78 Male / Female, 50.0 ft	295.00	277.30	259.60	241.90	224.20