



List Price \$228.00 USD

Availability **Non-Stock Item: This item is not normally stocked in our distribution facility.**

Technical Characteristics

Ampere Rating	9A
Degree of Protection	IP20
Horsepower Rating	2HP@230VAC - 5HP@460VAC
External Control Voltage	Built into the soft start
Input Voltage	200-240VAC
Marketing Trade Name	Altistart 01
Soft Starting Time	1 to 10 seconds (adjustable)
Soft Stopping Time	1 to 10 seconds (adjustable)
Number of Functions	1
Input Phase	3-Phase
Output Phase	3-Phase
Type	ATS01
Depth	4.45 Inches
Height	4.88 Inches
Width	1.77 Inches

Shipping and Ordering

Category	22392 -
Discount Schedule	I11
GTIN	00785901676027
Package Quantity	1
Weight	1.13 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	N
Country of Origin	DE

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.