

Main

Product or component type	Communication card
Range compatibility	Altivar 312
Communication port protocol	Profibus DP
Electrical connection	1 connector RJ45, Modbus 1 removable screw terminal block for inputs/outputs Screw terminal block, Profibus DP
Transmission rate	9600 bps, 19.2, 93.75, 187.5, 500 kbps, 1.5, 3, 6 or 12 Mbps
Number of addresses	1...126

Complementary

Input/Output number	AI2 and AI3: 2 analog input LI1...LI3: 3 logic input R2: 1 relay output
Communication service	CiA 402 profile Messaging via PKW periodic variables Periodic variables input : 4 PKW and 2 PZD Periodic variables output : 4 PKW and 2 PZD
Display type	1 LED 1 LED for ST (status)
Product weight	0.2 kg

Environment

RoHS EUR status	Compliant
RoHS EUR conformity date	0939

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.