

6.02174.50
W 18 LTX 125
4007430201249

18 Volt cordless angle grinder W 18 LTX 125



0217000S_51A.EPS

- Robust and wear-resistant motor
- Slim motor housing for ideal handling
- Battery pack can be swivelled for working in hard to reach places.
- Detachable dust filter for protection from intruding particles
- Tool change without key
- Twist-proof protective cover, can be adjusted within seconds without tools
- High torque for powerful grinding and quick separation
- Electronic soft start
- LED for information about specific situations (e.g. triggered no-volt release switch)
- Thermal overload protection
- No-volt release switch: Prevents unintentionally starting the machine.
- Multifunctional monitoring system to protect the machine and battery pack
- AIR COOLED technology for speedy charging and long service life
- Robust battery packs with capacity display
- 3 year battery pack warranty

Vergleichbare Gerätekenneiwerte

Type of battery pack	Li-ion
Capacity of battery pack	3,0 Ah
Battery pack voltage	18 V
Grinding wheel Ø	125 mm
Idle revolution	8.000 /min
Spindle thread	M 14
Weight (including battery pack)	2,4 kg

Scope of delivery

Protective cover, Inner support flange, adjusting nut (without tools), handle, dust filter, 2 Li-Power Extreme battery packs (18 V/3.0 Ah), "AIR COOLED" quick charger ASC 30, Plastic carry case