

Material Handling **Productivity Solutions**

Store Organize & Transport

Innovative **NEW** Products

InSight™ Ultra-Clear Bins – page 11

ShelfMax™ – page 13

Indicator™ Bins – page 21

AkroDrawers™ – pages 16-20

Wire & Steel Shelving Packages – pages 36-42



Akro-Mils® Productivity Solutions

store, organize, transport & more!



Ready, Set, Organize™ ... & Save!

Akro-Mils is all about storage, organization and transport solutions that increase material handling efficiency and reduce costs in virtually any industry. Our broad range of products are used to shorten assembly times, maintain accurate inventories, optimize storage space and improve parts protection – all in support of Lean practices and other initiatives to increase productivity and profitability in any setting, from industrial to commercial to retail.



Simplify Organization

Storage Bins – Replace the mess and expense of cardboard boxes with our wide selection of reusable bins. Simplify organization and maintain quality to improve efficiency in any operation.



Improve Handling Efficiency

Hand-Held Containers – Reusable containers deliver flexibility and savings. From Attached Lid to Straight Wall styles, our selection matches your needs in any industry – industrial, distribution, healthcare and more!

Maximize Space Usage

Bin Systems – Take back valuable floor space and improve storage efficiency with bin systems, including shelving, cabinets, racks, rails, carts and louvered panels.



Move With Efficiency

Transport Systems – We offer a broad selection of work centers, carts, platform trucks and dollies to complement any warehouse or workflow system. We can customize to fit your unique needs.

Custom Products

You can order a variety of custom products, OEM solutions and unique merchandising systems – all from Akro-Mils!



Our unrivaled production resources, dependable quality and dedicated customer service support provide custom solutions to meet your exact needs. With five thermoplastic molding processes, extensive metal and

Clean & Safe Work Environments

Waste Handling Systems – Durable, cost-effective carts provide years of dependable service for industrial waste collection and handling systems.



wood fabrication and quality powder-coating, Akro-Mils can match your custom project to the most effective process for optimal performance and cost-efficiency. From product concept to final product design, your project will be guided in an efficient process that incorporates quality at every stage.

Quality You Can Trust

Manufactured under rigorous ISO 9001 standards, Akro-Mils products are quality tested to ensure they continuously meet your performance expectations. In doing so, they optimize productivity and, ultimately, customer satisfaction throughout the supply chain. Akro-Mils is proud of the quality and service awards from our customers, and we apply the recognition we receive to work toward continuous improvement.



To learn more, call 800-253-2467 or visit www.akro-mils.com





Table of Contents

everything you need. . .

Storage Bins, Racks & Hanging Systems

<ul style="list-style-type: none"> • AkroBins® • EarthSaver AkroBins® • ProHANGER® • Rail Hanging Systems • Louvered Hanging Systems • ReadySpace™ Storage System • InSight™ Bins • Shelf Bins • ShelfMax™ Bins • EarthSaver™ Shelf Bins 	<ul style="list-style-type: none"> • Pick Rack Systems • AkroDrawers™ • Indicator™ Bins • VantageBins™ • 1800 Series AkroBins® • ESD Containers • Economy Bins • System Bins™ • Easy Flow Gravity Hopper 	4-25
--	---	-------------

Heavy Duty Bins, Totes, Containers & Small Parts Storage

<ul style="list-style-type: none"> • Super-Size AkroBins® • Stak-N-Store Bins • Nest & Stack Totes • Akro-Grids • Attached Lid Containers • Straight Wall Containers • Cross-Stack Akro-Tubs 	<ul style="list-style-type: none"> • Akro-Tubs • Storage Cabinets • Storage-Go-Round • Storage Cases • Roto-Shelf • Tote Caddy 	26-35
---	--	--------------

Shelving Systems & Cabinets

<ul style="list-style-type: none"> • Wire Shelving Systems • Steel Shelving Systems 	<ul style="list-style-type: none"> • Heavy-Duty Cabinets • Standard Cabinets 	36-44
---	--	--------------

Mobile Systems & Work Centers

<ul style="list-style-type: none"> • ProCart™ • Louvered Carts • Multi-Shelf Carts • Tray Service Cart • Box Trucks • High-End Narrow Aisle Trucks • Dollies • Hand Trucks 	<ul style="list-style-type: none"> • Specialty Hand Trucks • Drum Handling Equipment • VERSA/Deck™ • Platform Trucks • Skids (Semi-Live) • Portable Tables & Carts • Mobile Work Tables • Heavy-Duty Work Benches 	45-59
--	---	--------------

Waste Transport Systems

<ul style="list-style-type: none"> • Akro-Tilt Trucks • Akro-Carts 	<ul style="list-style-type: none"> • MegaKart® 	60
--	---	-----------

Materials/Casters & Wheels

<ul style="list-style-type: none"> • Materials Definitions & Benefits 	<ul style="list-style-type: none"> • Casters & Wheels Selection Information 	61
--	--	-----------


Product Index

62-63




- Control inventories, shorten assembly times and minimize parts handling
- Heavy-duty bins securely stack atop each other, sit on shelving and hang from Akro-Mils racks, panels, rails and carts
- Molded of high-impact polypropylene, AkroBins are unaffected by weak acids and alkalis
- Products made of polypropylene block copolymer are autoclavable up to 250° F
- Sturdy, one-piece construction is water, rust and corrosion-proof
- Guaranteed not to crack or break under normal load conditions as stated in our 1-year limited warranty
- Available in 14 sizes and 7 colors: Red, Yellow, Blue, Stone, Green, Semi-Clear and Black

accessories



"See-through" Crystal Styrene Lids keep contents dust-free and protected



Lengthwise Dividers keep items separated in the bin



30320 Wide AkroBins: Dividers available in two sizes



33" Wide AkroBin

Great Lengths to Organize More Efficiently

- 1 to 8 compartments, depending on divider placement
- Optional lid sold separately
- 2½" and 4" dividers available (comes with two 4" dividers)
- Fits on standard Akro-Mils rail, louvered and 36" shelf systems
- Reinforced sides for secure stacking



30320 33" Wide AkroBin with Optional Lid


features




Anti-slide stop prevents stacked bins from shifting forward



Full-width hanger lip supports bin on hanging system



Reinforced side ribs add strength and prevent spreading when stacked



Extra-wide stacking ledge saves space and prevents spills





Large front label area for easy coding and scanning



Curved-bottom hopper front makes it easy to retrieve small parts



Dividers allow you to create customizable compartment sizes



AkroBins	Model No.	Outside Dimensions Inches			Bottom Dimensions Inches				Bin Load Capacity On Rack	Bin Ctn. Qty.	Accessories			
		L	W	H	L	W	H	X			Dividers**	Divider Pkg. Qty.	Bin Lids***	Lid Pkg. Qty.
	A 30210	5 $\frac{3}{8}$	4 $\frac{1}{8}$	3	4 $\frac{3}{8}$	3 $\frac{7}{8}$	2 $\frac{13}{16}$	4	10 lbs.	24	40210 (1)	6	30211	24
	30220	7 $\frac{3}{8}$	4 $\frac{1}{8}$	3	6 $\frac{3}{8}$	3 $\frac{7}{8}$	2 $\frac{13}{16}$	6	10 lbs.	24	40220 (1)	6	30221	24
	30224	10 $\frac{7}{8}$	4 $\frac{1}{8}$	4	10 $\frac{1}{4}$	3 $\frac{3}{8}$	3 $\frac{3}{4}$	9	30 lbs.	12	-	-	-	-
	B 30230	10 $\frac{7}{8}$	5 $\frac{1}{2}$	5	10 $\frac{1}{4}$	4 $\frac{3}{8}$	4 $\frac{3}{8}$	9	30 lbs.	12	40230 (1)	6	30231	12
	30234	14 $\frac{3}{8}$	5 $\frac{1}{2}$	5	14 $\frac{1}{16}$	4 $\frac{3}{8}$	4 $\frac{3}{8}$	12 $\frac{13}{16}$	50 lbs.	12	-	-	-	-
	C 30239	10 $\frac{3}{4}$	8 $\frac{1}{4}$	7	10	6 $\frac{5}{8}$	6 $\frac{3}{4}$	8	50 lbs.	6	40239 (1)	6	-	-
	30240	14 $\frac{3}{4}$	8 $\frac{1}{4}$	7	14	6 $\frac{5}{8}$	6 $\frac{3}{4}$	12	60 lbs.	12	40245 (1)	6	-	-
	30265	18	8 $\frac{1}{4}$	9	17 $\frac{1}{8}$	6 $\frac{3}{4}$	8 $\frac{1}{4}$	14 $\frac{1}{2}$	60 lbs.	6	40265 (1)	6	-	-
	D 30235	10 $\frac{7}{8}$	11	5	10 $\frac{1}{4}$	10	4 $\frac{3}{8}$	9	50 lbs.	6	40230 (3)	6	30236	6
	30260	18	11	10	17	9 $\frac{1}{2}$	9 $\frac{3}{8}$	14 $\frac{3}{16}$	60 lbs.	6	40260 (3)	6	-	-
	E 30255	10 $\frac{7}{8}$	16 $\frac{1}{2}$	5	9 $\frac{3}{4}$	15	4 $\frac{3}{8}$	9	60 lbs.	6	40230 (3)	6	-	-
	30250	14 $\frac{3}{4}$	16 $\frac{1}{2}$	7	14	14 $\frac{3}{4}$	6 $\frac{3}{4}$	12	75 lbs.	6	40245 (3)	6	-	-
	30270	18	16 $\frac{1}{2}$	11	17 $\frac{1}{8}$	14 $\frac{3}{4}$	10 $\frac{1}{4}$	14	100 lbs.*	3	40270 (3)	6	-	-
	F 30320	8 $\frac{1}{8}$	33	5	7	31 $\frac{1}{2}$	4 $\frac{3}{8}$	6	80 lbs.	4	40321 & 40220 (7)	7	30321	4

One color per carton: Specify Red, Blue, Yellow, Stone, Semi-Clear, Green or Black. Order in carton quantities. *Note 30265 & 30270 are not designed for use with hanging systems.
 CAUTION: When using bins with hanging systems, do not exceed the weight capacity for the rack, which may be less than the total sum of bin capacities.
 ** () = Max. # of dividers per bin. ***Assembly required - hinge pins included.



products related products

Create the perfect storage system – mix and match your selection of AkroBins with compatible products including:

- Rail Hanging Systems..... pg. 8
- Louvered Hanging Systems pg. 9
- ReadySpace Storage Systems pg. 10
- Wire Shelving Systems pgs. 36-39
- Steel Shelving Systems pgs. 40-42
- Bin Cabinets pgs. 43-44
- ProCart..... pg. 45



EarthSaver™ Series: AkroBins®

storage bins, racks & hanging systems



- AkroBins now made from 100% recycled material
- Three color options – Hunter Green, Sandstone and Terra Cotta
- Optional dividers keep items neatly separated
- An eco-friendly choice in storage and organization products



Go Green With 100% Recycled Bins – Boost Productivity, Reduce Waste!

Feeling the need to “Go Green”? Akro-Mils introduces the **EarthSaver Series** – AkroBins and Shelf Bins (see pg. 14) made from 100% recycled plastic. Make a positive impact on the environment!

related products


Create the perfect storage system – mix and match your selection of AkroBins with compatible products including:

- Rail Hanging Systems..... pg. 8
- Louvered Hanging Systems pg. 9
- ReadySpace Storage Systems pg. 10
- Wire Shelving Systems pgs. 36-39
- Steel Shelving Systems pgs. 40-42
- Bin Cabinets..... pgs. 43-44
- ProCart..... pg. 45

accessories




“See-through” Crystal Styrene Lids keep contents dust-free and protected



Lengthwise Dividers keep items separated in the bin

AkroBins	Model No.	Outside Dimensions Inches			Inside Dimensions Inches				Bin Load Capacity On Rack	Bin Ctn. Qty.	Accessories			
		L	W	H	L	W	H	X			Dividers**	Divider Pkg. Qty.	Bin Lids***	Lid Pkg. Qty.
	30210RECVSS	5½	4¼	3	4¾	3⅞	2⅜	4	10 lbs.	24	40210 (1)	6	30211	24
	30210RECYTC	5½	4¼	3	4¾	3⅞	2⅜	4	10 lbs.	24	40210 (1)	6	30211	24
	30210RECYHG	5½	4¼	3	4¾	3⅞	2⅜	4	10 lbs.	24	40210 (1)	6	30211	24
	30220RECVSS	7½	4¼	3	6¾	3⅞	2⅜	6	10 lbs.	24	40220 (1)	6	30221	24
	30220RECYTC	7½	4¼	3	6¾	3⅞	2⅜	6	10 lbs.	24	40220 (1)	6	30221	24
	30220RECYHG	7½	4¼	3	6¾	3⅞	2⅜	6	10 lbs.	24	40220 (1)	6	30221	24
	30230RECVSS	10½	5½	5	10¼	4¾	4¾	9	30 lbs.	12	40230 (1)	6	30231	12
	30230RECYTC	10½	5½	5	10¼	4¾	4¾	9	30 lbs.	12	40230 (1)	6	30231	12
	30230RECYHG	10½	5½	5	10¼	4¾	4¾	9	30 lbs.	12	40230 (1)	6	30231	12
	30240RECVSS	14¾	8¼	7	14	6⅞	6¾	12	60 lbs.	12	40245 (1)	6	–	–
	30240RECYTC	14¾	8¼	7	14	6⅞	6¾	12	60 lbs.	12	40245 (1)	6	–	–
	30240RECYHG	14¾	8¼	7	14	6⅞	6¾	12	60 lbs.	12	40245 (1)	6	–	–
	30250RECVSS	14¾	16½	7	14	14¾	6¾	12	75 lbs.	6	40245 (3)	6	–	–
	30250RECYTC	14¾	16½	7	14	14¾	6¾	12	75 lbs.	6	40245 (3)	6	–	–
	30250RECYHG	14¾	16½	7	14	14¾	6¾	12	75 lbs.	6	40245 (3)	6	–	–



One color per carton: SS = Sandstone, TC = Terra Cotta and HG = Hunter Green. Order in carton quantities. CAUTION: When using bins with hanging systems, do not exceed the weight capacity for the rack, which may be less than the total sum of bin capacities.

() = Max. # of dividers per bin. *Assembly required – hinge pins included.

ProHANGER®

storage bins, racks & hanging systems

- ProHANGERS can be placed side-by-side on walls, rail rack or panel systems to support extra-long parts, supplies or materials
- Unique “J-hook design” cradles various shapes and sizes of contents
- Available End Cap inserts keep items from sliding out
- One-piece construction; molded of high-impact plastic for durability
- Each ProHANGER is capable of supporting up to 75 lbs.



Easy Long Parts Storage Wherever You Need It!

- ProHANGER can be used alone or with a variety of Akro-Mils products, including a wide range of AkroBins®
- ProHANGER can even be mounted (using Louvered Hanging System) in service trucks for maintenance workers, plumbers, electricians, carpenters or other tradespeople

ProHANGER®




ProHANGER shown with Louvered Hanging Panel and 33" Wide AkroBin

ProHANGER End Cap



ProHANGER

ProHANGER®				Inches			
	Model No.	Description	Ctn. Qty.	L	W	H	Capacity (lbs.)
	30330RED	ProHANGER	6	8¼	7¾	5	75
	40330	End Cap	6	6¾	¼	4¼	-
	403302PK	End Cap	2	6¾	¼	4¼	-

related products

Use your ProHANGER with:


- AkroBins pgs. 4-6
- Rail Hanging Systems pg. 8
- Louvered Hanging Systems pg. 9

* US patent pending.

features




Smooth surface protects suspended parts or products




End Caps help keep items contained and fit easily into molded-in slots



Full-width hanger lip supports ProHANGER on hanging systems



Notches provided in hanger lip for mounting to wall surface with screws



Substantial ribbing in base gives added strength to support heavier items




Rail Hanging Systems

storage bins, racks & hanging systems



- Rail Hanging Systems allow for fast, easy organization and parts retrieval
- Single-sided rail units are ideal for placement against a wall to save space
- Double-sided rail units can “float” in any room environment and be picked from both sides
- Mobile Kit available to mobilize two-sided racks
- Steel rail is ideal for workstations
- AkroBins sold separately



features



Rails securely support AkroBins



Heavy-duty steel for strength and durability



Attractive, durable powder-coated finish stands up to heavy-duty use



- 30008**
- 1-Sided, can be assembled as 12 or 16 Rail
 - 250 lb. capacity



- 30016**
- 2-Sided, can be assembled as 12 or 16 Rail
 - 500 lb. capacity



- 30812 Bin Cart with Casters**
- 14-gauge steel worktop
 - 250 lb. capacity



- 30812 Bin Cart**
Shown with 30230 AkroBins

- 30148 Steel Rail**
Wall-mountable unit accepts 7 sizes of AkroBins. 110 lb. capacity

Rail Hanging Systems

Model No.	Description	Ctn. Qty.	Dimensions Inches			AkroBins Model No. (Bin Weight Capacity)										
			L	W	H	30210 (10 lbs.)	30220 (10 lbs.)	30224 (30 lbs.)	30230 (30 lbs.)	30234 (50 lbs.)	30235 (60 lbs.)	30239 (50 lbs.)	30240 (60 lbs.)	30250 (75 lbs.)	30255 (60 lbs.)	
	30008*	1	36	14 $\frac{1}{2}$	53	96	96	48	48	48	24	24	24	12	16	
	30016*	1	36	20	53	192	192	96	96	96	48	48	48	24	32	
	30148	1	47 $\frac{3}{16}$	5 $\frac{1}{8}$	3	11	11	11	8	6	3	-	-	-	3	
	30812	1	38 $\frac{1}{2}$	24	36 $\frac{1}{2}$	96	96	64	48	48	24	24	24	12	16	

*Can be assembled as a 12 or 16 rail rack.

Mobile Kit

Model No.	Description	Ctn. Qty.	Fits Hanging System No.	Casters
30424	Mobile Kit - Casters & Handle	1	30016	4" Polyolefin



Two-Sided Racks can be mobilized with the **Mobile Kit**

Louvered Hanging Systems

storage bins, racks & hanging systems

- Louvered Hanging Systems allow for easy placement and configuration of AkroBins*
- Wall-mounted units keep items out of the way, off the floor and off the work table
- Floor standing racks can be placed near work areas to improve productivity
- Single-sided floor racks can be placed against wall to save floor space
- Double-sided units allow for picking from both sides
- Bench racks are used on work tables to keep parts within easy reach
- 11 different models available – accommodates up to 288 AkroBins
- Easy, one-person assembly



*AkroBins sold separately, see pg. 4-6

related products

Use the following products with Louvered Hanging Systems:

- AkroBins..... pgs. 4-6
- 33" Wide AkroBins..... pgs. 4-5
- ProHANGER..... Pg. 7

30636
Louvered Panel
Shown with 33" Wide AkroBins
(see pg. 4 for details)








98636
Bench Rack



Louvered Hanging Systems

Dimensions (Inches)

AkroBins Model No. (Bin Weight Capacity)

Model No.	Description	Ctn. Qty	L	W	H	Rack Wt. Cap.(lbs.)	30210 (10 lbs.)	30220 (10 lbs.)	30224 (30 lbs.)	30230 (30 lbs.)	30234 (50 lbs.)	30235 (60 lbs.)	30239 (50 lbs.)	30240 (60 lbs.)	30250 (75 lbs.)	30255 (60 lbs.)	30320 (80 lbs.)	
 30618*	Louvered Panel	4	18	5/16	19	160	16	16	12	9	9	3	4	4	2	3	-	
 30636*	Louvered Panel	4	35 3/4	5/16	19	160	32	32	24	18	18	9	8	8	4	6	3	
	2 Panels		35 3/4	5/16	37		72	72	36	36	36	18	16	16	8	12	5	
	3 Panels		35 3/4	5/16	55		104	104	54	54	54	27	28	28	14	18	8	
	4 Panels		35 3/4	5/16	73		144	144	72	72	72	36	36	36	18	24	11	
 98600*	Bench Rack	1	27 1/16	8 3/8	19 1/16	120	30	30	18	12	12	6	6	6	-	-	0	
	98636	Bench Rack	1	36	8	20	120	40	40	24	18	18	9	8	8	4	6	3
 30161	Louvered Panel	1	36	5/16	61	120	96	96	72	60	60	28	24	24	12	18	10	
	30118	Louvered Panel	1	18	5/16	61	160	48	48	36	30	30	14	12	12	6	9	-
 30653	Louvered Floor Rack	1	35 3/4	32	75 1/2	2000	288	288	192	144	144	72	72	72	36	48	0	
	30661	Louvered Rack Single-Sided	1	36 3/16	13 1/2	66 3/8	500	96	96	72	54	54	28	24	24	12	18	10
	30638	Louvered Rack Single-Sided	1	18	13 1/2	66 3/8	250	48	48	36	30	30	14	12	12	6	9	-
	30676	Louvered Rack Double-Sided	1	36 3/16	25	66 3/8	1000	192	192	144	108	108	56	48	48	24	36	20
	30651	Heavy Duty Louvered Rack Single-Sided	1	35 3/4	17	75 1/2	1000	144	144	98	72	72	36	36	36	18	24	11

*Also available in Beige.

features



Formed from 16-gauge cold-rolled steel for strength and durability



Attractive, durable powder-coated finish stands up to heavy-duty use



Horizontal ribs provide added strength



Louvers securely support AkroBins

Bin Retainer Clip

Hold bins safely on louvered panels

- Made of durable engineering grade plastic
- Easy to use
- Will work with any size AkroBin or ProHANGER
- Perfect for service vans; maintenance workers, plumbers, electricians or other tradesmen who store and transport supplies and materials



40599
Bin Retainer Clip

ReadySpace™ Storage System

storage bins, racks & hanging systems

- Wall, Bench or Mobile Floor Units can be purchased alone or with AkroBins
- Create a neat, attractive storage space in any environment – customer-friendly appearance
- Frees up valuable workspace
- Pre-configured packages with Stone color AkroBins are available or create your own custom system – see pg. 4-6 for more AkroBins!



Ideal For the Healthcare Industry!

Ready, Set, Organize!™

- Quickly create organized storage space virtually anywhere!
- Steel louvered storage system for hospitals, laboratories and medical offices
- Designed for use with a wide variety of Akro-Mils AkroBins®
- Clean, sleek look with a durable white, powder-coated finish
- Set up and installation are quick and easy
- ReadySpace Bench or Mobile Floor Units can double as a privacy wall!



98536 Bench Unit

- Can be assembled single- or double-sided



Wall Unit

- Accommodates multiple sizes of AkroBins



30553 Mobile Floor Unit

- Quickly transports supplies

features



Casters come standard with the Mobile Floor Unit



Wall Unit is shipped complete with its own mounting bracket for easy installation



Bench Unit has a two-piece base for placement against or away from wall for assembly as single- or double-sided



Durable white, powder-coated finish

ReadySpace™ Wall Unit

Model No.	Description (L x W x H)	No. of Ctns.	Ship Weight (lbs.)	Bin Qty.
30536	37½" x 1¾" x 25¾", Panel	1	35	N/A
30536210S	Unit with 30210STONE Bins	3	45	48
30536220S	Unit with 30220STONE Bins	3	51	48
30536230S	Unit with 30230STONE Bins	3	55	24
30536235S	Unit with 30235STONE Bins	3	55	12
30536320S	Unit with 30320STONE Bins	2	47	4

ReadySpace™ Mobile Floor Unit

Model No.	Description (L x W x H)	No. of Ctns.	Ship Weight (lbs.)	Bin Qty.
30553	24¾" x 23" x 52"	1	82	N/A
30553210S	Unit with 30210STONE Bins	6	117	120
30553220S	Unit with 30220STONE Bins	6	122	120
30553230S	Unit with 30230STONE Bins	6	142	60
30553235S	Unit with 30235STONE Bins	6	127	30
30553LF	Leveling Feet for Floor Unit	-	1	-

ReadySpace™ Bench Unit (Assemble as Single or Double-Sided)

Model No.	Description (L x W x H)	No. of Ctns.	Ship Weight (lbs.)	Bin Qty.
98536	37¾" x 12" x 26¾" (Single)	1	51	N/A
	37¾" x 22½" x 26¾" (Double)	1	51	N/A

ReadySpace™ Single-Sided Bench Unit Kits

Model No.	Description	No. of Ctns.	Ship Weight (lbs.)	Bin Qty.
98536210SS	Unit with 30210STONE Bins	3	61	48
98536220SS	Unit with 30220STONE Bins	3	67	48
98536230SS	Unit with 30230STONE Bins	3	71	24
98536235SS	Unit with 30235STONE Bins	3	71	12
98536320SS	Unit with 30320STONE Bins	2	63	4

ReadySpace™ Double-Sided Bench Unit Kits

Model No.	Description	No. of Ctns.	Ship Weight (lbs.)	Bin Qty.
98536210SD	Unit with 30210STONE Bins	5	71	96
98536220SD	Unit with 30220STONE Bins	5	83	96
98536230SD	Unit with 30230STONE Bins	5	91	48
98536235SD	Unit with 30235STONE Bins	5	91	24
98536320SD	Unit with 30320STONE Bins	3	75	8



InSight™

storage bins, racks & hanging systems



Wall Unit (30536A3 shown)

- Frees up valuable workspace
- Clean, sleek look with a white powder-coated finish
- Four bin size packages available



Mobile Floor Unit (30553B1 shown)

- Organizes, shares and transports supplies and products
- Perfect for "high-demand" items
- Panel easily locks into posts on base without tools
- Four bin size packages available



Louvered Panel Unit (30636BEIGE Louvered Panel shown with 305A3 bins)

- Louvers securely support InSight™ bins
- Use alone or side-by-side with additional louvered panels
- Easy one-person assembly

- Provide easy and maximum visibility to users in a sleek, modern design
- Can be stacked, sit on shelving or hang on Akro-Mils rails and louvered panels or ReadySpace™ Storage System
- Optional lids protect contents from dust – will stack with lids in place
- Patent Pending: No tip feature when bins are stacked
- Clear length and width dividers available
- Large label area for part identification and bar code scanning
- Autoclavable
- Available in 4 sizes



insight
by Akro-Mils

A Visible Difference in Storage & Organization!

- Perfect for a variety of settings – from industrial to healthcare
- Bins made of durable polycarbonate material

features



Bins stack with lids in place



Rear lip supports bin on hanging systems



Lids protect bin contents from dust




Dividers allow you to create customizable compartment sizes

Outside Dimensions Inside Dimensions Inches Inches

Model No.	L	W	H	L	W	H	Capacity (lbs.)	Width Divider	Length Divider	Lid
305A1	5¾	4¾	3¼	4¼	3¾	2¾	10	415A1 (1)	405A1 (1)	305A2
305A3	7¾	4¾	3¼	6¼	3¾	2¾	10	415A1 (2)	405A3 (1)	305A4
305A5	10¾	4¾	3¼	9¼	3¾	2¾	15	415A1 (3)	405A5 (1)	305A6
305B1	10¾	5½	5¼	9¾	4¾	4¼	25	415B1 (3)	405B1 (1)	305B2

in () represents divider slots per bin



Louvered Panel and Bin Combinations

Model No.	305A1	305A3	305A5	305B1
30618BEIGE	16	16	16	9
30636BEIGE	32	32	32	18
98600BEIGE	30	30	30	12

Bins sold separately

ReadySpace™ Packages

Model No.	Description
30536A1	ReadySpace Wall Unit with 48ea. 305A1
30536A3	ReadySpace Wall Unit with 48ea. 305A3
30536A5	ReadySpace Wall Unit with 48ea. 305A5
30536B1	ReadySpace Wall Unit with 24ea. 305B1
30553A1	ReadySpace Mobile Floor Unit with 120ea. 305A1
30553A3	ReadySpace Mobile Floor Unit with 120ea. 305A3
30553A5	ReadySpace Mobile Floor Unit with 120ea. 305A5
30553B1	ReadySpace Mobile Floor Unit with 64ea. 305B1

* US Patent Pending

Shelf Bins

storage bins, racks & hanging systems



features



Wide hopper front allows easy access



Built-in rear hanger allows bin to tilt out for complete access




Molded-in label area identifies contents

accessories



Dividers create additional storage compartments. Each Bin accepts up to 7 dividers (except 30110)




Extended Label Holders are designed for larger bar code scanning



Bin Cups lift out easily for parts retrieval (see chart)

- Shelf Bins outlast corrugated bins – paying for themselves in reduced replacement costs
- Superior construction allows Shelf Bins to be fully loaded without spreading or cracking
- Durable polypropylene bins provide an attractive, neat appearance
- Works with 12", 18" and 24" deep shelving or vertical storage and retrieval units
- One-piece construction is waterproof and unaffected by grease or oil
- Available in 13 sizes and 5 colors: Red, Yellow, Blue, Green and White



related products

Expand your sorting options with:

- Pick Rack Systems.....pg. 15
- Wire Shelving Systems.....pgs. 36-39
- Steel Shelving Systemspgs. 40-42

Shelf Bins & Accessories		Outside Dimensions Inches			Bottom Dimensions Inches			Cups per Bin		Accessories		
Ltr	Model No.	L	W	H	L	W	H	Ctn. Qty.	Small 30101	Large 30102	Optional Dividers*	Divider Pkg. Qty.
12" Shelf Bins	30110	11½"	2¾"	4"	10¼"	1½"	4"	24	3	–	–	–
	30120	11½"	4½"	4"	10¼"	3"	4"	24	5	2	40120	24
	30130	11½"	6½"	4"	10¼"	5½"	4"	12	9	4	40130	24
	30150	11½"	8½"	4"	10¼"	7½"	4"	12	11	4	40150	24
	30170	11½"	11½"	4"	10¼"	10"	4"	12	15	6	40170	24
18" Shelf Bins	30128	17½"	4½"	4"	16½"	3"	4"	12	8	3	40120	24
	30138	17½"	6½"	4"	16½"	5½"	4"	12	15	6	40130	24
	30158	17½"	8½"	4"	16½"	7½"	4"	12	15	6	40150	24
	30178	17½"	11½"	4"	16½"	10"	4"	12	25	12	40170	24
24" Shelf Bins	30124	23½"	4½"	4"	22½"	3"	4"	12	11	4	40120	24
	30164	23½"	6½"	4"	22½"	5½"	4"	6	21	8	40130	24
	30184	23½"	8½"	4"	22½"	7½"	4"	6	25	8	40150	24
	30174	23½"	11½"	4"	22½"	10"	4"	6	35	16	40170	24
Bin Cups	30101	2"	3¼"	3"	–	–	–	48	–	–	–	–
	30102	2¾"	5"	3"	–	–	–	24	–	–	–	–
Extended Label Holder	10°	40410	–	4"	2¼"	–	–	–	24	–	–	–
	45°	40445	–	4"	2¼"	–	–	–	24	–	–	–

* 24 Dividers per package. One color per carton: Specify Red, Blue, Yellow, Green or White. Order in carton quantities.

ShelfMax™

storage bins, racks & hanging systems

- Go deep! Expand your storage capacity up to 85% over traditional 4" bins
- Holding capacity is up to 25% more than comparable 6" bins
- Front opening is .75" higher than comparable products
- Superior, durable construction compared to corrugated bins
- Seven sizes and five color options: Red, Blue, Yellow, Green and White
- Optional width dividers keep items neatly separated
- Rolled ridge for added strength when filled to maximum capacity



ShelfMax can be used with steel shelving, wire shelving, bench racks or pick racks



Maximize Your Storage Capacity!

- Available in five colors with optional width dividers – ShelfMax offers you the versatility you need to make the most of your storage space and keep everything in its place!
- Easy to label for quick inventory identification



APRBENCH
with 30040 ShelfMax Bins
See pg. 15

ShelfMax™	Model No.	Outside Dimensions Inches			Bottom Dimensions Inches			Storage Capacity			
		L	W	H	L	W	H	Cubic Inches	Ctn. Qty.	Optional Dividers	Divider Pkg. Qty.
	30040	11 $\frac{1}{8}$	4 $\frac{1}{8}$	6	9 $\frac{3}{4}$	2 $\frac{1}{2}$	5 $\frac{1}{16}$	175	16	40020	12
	30048	17 $\frac{7}{8}$	4 $\frac{1}{8}$	6	16	2 $\frac{1}{2}$	5 $\frac{1}{16}$	280	8	40020	12
	30080	11 $\frac{1}{8}$	8 $\frac{3}{8}$	6	9 $\frac{3}{4}$	6 $\frac{3}{8}$	5 $\frac{1}{16}$	398	8	40040	12
	30088	17 $\frac{7}{8}$	8 $\frac{3}{8}$	6	16	6 $\frac{3}{8}$	5 $\frac{1}{16}$	648	8	40040	12
	30090	11 $\frac{1}{8}$	6 $\frac{3}{8}$	6	9 $\frac{3}{4}$	5	5 $\frac{1}{16}$	310	10	40030	12
	30094	23 $\frac{3}{4}$	6 $\frac{3}{8}$	6	21 $\frac{3}{4}$	5	5 $\frac{1}{16}$	686	10	40030	12
	30098	17 $\frac{7}{8}$	6 $\frac{3}{8}$	6	16	5	5 $\frac{1}{16}$	505	10	40030	12

features



Easy to carry with large handle




Large label area on front of bin



Dividers keep items neatly separated



Built-in rear hanglock allows bin to tilt out for complete access



Reinforced side ribs for added strength

products

Use your ShelfMax bins with:

- Bench Pick Rack Systems pg. 15
- Pick Rack Systems..... pg. 15
- Wire Shelving Systems pgs. 36-39
- Steel Shelving Systems..... pgs. 40-42

EarthSaver™ Series: Shelf Bins

storage bins, racks & hanging systems



- Shelf Bins now made from 100% recycled material
- Three color options – Hunter Green, Sandstone and Terra Cotta
- Optional dividers keep items neatly separated
- An eco-friendly choice in storage and organization products






related products

Create the perfect storage system – mix and match your selection of bins with compatible products including:

- Wire Shelving Systems pgs. 36-39
- Steel Shelving Systems pgs. 40-42
- Bin Cabinets pgs. 43-44

Go Green With 100% Recycled Bins – Boost Productivity, Reduce Waste!


Feeling the need to “Go Green”? Akro-Mils introduces the **EarthSaver Series** – Shelf Bins and AkroBins (see pg. 6) made from 100% recycled plastic. Make a positive impact on the environment!

Shelf Bins & Accessories	Model No.	Outside Dimensions Inches			Inside Dimensions Inches			Ctn. Qty.	Cups per Bin		Accessories	
		L	W	H	L	W	H		Small 30101	Large 30102	Optional Dividers*	Divider Pkg. Qty.
 12" Shelf Bins	30120RECYSS	11½"	4¾"	4"	10¼"	3"	4"	24	5	2	40120	24
	30120RECYTC	11½"	4¾"	4"	10¼"	3"	4"	24	5	2	40120	24
	30120RECYHG	11½"	4¾"	4"	10¼"	3"	4"	24	5	2	40120	24
	30130RECYSS	11½"	6"	4"	10¼"	5½"	4"	12	9	4	40130	24
	30130RECYTC	11½"	6"	4"	10¼"	5½"	4"	12	9	4	40130	24
	30130RECYHG	11½"	6"	4"	10¼"	5½"	4"	12	9	4	40130	24
 18" Shelf Bins	30128RECYSS	17½"	4¾"	4"	16½"	3"	4"	12	8	3	40120	24
	30128RECYTC	17½"	4¾"	4"	16½"	3"	4"	12	8	3	40120	24
	30128RECYHG	17½"	4¾"	4"	16½"	3"	4"	12	8	3	40120	24
	30138RECYSS	17½"	6"	4"	16½"	5½"	4"	12	15	6	40130	24
	30138RECYTC	17½"	6"	4"	16½"	5½"	4"	12	15	6	40130	24
	30138RECYHG	17½"	6"	4"	16½"	5½"	4"	12	15	6	40130	24
 24" Shelf Bins	30124RECYSS	23½"	4¾"	4"	22½"	3"	4"	12	11	4	40120	24
	30124RECYTC	23½"	4¾"	4"	22½"	3"	4"	12	11	4	40120	24
	30124RECYHG	23½"	4¾"	4"	22½"	3"	4"	12	11	4	40120	24
	30164RECYSS	23½"	6"	4"	22½"	5½"	4"	6	21	8	40130	24
	30164RECYTC	23½"	6"	4"	22½"	5½"	4"	6	21	8	40130	24
	30164RECYHG	23½"	6"	4"	22½"	5½"	4"	6	21	8	40130	24

One color per carton: SS = Sandstone, TC = Terra Cotta and HG = Hunter Green. Order in carton quantities.

Bin Cups	L	W	H	Ctn. Qty.
30101	2"	3¼"	3"	48
30102	2¾"	5"	3"	24

Extended Label Holder	W	H	Ctn. Qty.	
10°	40410	4"	2¼"	24
45°	40445	4"	2¼"	24





Pick Rack Systems

storage bins, racks & hanging systems

- Improve workspace organization and efficiency with rack and bin systems
- Angled shelves keep parts at the front of bins for easy access
- Convenient, high-density storage with up to 192 bins
- Easy to assemble
- Choose from 3 styles available separately or with bin packages
- 16-gauge steel construction
- Compatible with:



Shelf Bins, pgs. 12-14



ShelfMax™, pg. 13



Indicator™ Bins, pg. 21


features



Angled shelves keep parts at front of bin



NEW
product!



Single-Sided Pick Rack

- Model No. APRS36442BLU
- Holds up to 64 Indicator Bins on 8 shelves
- Holds up to 64 ShelfMax Bins
- Maximum 400 lb. weight capacity

NEW
product!



Double-Sided Pick Rack & Mobile Kit

- Model No. APRD120Y
- Creates a mobile, double-sided pick rack with APRDMOBILE
- Holds up to 192 Shelf Bins
- Holds up to 128 ShelfMax Bins
- Maximum 800 lb. weight capacity for Double-Sided Pick Rack, 500 lb. weight capacity when used with Mobile Kit

NEW
product!



Bench Pick Rack

- Model No. APRBENCH040
- 12" D x 36 3/4" W x 25" H
- Holds up to 24 Shelf Bins or ShelfMax Bins
- Holds up to (3) 30312 System Bins

Single-Sided 12" D x 36 3/4" W x 60 1/4" H

Bin Dimensions (Inches)

Model No.	Description	Bin Model No.	L	W	H	Bin Qty.	Bonus Bins*
APRS	Single-Sided Pick Rack (no bins)	-	-	-	-	-	-
APRS110Y	Rack with Shelf Bins	30110YELLO	11 1/8"	2 3/4"	4"	96	-
APRS120Y	Rack with Shelf Bins	30120YELLO	11 1/8"	4 1/8"	4"	64	8
APRS130Y	Rack with Shelf Bins	30130YELLO	11 1/8"	6 1/8"	4"	40	8
APRS150Y	Rack with Shelf Bins	30150YELLO	11 1/8"	8 3/8"	4"	32	4
APRS170Y	Rack with Shelf Bins	30170YELLO	11 1/8"	11 1/8"	4"	24	-
APRS040**	Rack with ShelfMax	30040	11 1/8"	4 1/8"	6"	64	-
APRS080**	Rack with ShelfMax	30080	11 1/8"	8 3/8"	6"	32	-
APRS090**	Rack with ShelfMax	30090	11 1/8"	6 1/8"	6"	40	-
APRSAST00**	Rack with ShelfMax	30040 / 30090	See above			32 / 20	-
APRS36442B	Rack with Indicator Bins	36442BLUE	11 1/8"	4 1/4"	4"	64	8
APRS36462B	Rack with Indicator Bins	36462BLUE	11 1/8"	6 3/4"	4"	40	8

*Due to case pack, Bonus Bins are included at no extra charge. **Specify color of bins when ordering: Red, Blue, Yellow, Green or White.

Double-Sided 24" D x 36 3/4" W x 60 1/4" H

Bin Dimensions (Inches)

Model No.	Description	Bin Model No.	L	W	H	Bin Qty.	Bonus Bins*
APRD	Double-Sided Pick Rack (no bins)	-	-	-	-	-	-
APRD110Y	Rack with Shelf Bins	30110YELLO	11 1/8"	2 3/4"	4"	192	-
APRD120Y	Rack with Shelf Bins	30120YELLO	11 1/8"	4 1/8"	4"	128	16
APRD130Y	Rack with Shelf Bins	30130YELLO	11 1/8"	6 1/8"	4"	80	4
APRD150Y	Rack with Shelf Bins	30150YELLO	11 1/8"	8 3/8"	4"	64	8
APRD170Y	Rack with Shelf Bins	30170YELLO	11 1/8"	11 1/8"	4"	48	-
APRD040**	Rack with ShelfMax	30040	11 1/8"	4 1/8"	6"	128	-
APRD080**	Rack with ShelfMax	30080	11 1/8"	8 3/8"	6"	64	-
APRD090**	Rack with ShelfMax	30090	11 1/8"	6 1/8"	6"	80	-
APRDAST00**	Rack with ShelfMax	30040 / 30090	See above			64 / 40	-
APRD36442B	Rack with Indicator Bins	36442BLUE	11 1/8"	4 1/4"	4"	128	16
APRD36462B	Rack with Indicator Bins	36462BLUE	11 1/8"	6 3/4"	4"	80	4
APRDMOBILE	Mobile Kit (Handle & Dolly) for Double-Sided Pick Rack						

*Due to case pack, Bonus Bins are included at no extra charge. **Specify color of bins when ordering: Red, Blue, Yellow, Green or White. When using the mobile kit weight capacity is 500 lbs.

Bench Rack 12" D x 36 3/4" W x 25" H

Bin Dimensions (Inches)

Model No.	Description	Bin Model No.	L	W	H	Bin Qty.
APRBENCH	Bench Pick Rack, No Bins	-	-	-	-	-
APRBENCH120	Bench Pick Rack with Shelf Bins	30120YELLO	11 1/8"	4 1/8"	4"	24
APRBENCH150	Bench Pick Rack with Shelf Bins	30150YELLO	11 1/8"	8 3/8"	4"	12
APRBENCH040*	Bench Pick Rack with ShelfMax	30040	11 1/8"	4 1/8"	6"	24
APRBENCH090*	Bench Pick Rack with ShelfMax	30090	11 1/8"	6 1/8"	6"	15

*Specify color of bins when ordering: Red, Blue, Yellow, Green or White.

accessories



APRDMOBILE Mobile Kit

For double-sided Pick Rack
4" x 2" Phenolic Casters

AkroDrawers™

storage bins, racks & hanging systems

- Available in five convenient sizes and five colors – including Crystal Clear – which keeps AkroDrawer contents highly visible!
- Colors made of high-impact polystyrene
- Crystal Clear made of durable acrylic blend
- Offered in 12" or 18" depths to work with compatible shelving
- Easy to label and color code inventory for quick identification of parts and supplies
- Drawers can be stacked to optimize space
- Wide front handle for easy gripping when AkroDrawers are loaded or contain heavy contents
- Dividers available to keep contents neatly separated in drawers
- Colors: Crystal Clear, Red, Blue, Yellow and Gray



AkroDrawers™



AkroDrawers

Cover, Store, Protect & More!

- Designed for use in a variety of environments – from industrial to healthcare to other applications, AkroDrawers will help keep supplies, parts, tools and other materials secure and dust-free.
- Can be used with available shelving, racks, mobile carts or can be used by themselves

features



Sturdy backstop tab ensures AkroDrawers can hang securely from shelves




Features a wide front handle for easy gripping when full or filled with heavy contents

AkroDrawers™ Model No.	Outside Dimensions Inches			Bottom Dimensions Inches			Weight Capacity	Ctn. Qty.	Dividers
	L	W	H	L	W	H			
31142	11 ¹¹ / ₁₆	3 ³ / ₄	4 ¹ / ₂	10 ¹ / ₄	3	4 ⁷ / ₁₆	15 lbs.	6	41440
31162	11 ¹¹ / ₁₆	5 ⁵ / ₁₆	4 ¹ / ₂	10 ¹ / ₄	4 ⁷ / ₁₆	4 ⁷ / ₁₆	20 lbs.	6	41460
31182	11 ¹¹ / ₁₆	8 ¹ / ₂	4 ¹ / ₂	10 ¹ / ₄	7 ⁷ / ₁₆	4 ⁷ / ₁₆	20 lbs.	4	41480
31168	17 ¹⁷ / ₁₆	5 ⁵ / ₁₆	4 ¹ / ₂	16 ¹ / ₄	4 ⁷ / ₁₆	4 ⁷ / ₁₆	25 lbs.	6	41460
31188	17 ¹⁷ / ₁₆	8 ¹ / ₂	4 ¹ / ₂	16 ¹ / ₄	7 ⁷ / ₁₆	4 ⁷ / ₁₆	25 lbs.	4	41480

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear.

Dividers		Dimensions			
Model No.	W	H	D	Pkg. Qty.	Ctn. Qty.
41440	3 ³ / ₁₆	4 ¹ / ₂	1 ¹³ / ₁₆	6	30
41460	5 ²¹ / ₆₄	4 ¹ / ₂	1 ¹³ / ₁₆	6	26
41480	8 ⁸ / ₆₄	4 ¹ / ₂	1 ¹ / ₁₀	6	26



Super Modular Cabinets

storage bins, racks & hanging systems

- Organize your AkroDrawers on specially designed stackable or wall-mountable cabinets
- Units can be safely stacked up to three high
- AkroDrawers fit snugly on each shelf so open top on each AkroDrawer is protected from dust and debris
- Drawers hang securely in place from shelves by sturdy backstop tab
- Ships fully assembled
- 11" cabinets can be mounted to wall (light assembly required for wall mounting)
- Durable powder-coated finish
- Weight capacity:
60 lbs. 18" Modular Cabinets
75 lbs. 24" Modular Cabinets
- Combined stack weight capacity: 100 lbs.
- Colors: Textured Charcoal Gray or Textured Putty



AD1811P62



AD1817CAST



AD2311CAST



Small and Medium Super Modular Cabinets can be mounted on two rails under ProCart. Optional two-rail hanging system (No. 30902) required.



features



For secure stacking, special feet nest into recessed dimples in the top of the cabinets

Super Modular Cabinets 18"W x 11"D x 16-1/2"H

Model Number	Description	Cabinet Color	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers
			L	W	H	D	L	H	
AD1811C AD1811P	Small Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	11	17	4 ¹ / ₂	-
AD1811C62 AD1811P62	Small Cabinet with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11 ¹ / ₂	5 ¹ / ₂	4 ¹ / ₂	11	17	4 ¹ / ₂	9
AD1811C82 AD1811P82	Small Cabinet with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11 ¹ / ₂	8 ¹ / ₂	4 ¹ / ₂	11	17	4 ¹ / ₂	6
AD1811CAST AD1811PAST	Small Cabinet with 31162 and 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			11	17	4 ¹ / ₂	6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

Super Modular Cabinets 23"W x 11"D x 16-1/2"H


Model Number	Description	Cabinet Color	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers
			L	W	H	D	L	H	
AD2311C AD2311P	Medium Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	11	22 ³ / ₄	4 ¹ / ₂	-
AD2311C42 AD2311P42	Medium Cabinet with 31142 AkroDrawers	Textured Charcoal Gray Textured Putty	11 ¹ / ₂	3 ³ / ₄	4 ¹ / ₂	11	22 ³ / ₄	4 ¹ / ₂	18
AD2311C62 AD2311P62	Medium Cabinet with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11 ¹ / ₂	5 ¹ / ₂	4 ¹ / ₂	11	22 ³ / ₄	4 ¹ / ₂	12
AD2311CAST AD2311PAST	Medium Cabinet with 31142 and 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			11	22 ³ / ₄	4 ¹ / ₂	6 / 8

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

Super Modular Cabinets 18"W x 17"D x 16-1/2"H

Model Number	Description	Cabinet Color	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers
			L	W	H	D	L	H	
AD1817C AD1817P	17" Deep Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	17	17	4 ¹ / ₂	-
AD1817C68 AD1817P68	17" Deep Cabinet with 31168 AkroDrawers	Textured Charcoal Gray Textured Putty	17 ¹ / ₂	5 ¹ / ₂	4 ¹ / ₂	17	17	4 ¹ / ₂	9
AD1817C88 AD1817P88	17" Deep Cabinet with 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	17 ¹ / ₂	8 ¹ / ₂	4 ¹ / ₂	17	17	4 ¹ / ₂	6
AD1817CAST AD1817PAST	17" Deep Cabinet with 31168 and 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			17	17	4 ¹ / ₂	6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.



Stackable Cabinets

storage bins, racks & hanging systems

- Increased storage capacity for AkroDrawers by providing more space to organize and color code inventory
- Units can be safely stacked up to three high
- Available in two sizes – one for 12" AkroDrawers and one for 18" AkroDrawers
- Optional 8" high Base Stands for each size cabinet available in matching colors for either cabinet – keeps cabinets off the floor for easier clean-up underneath
- Durable powder-coated finish
- Cabinets ship fully assembled
- Weight capacity: 120 lbs.
- Combined stacked weight capacity: 200 lbs.
- Colors for Stackable Cabinets and optional Base Stands: Textured Charcoal Gray or Textured Putty




features



For secure stacking, special feet nest into recessed dimples in the top of the cabinets



Optional Base Stands provide eight more inches of height for easier, more comfortable access to lower shelves



Stacking a 12" deep cabinet on top of an 18" cabinet provides additional work space for sorting and organizing

Stackable Cabinet 35"W x 11"D x 22"H

Model Number	Description	Cabinet Color	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers
			L	W	H	D	L	H	
AD3511C AD3511P	Stackable Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	11	34	4 ¹ / ₂	-
AD3511C42 AD3511P42	Stackable Cabinet with 31142 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	3%	4%	11	34	4 ¹ / ₂	32
AD3511C62 AD3511P62	Stackable Cabinet with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	5%	4%	11	34	4 ¹ / ₂	24
AD3511C82 AD3511P82	Stackable Cabinet with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	8%	4%	11	34	4 ¹ / ₂	16
AD3511CAST AD3511PAST	Stackable Cabinet with 31142, 31162 & 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			11	34	4 ¹ / ₂	8 / 12 / 4

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

Stackable Cabinet 35"W x 17"D x 22"H

Model Number	Description	Cabinet Color	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers
			L	W	H	D	L	H	
AD3517C AD3517P	Stackable Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	17	34	4 ¹ / ₂	-
AD3517C68 AD3517P68	Stackable Cabinet with 31168 AkroDrawers	Textured Charcoal Gray Textured Putty	17%	5%	4%	17	34	4 ¹ / ₂	24
AD3517C88 AD3517P88	Stackable Cabinet with 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	17%	8%	4%	17	34	4 ¹ / ₂	16
AD3517CAST AD3517PAST	Stackable Cabinet with 31168 & 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			17	34	4 ¹ / ₂	12 / 8

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

Color code: B= Blue, CRY= Crystal Clear, GR=Gray, R=Red, Y=Yellow

Optional Base Stands for Stackable Cabinets Dimensions



Model No.	Description	Base Stand Color	W	D	H
AD3511BS	Base Stand for 11" Stackable Cabinet	Textured Charcoal Gray or Textured Putty	35 ¹ / ₂	11 ¹ / ₂	8
AD3517BS	Base Stand for 17" Stackable Cabinet	Textured Charcoal Gray or Textured Putty	35 ¹ / ₂	17 ¹ / ₂	8




Secure Mini-Cabinets

storage bins, racks & hanging systems



- Lockable cabinet provides secure storage for sensitive supplies
- Accommodates 12" AkroDrawers
- Made from 18-gauge steel
- Wall mountable
- Features standard four adjustable shelves with fully louvered panel built into back for hanging AkroBins®
- Available with a quick-view door to keep contents visible
- Solid door option keeps sensitive contents secure and out of sight
- Foam gasket around door frame seals out dust
- Welded frame and durable powder-coated finish
- Ships fully assembled
- Weight capacity: 350 lbs.
- Colors: Textured Charcoal Gray or Textured Putty

features




Quick-View Door keeps cabinet contents visible



Solid Door option keeps sensitive contents out of sight



Lockable latch rotates and recesses into door when closed for flush look



Louvered back panel extends organizing options



Textured Charcoal Gray



Textured Putty



ACQV4P62



ACS4C



Quick-View Mini-Cabinet 19-1/4"W x 13-1/4"D x 38"H

Model Number	Description	Cabinet Color	L	W	H	Qty. of Drawers
ACQV4C ACQV4P	Secure Mini-Cabinet, Quick-View Door, no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	-
ACQV4C42 ACQV4P42	Secure Mini-Cabinet, Quick-View Door with 31142 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	3%	4%	16
ACQV4C62 ACQV4P62	Secure Mini-Cabinet, Quick-View Door with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	5%	4%	12
ACQV4C82 ACQV4P82	Secure Mini-Cabinet, Quick-View Door with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	8%	4%	8
ACQV4CAST ACQV4PAST	Secure Mini-Cabinet, Quick-View Door with 31142, 31162 & 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			4 / 6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

Steel Door Mini-Cabinet 19-1/4"W x 13-1/4"D x 38"H

Model Number	Description	Cabinet Color	L	W	H	Qty. of Drawers
ACS4C ACS4P	Secure Mini-Cabinet, Steel Door, no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	-
ACS4C42 ACS4P42	Secure Mini-Cabinet, Steel Door with 31142 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	3%	4%	16
ACS4C62 ACS4P62	Secure Mini-Cabinet, Steel Door with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	5%	4%	12
ACS4C82 ACS4P82	Secure Mini-Cabinet, Steel Door with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	8%	4%	8
ACS4CAST ACS4PAST	Secure Mini-Cabinet, Steel Door with 31142, 31162 & 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			4 / 6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

12" & 18" Enclosed Steel Shelving Systems

storage bins, racks & hanging systems



- Steel shelving will accommodate new 12" and 18" AkroDrawers
- Manufactured from high-grade, 22-gauge steel with powder-coated finish
- Can be ordered independently or purchased with AkroDrawers for a complete system
- Closed back and sides keep drawers contained to one side of shelves and further eliminate dust and debris
- Drawers can hang securely in place from shelves by sturdy backstop tab
- Easy to assemble using shelf clips
- Each shelving system can hold up to a maximum of 8,500 lbs.
 - 12" x 36" shelf holds 500 lbs.
 - 18" x 36" shelf holds 550 lbs.
- Color: Gray

Pick Racks



- Angled shelves keep parts and supplies at the front of AkroDrawers for easy access
- Improve workspace organization and efficiency
- 16-gauge steel construction
- Durable powder-coated finish
- Weight capacity: 400 lbs. Single-Sided; Up to 800 lbs. Double-Sided
- Color: Gray



accessories



APRDMOBILE
Mobile Kit
For double-sided
Pick Rack



12" Enclosed Shelving Systems (13 Shelves)

Model Number	Description	Drawer Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers	Drawer Color
			L	W	H	D	L	H		
ASC1279	Shelving (no AkroDrawers)	-	-	-	-	12	36	79	-	-
ASC1279142	Shelving with AkroDrawers	31142	11%	3%	4%	12	36	79	96	R,B,Y,GRY,CRY
ASC1279162	Shelving with AkroDrawers	31162	11%	5%	4%	12	36	79	72	R,B,Y,GRY,CRY
ASC1279182	Shelving with AkroDrawers	31182	11%	8%	4%	12	36	79	48	R,B,Y,GRY,CRY
ASC1279AST	Shelving with AkroDrawer Mix	31142, 31162, 31182	See Above			12	36	79	27 / 36 / 12	R,B,Y,GRY,CRY

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear. Only one color per unit.

18" Enclosed Shelving Systems (13 Shelves)

Model Number	Description	Drawer Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers	Drawer Color
			L	W	H	D	L	H		
ASC1879	Shelving (no AkroDrawers)	-	-	-	-	18	36	79	-	-
ASC1879168	Shelving with AkroDrawers	31168	17%	5%	4%	18	36	79	72	R,B,Y,GRY,CRY
ASC1879188	Shelving with AkroDrawers	31188	17%	8%	4%	18	36	79	48	R,B,Y,GRY,CRY
ASC1879AST	Shelving with AkroDrawer Mix	31168, 31188	See Above			18	36	79	36 / 24	R,B,Y,GRY,CRY

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear. Only one color per unit.

Single-Sided Pick Rack 12" D x 36-3/4" W x 60-1/4" H (8 Shelves)

Model Number	Description	Drawer Model No.	Drawer Dimensions			Qty. of Drawers	Drawer Color
			L	W	H		
APRS142	Rack with AkroDrawers	31142	11%	3%	4%	72	R,B,Y,GRY,CRY
APRS162	Rack with AkroDrawers	31162	11%	5%	4%	48	R,B,Y,GRY,CRY
APRS182	Rack with AkroDrawers	31182	11%	8%	4%	32	R,B,Y,GRY,CRY
APRSAST	Rack with AkroDrawer Mix	31142, 31162, 31182	See Above			18 / 24 / 8	R,B,Y,GRY,CRY

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear. Only one color per unit.

Double-Sided Pick Rack 24" D x 36-3/4" W x 60-1/4" H (16 Shelves)

Model Number	Description	Drawer Model No.	Drawer Dimensions			Qty. of Drawers	Drawer Color
			L	W	H		
APRD142	Rack with AkroDrawers	31142	11%	3%	4%	144	R,B,Y,GRY,CRY
APRD162	Rack with AkroDrawers	31162	11%	5%	4%	96	R,B,Y,GRY,CRY
APRD182	Rack with AkroDrawers	31182	11%	8%	4%	64	R,B,Y,GRY,CRY
APRDAST	Rack with AkroDrawer Mix	31142, 31162, 31182	See Above			36 / 48 / 16	R,B,Y,GRY,CRY

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear. Only one color per unit. Color code: B=Blue, CRY=Crystal Clear, GRY=Gray, R=Red, Y=Yellow. When using the APRD with the mobile kit, weight capacity is 500 lbs.



Indicator Stock, Pick, Flip & Replenish

STOCK the Indicator Bin using the divider to designate volume for the inventory reserve.

PICK from the blue side of the bin until you reach the divider.

FLIP the bin to the orange reserve to indicate inventory levels are low.

REPLENISH the bin and repeat!




- Easy organization of supplies and work-in-process
- Reduces excess inventory
- Width dividers used for orange reserve to prevent stock-outs and assembly line interruptions
- Works with 14" wire shelving, 12" steel shelving or with pick rack systems

Indicator™ Bins – Effective inventory control at a glance!

The Indicator Bin simplifies visual recognition when supplies need to be replenished. An innovative, low-cost alternative to high-end inventory control systems!

Pick Rack Systems




- Available as single-sided or double-sided
- Angled shelves keep parts at the front of bins for easy access
- 16-gauge steel construction
- 400-800 lb. weight cap.
- See page 15 for bin quantity

Steel Shelving Systems




- Manufactured from high-grade, 22-gauge steel with a powder-coated finish
- Easy assembly
- Holds (96) 36442BLUE bins and (60) 36462BLUE bins
- 500 lb. weight capacity per shelf, up to 8,500 lbs.

Wire Shelving Systems



- Constructed from steel with a chrome finish for durability and strength
- Open wire design minimizes dust collection and improves visibility
- Holds (88) 36442BLUE bins and (55) 36462BLUE bins
- 2,000 lb. max. weight capacity per unit

features



Bright orange trigger color used in Lean and 5S initiatives



Innovative double hopper bin can be filled or picked from both sides



Large label area on both sides for part identification or bar code scanning



Rolled ridge provides added strength and durability




Width dividers used for orange reserve to prevent stock-outs and assembly line interruptions

related products

Create the perfect storage system – mix and match your selection of Indicator Bins with compatible products including:

- Pick Racks pg. 15
- Wire Shelving Systems pgs. 36-39
- Steel Shelving Systems pgs. 40-42



Indicator Bins

Outside Dimensions

Inside Bottom Dimensions

	Model No.	Description	L	W	H	L	W	H	Bin Ctn. Qty.	Divider*	Divider Pkg. Qty.
	36442BLUE	Indicator Bin (Blue/Orange)	11 $\frac{1}{2}$ "	4 $\frac{1}{4}$ "	4"	9 $\frac{1}{2}$ "	2 $\frac{9}{16}$ "	3 $\frac{3}{16}$ "	24	40120	24
	36462BLUE	Indicator Bin (Blue/Orange)	11 $\frac{1}{2}$ "	6 $\frac{3}{4}$ "	4"	9 $\frac{1}{2}$ "	5 $\frac{3}{8}$ "	3 $\frac{3}{16}$ "	12	40130	24

*Dividers Sold Separately

* US Patent Pending



Efficient Organization with Customizable Storage

Dividable VantageBin™

- Sturdy bin holds dovetailed dividers to customize compartments
- Fits on standard 24" deep or wide shelving and counters
- Bins nest when empty to conserve storage space
- 24" x 5½" x 7" bin is dividable in up to 10 sections
- Sturdy polypropylene construction
- Available in two colors: White and Gray
- Longer and taller than VantageBin
- 9 divider positions per bin

features




Corner ribs prevent jamming when nested



Rolled rim for added strength and durability



Dovetailed design securely locks dividers in, maintaining bin shape under heavy loads



Molded-in V-grooves on the VantageBin create non-slip surface on inside bottom

VantageBin™

- Molded-in V-groove bottom keeps items upright and prevents them from sliding without dividers
- Bins nest when empty to conserve storage space
- Durable, injection-molded polypropylene construction
- Quick, easy access and identification when organizing envelopes, bags, jewel cases, photographs and more
- Ideal for retail and material handling as well as home and office storage applications
- Available in three colors: White, Gray and Yellow



VantageBin	Model No.	Description	Outside Dimensions Inches			Inside Dimensions Inches				Ctn. Qty.	Dividers/Pk.
			L	W	H	L	W	H	X		
	30420WH16PK	Dividable Bin	24	5½	7	22¾	3½	7	22¾	6	40420/12
	30420GRY6PK	Dividable Bin	24	5½	7	22¾	3½	7	22¾	6	40420/12
	30400YEL10PK	Standard Bin	16¾	7¼	5½	15½	6¾	5½	15½	10	-
	30400WH10PK	Standard Bin	16¾	7¼	5½	15½	6¾	5½	15½	10	-
	30400GRY10PK	Standard Bin	16¾	7¼	5½	15½	6¾	5½	15½	10	-

One color per carton: Specify color when ordering. Order in carton quantities. Weight capacity per bin is 40 lbs.



related products

Organize your VantageBin on:

- Wire Shelving Systems pgs. 36-39
- Steel Shelving Systems pgs. 40-42



1800 Series AkroBins[®], ESD Containers & Economy Bins

storage bins, racks & hanging systems



1800 Series AkroBins

- Strong, durable copolymer polypropylene construction
- Storage systems for large, heavy and bulky items
- One black crosswise divider included per bin
- Color: Beige



ESD Containers

- Akro-Mils ESD containers dissipate electrostatic charges, which can severely damage sensitive electronic components
- Grounding Wire 98100 – Designed to convert existing Akro-Mils rail and hanging systems (see pgs. 8-9). Conducts static charges away from the storage system

accessories



Grounding Wire
98100

Economy Bins

- Versatile Economy Bins make full use of shelf depth on 12" or 18" deep shelving and stack to fill space between shelves
- The only small parts bin that can nest and stack
- Molded from copolymer polypropylene
- Generous opening allows easy access to stacked items

1800 Series

Model No.	Outside Dimensions Inches			Inside Dimensions Inches				Ctn. Qty.	Dividers	Pkg. Qty.	Capacity (lbs.)
	L	W	H	L	W	H	X				
30348BEIGE	20½	8¼	7	20	7¾	6½	20	6	40348 (3)	6	60
30358BEIGE	20½	11	7	20	10½	6½	20	6	40358 (3)	6	75

Available in Beige. Order in carton quantities.

ESDs

Model No.	Outside Dimensions Inches			Inside Dimensions Inches				Cap. on Rack	Ctn. Qty.
	L	W	H	L	W	H	X		
30210ESD	5¾	4¼	3	4¾	3¼	2¼	4	10 lbs.	24
30220ESD	7¾	4¼	3	6¾	3¼	2¼	6	10 lbs.	24
30230ESD	10¾	5½	5	10¼	4¾	4¾	9	30 lbs.	12
30235ESD	10¾	11	5	10¼	10	4¾	9	50 lbs.	6
30240ESD	14¾	8¼	7	14	6¾	6¾	12	60 lbs.	12

Order in carton quantities.


Economy Bins

Model No.	Outside Dimensions Inches			Inside Dimensions Inches			Ctn. Qty.
	L	W	H	L	W	H	
30796BLACK	8¾	6¾	5	6¾	4	4¼	10 each
30716BLACK	11¾	6¾	5	9¾	4	4¼	10 each
30776BLACK	17¾	6¾	7	14¾	3¾	6¼	10 each
30718BLACK	11¾	8¾	5	9	5¾	4¼	8 each
30778BLACK	17¾	8¾	7	14¾	5½	6¼	8 each

Order in carton quantities.



1800 Series AkroBins



ESD Container



Economy Bins



Nests When Empty
 • Saves space in storage areas

Convenient, Efficient Organization in a Single-Piece Six-Bin Unit

- Configured six across in a single unit, 33" wide x 5" high
- Available in 12" or 18" depths to fit standard shelving
- Separate and sort parts to increase efficiency, shorten assembly times and maintain accurate inventories
- A cost-efficient alternative to flimsy, individual cardboard boxes
- Can be safely stacked using a 3/8" wood dowel rod
- Available colors: Blue, Red, Yellow and Green



System Bins shown on Steel Shelving



APRBENCH
 • Holds (3) 30312 System Bins


related products

- System Bins work great with:
- Pick Rack Systems pg. 15
 - Wire Shelving Systems pgs. 36-39
 - Steel Shelving Systems pgs. 40-42

features




Large label area for easy content identification
 Smooth surfaces. Easy to fill, handle and keep clean
 Sturdy interior double wall construction. One-piece, injection-molded for durability
 Wide hopper front allows easy access for quick parts picking

System Bins	Model No.	Description	Dimensions Inches			Bin Compartment Dimensions** Inches			Ctn. Qty.
			L	W	H	L	W	H	
	30312	12" System Bin	12	33	5	10%	3 ¹³ / ₅₀	4 ⁴⁷ / ₅₀	5
	30318	18" System Bin	18	33	5	16%	3 ¹³ / ₅₀	4 ⁹³ / ₁₀₀	5
	40312*	System Bin Divider (Black only)	¼	4%	4%	-	-	-	6 pk.

One color per carton: Specify Red, Blue, Yellow or Green. Order in carton quantities. *One divider per compartment, six per unit. **Inside dimension per compartment.

Shelving Systems	Model No.	Description	Dimensions Inches			
			L	W	H	Bin Qty.
	APRBENCH	Bench Pick Rack	36¾	12	25	‡
	AS1279312	12" Shelving Unit	36	12	79	10*
	AS1879318	18" Shelving Unit	36	18	79	10**

‡Order bins separately. Specify bin color when ordering. *Qty. of 30312 System Bins included. **Qty. of 30318 System Bins included.


Cart Systems	Model No.	Description	Dimensions Inches			
			L	W	H	Bin Qty.
	R5SYT5HR2436	Multi-Shelf Cart (5 shelves)	36	24½	40	10*
	R5SYT8MR2436	Multi-Shelf Cart (5 shelves)	36	24½	43	10*
	R5SYT5HR3636	Multi-Shelf Cart (5 shelves)	36	36½	40	10**
	R5SYT8MR3636	Multi-Shelf Cart (5 shelves)	36	36½	43	10**

Specify bin color when ordering. *Qty. of 30312 System Bins included. **Qty. of 30318 System Bins included.

accessories



System Bin Divider





Easy Flow Gravity Hopper

storage bins, racks & hanging systems

New Size!

A Unique Way to Improve Workflow!

- Unique hopper provides exceptional product storage, while saving space through a compact vertical design
- Large, angled top opening allows easy filling, whether used on the Gravity Hopper Floor Rack or on a work platform
- Generous picking area provides easy access to the loaded product, while keeping it neatly contained and sorted
- Great for: fasteners, assembly areas, kanban, inventory stock, merchandise and work cells
- 31620 – 50 lb. capacity, 31625 – 75 lbs. capacity per hopper
- Rotational-molded for strength and durability – LLDPE
- Allows for proper lot rotation




31620 BLUE




- 31620 – New smaller size option**
- First-In-First-Out (FIFO) sliding divider shelf helps eliminate waste and spoilage of product



31625
(31625 hopper available in Red or Blue)



Gravity Hopper

Model No.	Description	Inches			Load Capacity			Ctn. Qty.
		L	W	H	lbs.	cu. in.	gal.	
 31620	Small Easy Flow Gravity Hopper	16	8 $\frac{1}{4}$	16	50	1400	6	1
31625	Large Easy Flow Gravity Hopper	18	10 $\frac{3}{4}$	19 $\frac{1}{2}$	75	2400	10.39	1

When ordering 31625 specify color Red or Blue. † Sliding divider shelf with 31620 hopper only.

Model No.	Description	Wt. Cap.
31625RACK	Easy Flow Gravity Hopper Rack 36" x 36" x 69"	900 lbs.
30600DOLLY	Easy Flow Gravity Hopper Dolly with 4" x 1.5" Polyolefin Casters	900 lbs.
30600BRACKET	Easy Flow Gravity Hopper Bracket	75 lbs.



- 30600BRACKET**
- Bracket available to attach either size hopper to existing louvered panel


31625RACK Gravity Hopper Floor Rack

- Holds 9 large/12 small Easy Flow Gravity Hoppers per side for maximum efficiency
- 13-gauge steel
- 900 lb. load capacity
- Adjustable rail heights
- Can be mobilized with optional dolly


31625RACK
Shown with 31620 Easy Flow Gravity Hopper Bins

31625RACK
Shown with 31625 Easy Flow Gravity Hopper Bins

features



Large, angled top opening for easy filling



Generous picking area provides easy access to loaded product

- 30600DOLLY**
- Rack can be mobilized with optional dolly
 - Four swivel casters (two with brakes)



30600DOLLY

Super-Size AkroBins®

heavy duty bins, totes, containers & small parts storage

- Large-capacity storage to improve organization
- Molded of high-impact polypropylene and unaffected by weak acids or alkalis
- Sturdy, one-piece construction is water, rust and corrosion-proof
- Guaranteed not to crack or break under normal load conditions as stated in the 1-year limited warranty
- Products made of polypropylene block copolymer are autoclavable up to 250° F
- Available in three vibrant colors – Red, Yellow and Blue

features



Anti-slide stop prevents stacked bins from shifting forward



Easy to carry with large handle molded onto back of bin



Reinforced side ribs add strength and prevent spreading when stacked



Large label area on front of bin



accessories



Window Insert optimizes interior space and keeps contents visible



Lengthwise Dividers keep items separated in the bin

Exclusively from Akro-Mils
Width Dividers
Create Extra Storage!



Widthwise Dividers create extra storage compartments

Super-Size AkroBins

New Ways to Super-Size & Organize

- Provide additional options to efficiently organize large items and improve workflow
- Heavy-duty bins securely stack atop each other or can sit on shelving, carts or dollies



30284 Super-Size AkroBins
23 7/8" x 8 1/4" x 7"



30293
on R216CS2836

30289

30283 on RU843HR2018

30280

30282

30288

30293

New Size!

30284

30287

30290

30286

30292 on RU843TP2227

30281

Super-Size AkroBins	Outside Dimensions Inches			Inside Dimensions Inches				Max. Cap. per Bin	Stacking Cap./= Qty. Stacked	Ctn. Qty.	Width	Length	Dividers*		Accessories		Windows	
	L	W	H	L	W	H	X						Divider Pkg. Qty. W	Qty. L	Windows	Window Pkg. Qty.		
30280	20	12 $\frac{3}{8}$	6	16 $\frac{7}{8}$	10 $\frac{1}{16}$	5 $\frac{3}{8}$	15 $\frac{1}{2}$	200 lbs.	40 lb./10	4	-	40280 (3)	-	2	21280	2		
30281	20	12 $\frac{3}{8}$	8	16 $\frac{7}{8}$	10 $\frac{1}{16}$	7 $\frac{3}{8}$	15 $\frac{1}{2}$	200 lbs.	50 lb./7	3	-	40281 (3)	-	3	21281	3		
30282	20	12 $\frac{3}{8}$	12	16 $\frac{7}{8}$	10 $\frac{1}{16}$	11 $\frac{3}{8}$	15 $\frac{1}{2}$	200 lbs.	60 lb./5	2	-	40282 (3)	-	1	21282	2		
30283	20	18 $\frac{3}{8}$	12	16 $\frac{7}{8}$	16 $\frac{3}{16}$	11 $\frac{3}{8}$	15 $\frac{1}{2}$	300 lbs.	150 lb./5	1	-	40283 (3)	-	1	21283	1		
30284	23 $\frac{3}{8}$	8 $\frac{3}{4}$	7	20 $\frac{7}{8}$	6 $\frac{3}{8}$	6 $\frac{3}{8}$	19 $\frac{1}{2}$	200 lbs.	150 lb./5	4	41284 (2)	40286 (1)	2	4	21284	4		
30286	23 $\frac{3}{8}$	11	7	20 $\frac{7}{8}$	9 $\frac{3}{8}$	6 $\frac{3}{8}$	19 $\frac{1}{2}$	200 lbs.	150 lb./5	4	41286 (2)	40286 (3)	2	4	21286	4		
30287	23 $\frac{3}{8}$	11	10	20 $\frac{3}{4}$	9	9 $\frac{3}{8}$	19 $\frac{1}{2}$	300 lbs.	150 lb./5	4	41287 (2)	40287 (3)	6	6	21287	4		
30288	23 $\frac{3}{8}$	16 $\frac{1}{2}$	11	20 $\frac{3}{4}$	14 $\frac{3}{8}$	10 $\frac{3}{8}$	19 $\frac{1}{2}$	300 lbs.	150 lb./5	1	41288 (2)	40287 (3)	6	6	21288	1		
30289	23 $\frac{3}{8}$	18 $\frac{3}{4}$	12	20 $\frac{3}{4}$	16	11 $\frac{3}{8}$	19 $\frac{1}{4}$	300 lbs.	150 lb./5	1	41289 (2)	40289 (3)	2	1	21289	1		
30290	29 $\frac{1}{4}$	18 $\frac{3}{8}$	12	26 $\frac{1}{8}$	16 $\frac{3}{16}$	11 $\frac{3}{8}$	24 $\frac{3}{4}$	300 lbs.	150 lb./5	1	-	40290 (3)	-	1	21283	1		
30292	29 $\frac{1}{4}$	11	10	26 $\frac{3}{4}$	9	9 $\frac{3}{8}$	25 $\frac{1}{8}$	300 lbs.	150 lb./5	4	41287 (2)	40292 (3)	6	6	21287	4		
30293	29 $\frac{1}{4}$	16 $\frac{1}{2}$	11	26 $\frac{3}{4}$	14 $\frac{3}{8}$	10 $\frac{3}{8}$	25 $\frac{1}{8}$	300 lbs.	150 lb./5	1	41288 (2)	40292 (3)	6	6	21288	1		

One color per carton: Specify Red, Blue, or Yellow. Not recommended to hang on rack or panel systems. Order in carton quantities. * () = Max. # of divider slots per bin.

Super-Size AkroBin Carts

Dimensions Inches

Model No.	Descriptions	L	W	H	Capacity lbs.	No. of Handles	Ctn. Qty.
R214CS1841	Transports six 30283 Bins	41	18	48	900	2	1
R214CS1859	Transports nine 30283 Bins	59	18	48	1350	2	1
R214CS1878	Transports twelve 30283 Bins	78	18	48	1500	2	1
R214CS2841	Transports six 30290 Bins	41	27 $\frac{1}{2}$	48	900	2	1
R214CS2859	Transports nine 30290 Bins	59	27 $\frac{1}{2}$	48	1350	2	1
R214CS2878	Transports twelve 30290 Bins	78	27 $\frac{1}{2}$	48	1500	2	1
R216CS2236	Transports sixteen 30284 Bins, six 30286 Bins, six 30287 Bins, four 30288 Bins	35 $\frac{1}{2}$	22 $\frac{1}{8}$	35	900	1	1
R216CS2836	Transports six 30292 Bins, four 30293 Bins	35 $\frac{1}{2}$	28 $\frac{1}{8}$	35	900	1	1
R216CS2239	Transports four 30289 Bins	35 $\frac{1}{2}$	22 $\frac{1}{8}$	39	900	1	1




Optional security bar available for all sizes. Bins sold separately.

Super-Size AkroBin Dollies

Dimensions Inches

Model No.	Descriptions	L	W	H	Casters	Capacity lbs.	Ctn. Qty.
RU843HR2018	Compatible with Model 30280, 30281, 30282 & 30283 Bins - Fits 1 wide	17 $\frac{1}{16}$	18 $\frac{3}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843HR2918	Compatible with Model 30290 Bins - Fits 1 wide	26 $\frac{1}{16}$	18 $\frac{3}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP2122	Compatible with Model 30286 & 30287 Bins - Fits 2 wide	20 $\frac{7}{8}$	21 $\frac{1}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP2227	Compatible with Model 30292 Bins - Fits 2 wide	21 $\frac{7}{8}$	26 $\frac{7}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP1721	Compatible with Model 30284 Bins - Fits 2 wide Compatible with Model 30288 Bins - Fits 1 wide	16 $\frac{1}{2}$	20 $\frac{7}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP1727	Compatible with Model 30293 Bins - Fits 1 wide	16 $\frac{1}{2}$	26 $\frac{7}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1
RU843TP1821	Compatible with Model 30289 Bins - Fits 1 wide	18 $\frac{1}{2}$	20 $\frac{7}{8}$	4 $\frac{1}{16}$	3" Polyolefin	500	1

Bins sold separately.



products related products

Increase the benefits of your Super-Size AkroBins with:

- Wire Shelving Systems pgs. 36-39
- Steel Shelving Systems pgs. 40-42
- Shelf Cart pg. 47

Window Inserts

Optimize interior space and keep contents visible



Carts & Dollies

AkroBin Carts

Easy organization of bulky parts in 4, 6, 9, 12 and 16 bin configurations!

- Super-Size AkroBins (sold separately) store and organize large, bulky items
- Heavy-duty frames with capacity from 900 - 1,500 lbs.



AkroBin Solid Steel Dollies

Available for efficient parts transport

Stak-N-Store Bins

heavy duty bins, totes, containers & small parts storage

- The perfect way to organize heavy, bulky items
- Bins stack to form tall, stable storage arrangements on floors or standard industrial shelving
- 75 lb. weight capacity
- Color: Gray, Red and Blue
- 13017 is also available in White




features



Large radius corners and curved upper lip add strength



Side ribs add stability when stacked



Wide hopper front allows easy access to bulky items



Large comfort grip handles

related products

Add mobility to your Stak-N-Store Bins with:

- Wire Shelving Systems pgs. 36-39
- Steel Shelving Systems pgs. 40-42
- Solid Steel Dollies pg. 50
- VERSA/Deck pg. 53
- Platform Trucks pgs. 54-57




Secure Stacking


- Stack bins together to form vertical storage and picking systems




Solid Steel Dollies

- Available for efficient, easy load transport



Stak-N-Store Bins	Model No.	Outside Dimensions Inches			Inside Dimensions Inches				Capacity Cu. Ft.	Ctn. Qty.
		L	W	H	L	W	H	X		
	13014	17½	10¾	12½	15%	8	12¼	13½	.98	4
	13017	15¼	19¾	12½	13%	17½	12¼	11½	1.7	3
	13018	17½	16½	12½	15%	13¾	12¼	13½	1.6	2

One color per carton. Specify Red, Blue or Gray. 13017 also available in White. Order in carton quantities.

Steel Dolly	Model No.	Inches			Ctn. Qty.	Capacity	Casters	Bin Compatibility
		L	W	H				
	RU843HR1617	16¾	15¾	4½	1	900 lbs.	3" Polyolefin	13018
	RU843HR1519	19¼	14¾	4½	1	900 lbs.	3" Polyolefin	13017




Nest & Stack Totes

heavy duty bins, totes, containers & small parts storage

- Extremely durable industrial-grade totes
- Ideal for shipping, transfer and storage applications
- NSTs stack with or without lids for storage and shipping, nest when empty
- Strong, high impact polypropylene will not rust, corrode or bend out of shape even when fully loaded
- Heavy-duty construction provides a longer service life resulting in lower replacement costs than other “budget-priced” totes
- Easy to clean, smooth surfaces are resistant to most solvents and chemicals
- NSTs are manufactured from FDA-sanctioned materials
- Optional lids protect contents from dust and damage
- Available in 9 sizes and 3 colors: Red, Blue and Gray



features



Smooth surfaces are easy to clean



Comfortable grip makes handling easy



Textured bottoms provide a no-slip grip on conveyor belts



Ribs under the lip will prevent jamming when nested

products related products

Add mobility to your Nest & Stack Totes with:

- Carts pgs. 45-47
- Dollies..... pgs. 49-50
- Wire Shelving Systems pgs. 36-39



Dollies


- Available to transport containers – see pgs. 49-50



accessories





Clear Plastic Label Holders attach easily to NSTs, with or without the lid in place. Holders accommodate labels up to 3¾" x 5"



Lids snap tight to protect contents. See lids chart for matching lid size below

Label Holders

Model No.	Pkg. Qty.	Label Size (In.)
35010	6	3¾ x 5
35011	6	3 x 5



Nest & Stack Totes (NSTs)	Outside Dimensions Inches				Inside Dimensions Inches					NST Ctn. Qty.	Cu. Ft.	Lid Model	Ctn. Qty.
	Model No.	L	W	H	A	B	C	D	E				
35180	18	11	6	10	16	15¼	9%	5%	6	0.5	35181	6	
35185	18	11	9	10	16	15%	9%	8%	6	0.76	35181	6	
35190	19½	15½	10	14½	17	16	13¼	9%	6	1.2	35191	6	
35195	19½	15½	13	14½	17	15%	13%	12%	6	1.7	35191	6	
35200	19½	13½	8	12%	17½	16%	11½	7%	6	0.8	35201	6	
35225	23½	19½	10	18¼	20%	19%	16%	9%	3	2	35231	3	
35230	23½	19½	13	18%	20%	19½	16%	12%	3	2.6	35231	3	
35240*	23½	15½	12	14¼	20%	19%	13	11%	3	1.7	35241	3	
35300*	29½	19½	15	18¼	26%	25%	16%	14%	3	3.7	35301	3	

One color per carton. Specify color: Red, Blue or Gray. Order in carton quantities. *Made of HDPE polyethylene.

Akro-Grids

heavy duty bins, totes, containers & small parts storage

- Versatile work-in-process transfer containers
- Dividers allow subdivision of the containers down to a 1½" square compartment size
- Injection-molded from polypropylene block copolymer
- Resists most solvents and chemicals
- Compatible with most racks, shelving and automated material handling equipment
- Dividers, lids and label holders sold separately
- Available in 8 sizes and 3 colors: Red, Blue and Gray



features



Divider slots allow you to create hundreds of different compartment sizes



Strong stacking rims and external ribbing provide added strength

accessories



Dividers allow subdivision of the containers down to a 1½" square compartment size. Color: Black



Clear Plastic Label Holders snap securely on any side of the container



Clear Plastic Covers keep contents clean yet visible. Molded corner guides provide secure stacking



Akro-Grids	Outside Dimensions Inches			Inside Dimensions Inches					Capacity			Accessories		Pkg. Qty.
	Model No.	L	W	H	A	B	C	D	E	Ctn. Qty.	Cu. Ft.	Lbs.	Long Divider*	
33105	10½	8¼	5	6½	9½	9½	6½	4½	20	.16	25	42105 (5)	41105 (7)	6
33164	16½	10½	4	9½	14½	14½	9½	3½	12	.29	20	42164 (7)	41164 (11)	6
33166	16½	10½	6	9½	14½	14½	9½	5½	8	.44	35	42166 (7)	41166 (11)	6
33168	16½	10½	8	9½	14½	14½	9½	7½	6	.59	40	42168 (7)	41168 (11)	6
33220	22½	17½	10	15¼	20½	19½	14½	9½	2	1.66	50	42220 (11)	41220 (15)	6
33224	22½	17½	4	15¼	20½	20	15	3½	6	.61	30	42224 (11)	41224 (15)	6
33226	22½	17½	6	15¼	20½	19½	14½	5½	4	.96	40	42226 (11)	41226 (15)	6
33228	22½	17½	8	15¼	20½	19½	14½	7½	3	1.30	50	42228 (11)	41228 (15)	6


One color per carton. Specify Red, Blue or Gray. Order in carton quantities. *() = max # of dividers.

Clear Plastic Covers

Model No.	Fits Grid No.	Ctn. Qty.
33101	33105	10
33161	33166, 33168, 33164	4
33221	33228, 33220, 33226, 33224	3

Label Holders

Model No.	Description	Pkg. Qty.
35010	Fits all Akro-Grids except 33164 and 33224	6
35011	Fits grids No. 33164, 33224	6



Dollies

- Available to transport containers. See pgs. 49-50



Attached Lid Containers

heavy duty bins, totes, containers & small parts storage



features



Textured bottoms provide a sure grip on conveyor belts



Strong molded-in handle grips are ergonomically designed for easy lifting and carrying




Padlock eye on both ends accommodates security ties



Reinforced hinge pins for years of smooth lid operation

- ALCs stack and nest for optimal space use
- Reusable shipping, distribution, order picking, and storage containers
- Attached lids snap securely closed to protect contents from dust or damage
- Containers interwork for easy pallet loading
- See chart below for color options



Attached Lid Containers

- Models 39160, 39175 and 39280 are available in gray only

ALCs Model No.	Available Colors	Outside Dimensions Inches			Inside Dimensions Top Inches			Inside Dimensions Bottom Inches		Capacity				
		L	W	H	L	W	H	L	W	Cu. Ft.	Gal.	Lbs.	Ctn. Qty.	Stack Cap./Qty. Stacked
39085	Blue, Gray	21½	15	9	19¾	14½	8%	18⅞	13¼	1.12	8.5	35	6	35 lbs./5
39120	Blue, Green, Red, Gray	21½	15	12½	19¾	14½	12	18⅞	13¼	1.62	12	65	6	65 lbs./5
39160	Gray	27	17	12½	25	15½	11	23½	14	2.25	16.83	100	1	100 lbs./4
39170	Blue, Gray	21½	15	17	19¾	14½	16%	18⅞	13¼	2.28	17	100	3	100 lbs./3
39175	Gray	24	19½	12½	22	18	11	20½	16½	2.3	17.20	80	1	80 lbs./5
39280	Gray	28	21	15½	26	19	14	25	18	3.82	28.57	100	1	100 lbs./4

Order in carton quantities. Specify color when ordering.

Dollies

- Plastic, steel and wood dollies available to transport containers. See pgs. 49-50



Straight Wall Containers

heavy duty bins, totes, containers & small parts storage

- SWCs are reusable shipping, storage, and work-in-process containers
- Straight walls provide efficient internal and external space usage
- Solid-sided containers have smooth inner walls for easy, sanitary cleaning
- Mesh-sided containers allow hot or cold air ventilation
- Injection-molded from high-density polyethylene
- Available in 4 sizes and 3 styles
- Color: Gray




3 Styles Per Size:
Solid, mesh and combinations



features




One-inch wall thickness for secure stacking



Strong, 1" wide, stacking rims and external ribbing provide added strength



Straight walls provide efficient cubing in trucks and on pallets



Open .72 x .90 mesh pattern allows high visibility and good airflow

related products

Add more productivity to your Straight Wall Containers with:

- Carts pgs. 45-47
- Dollies..... pgs. 49-50
- Platform Trucks..... pgs. 54-57




Dollies

- Plastic, steel and wood dollies available to transport containers. See pgs. 49-50

Straight Wall Containers (SWCs)

Straight Wall Containers (SWCs)			Outside Dimensions Inches			Inside Dimensions Top Inches			Stacking Capacity / Qty. Bottom Type		
Model No. Mesh Side & Base	Model No. Mesh Side/Solid Base	Model No. Solid Side & Base	L	W	H	L	W	H	Ctn. Qty.	Solid	Mesh
37208	37278	37288	15¾	11¾	8¼	14¼	10¼	8	12	83 lbs./6	30 lbs./6
37608	37678	37688	23¾	15¾	8¼	22¼	14¼	8	4	83 lbs./6	45 lbs./6
37612	37672	37682	23¾	15¾	12¼	22¼	14¼	12	3	125 lbs./5	45 lbs./5
37616	37676	37686	23¾	15¾	16¾	22¼	14¼	16	2	150 lbs./4	45 lbs./4

Order in carton quantities.





Cross-Stack Akro-Tub

heavy duty bins, totes, containers & small parts storage

- Ideal for food processing and handling operations or industrial work-in-progress activities
- Industrial-grade 90° nest and stack tub
- Nesting when empty conserves storage space
- Molded-in side handles for comfortable lifting
- Manufactured from FDA-sanctioned materials
- Smooth surface is easy to clean
- Compatible with standard 36" shelving and conveyor systems
- Color: Gray



features

cross-stack akro-tub features



Stacking grooves allow stable 90° stacks



Molded-in handles for easy lifting



Extra-thick walls and reinforcing ribs provide superior strength



Akro-Tub & Rack

- Heavy-duty, industrial-grade nesting tub
- Tub manufactured from FDA-sanctioned materials
- Smooth surface is easy to clean
- Nests when empty to conserve storage space
- Use the Akro-Tub Rack (RA6TR4MR) to provide easy loading and transport of multiple Akro-Tubs
- 75 lb. capacity per tub
- Color: Gray




features

akro-tub features




Rounded corner design adds strength to stress points




Rolled top rim forms comfortable handles



Extra-thick walls for superior strength



Ribs prevent jamming when nested

Cross-Stack Akro-Tub	Outside Dimensions Inches							
	Model No.	L	W	H	A	B	Capacity Gal.	Ctn. Qty.
	34301	17¼	11	8	13¼	7¼	3.85	6
	34302	17¼	11	12	12½	7	5.51	6
	34303	23¾	17¼	8	19¾	14	9.81	6
	34304	23¾	17¼	12	19	13¼	14.38	6

Order in carton quantities.

Double-Sided Cross-Stack Akro-Tub Rack		Inches			
Model No.	Description	L	W	H	Rack Weight/lbs.
RACR5MR	Holds 32 (34301) Cross-Stack Akro-Tubs* or 16 (34303) Cross-Stack Akro-Tubs*	53	29	62	1000 lbs.

Order in carton quantities. *Tubs sold separately.

Akro-Tub		Inches					
Model No.	L	W	H	A	B	Capacity Gal.	Ctn. Qty.
34240	19	24½	9½	20½	15½	14.6	6

Order in carton quantities.

Akro-Tub Rack		Inches			Casters
Model No.	H	W	D		
RA6TR4MR	73	24	24	4" x 2" Mold-On Rubber: 2 Rigid, 2 Swivel	



Double-Sided Cross-Stack Tub Rack

- Holds 32 (34301) or 16 (34303) Cross-Stack Akro-Tubs*



Akro-Tub Rack

- Holds 6 Akro-Tubs on angle-iron slides for up to 600 lb. total capacity. Welded steel frame with 12-gauge base and bolted-on casters.*

*Akro-Tubs sold separately.



Steel Storage Cabinets

heavy duty bins, totes, containers & small parts storage

19-Series Heavy-Duty Cabinets

- Frame: 17" W x 11" D x 11" H with five different drawer sizes
- 2 dividers per drawer
- Color Code – make visual reference simple & quick
- Molded-in label holder
- Transparent window for content identification
- Rear stop tabs prevent spills
- Two cabinets fit side-by-side on 36" wide shelving



19228 – 28 Drawers

- Frame: 17" W x 11" H x 11" D
- Drawer: 2 $\frac{3}{16}$ " W x 2 $\frac{1}{4}$ " H x 10 $\frac{1}{16}$ " D



19320 – 20 Drawers

- Frame: 17" W x 11" H x 11" D
- Drawer: 3 $\frac{1}{16}$ " W x 2 $\frac{1}{4}$ " H x 10 $\frac{1}{16}$ " D



19416 – 16 Drawers

- Frame: 17" W x 11" H x 11" D
- Drawer: 4 $\frac{3}{16}$ " W x 2 $\frac{1}{4}$ " H x 10 $\frac{1}{16}$ " D



19-Series Drawers

- Available separately for a variety of uses
- Now available in 5 colors and 5 sizes!
- Made of high-impact polystyrene
- Drawers can be divided into as many as 8 compartments with dovetailed dividers, for customized storage



19715 – 15 Drawers

- Frame: 17" W x 11" H x 11" D
- Drawer: 3 $\frac{1}{16}$ " W x 3 $\frac{3}{16}$ " H x 10 $\frac{1}{16}$ " D



19909 – 9 Drawers


- Frame: 17" W x 11" H x 11" D
- Drawer: 5 $\frac{1}{16}$ " W x 3 $\frac{3}{16}$ " H x 10 $\frac{1}{16}$ " D



19109 – 9 Drawers

- Frame: 17" W x 11" H x 11" D
- Drawer: 5 $\frac{1}{16}$ " W x 3 $\frac{3}{16}$ " H x 10 $\frac{1}{16}$ " D

Dovetail dividers lock dividers securely in place



Storage Cabinets Hanging & Rotary Systems




98325 Storage-Go-Round

- Access up to 20 cabinets and as many as 560 drawers in less than 1 square yard of floor space
- Holds up to 1,000 lbs. of parts
- Accommodates models 19228, 19320, 19416, 19715 and 19909
- Swing diameter 43 $\frac{3}{16}$ "



30638 Louvered Rack

- Holds up to 5 cabinets
- Max. 250 lbs.



30661 Louvered Rack

- Holds up to 10 cabinets
- Max. 500 lbs.



30016 Double-Sided Rail Rack

- Mix or match up to 12 cabinets
- Supports up to 500 lbs.
- Optional Mobile Kit available (shown in picture)



Mobile Kit 30424

- Rack can be mobilized with the optional mobile kit

98400 Suspension Straps

- Secure cabinets to rail rack with optional suspension straps

19-Series features



Heavy-duty welded-steel frame with durable powder-coated finish



Label holder and transparent window for content identification



Strong, high-impact polystyrene drawers



Steel Storage Cabinets

heavy duty bins, totes, containers & small parts storage

19-Series Heavy-Duty Steel Cabinets

Model No.	Description	Drawers per Cabinet	Inside Drawer Dimensions (In.)			Ctn. Qty.	Drawers	Dividers
			W	H	D			
19228	Steel Storage Cabinet*	28	2 ³ / ₁₆	2 ¹ / ₁₆	10 ⁹ / ₁₆	1	20228	40228
19320	Steel Storage Cabinet*	20	3 ³ / ₁₆	2 ¹ / ₁₆	10 ⁹ / ₁₆	1	20320	40320
19416	Steel Storage Cabinet*	16	4	2 ¹ / ₈	10 ⁹ / ₁₆	1	20416	40416
19715	Steel Storage Cabinet*	15	3 ³ / ₁₆	3 ³ / ₁₆	10 ⁹ / ₁₆	1	20715	40715
19909	Steel Storage Cabinet*	9	5 ³ / ₁₆	3 ³ / ₁₆	10 ⁹ / ₁₆	1	20909	40909
19109 [‡]	Steel Storage Cabinet w/ Locking Door	9	5 ³ / ₁₆	3 ³ / ₁₆	10 ⁹ / ₁₆	1	20909	40909

One drawer color per cabinet: Specify Red, Blue, Yellow, Gray or Black when ordering. Two removable dividers and one label per drawer included.

* Available with a locking door when ordered in quantities of 50 or more. ‡ Not available with colored drawers.

Storage-Go-Round

Assembled Dimensions (In.)

Model No.	Description	L	W	H	Compatible with Models*
98325	Storage-Go-Round with turntable base	31	31	60	19228, 19320, 19416, 19715, 19909

Assembly required. * 19-Series Cabinets sold separately.

Mobile Steel Cabinet Rack & Accessories

Model No.	Description
30016	Double-Sided Rail Rack – 36" W x 24" D x 57" H
30424	Mobile Kit
98400	Suspension Straps (Set of 2)**

Assembly required. † Mix or Match 19-Series Steel Cabinet packages. See chart above. **98400 suspension straps required for hanging. Two straps per cabinet needed to secure cabinet to rack.

Louvered Hanging Systems

Rack Dimensions (In.)

Model No.	Description	L	W	H	Compatible with Models*
30638	Louvered Rack Single-Sided	18	13 ¹ / ₂	66 ³ / ₈	19228, 19320, 19416, 19715, 19909, 19109
30661	Louvered Rack Single-Sided	36 ³ / ₈	13 ¹ / ₂	66 ³ / ₈	19228, 19320, 19416, 19715, 19909, 19109

Easy one-person assembly required. † 19-Series Cabinets sold separately. Specify Red, Blue, Yellow, Gray or Black when ordering. **98400 suspension straps required for hanging. Two straps per cabinet needed to secure cabinet to rack.



Light-Duty Steel Storage Cabinets



17-Series Light-Duty Cabinet

- Durable steel frame
- Removable drawers are rust, corrosion and dent-proof

17-Series Light-Duty Steel Cabinet

Drawer Dimensions (In.)

Model No.	Description	Drawers Per Cabinet [‡]	W	H	D	Ctn. Qty.	Drawer Model No.	Dividers 25/Pkg. Model No.
17018	Storage Cabinet*	18	2 ³ / ₄	2 ¹ / ₂	5 ³ / ₄	1	20902	40901

‡ One removable divider and one label per drawer included. * Available with a locking door when ordered in quantities of 50 or more.

17018 – 18 Drawers

- Frame: 18" W x 6" D x 9¹/₂" H
- Drawer depth 5³/₄"



Plastic Storage Cabinets

- Strong plastic cabinets organize and protect components
- A variety of drawer configurations provide versatile storage solutions
- Cabinets stack securely and are wall mountable
- Dividers included

Frame Dimensions (In.)

Model No.	Description	W	H	D	Ctn. Qty.
10116	16-Drawer Cabinet	10 ⁹ / ₁₆	8 ¹ / ₂	6 ³ / ₈	1
10124	24-Drawer Cabinet	20	15 ¹ / ₁₆	6 ³ / ₈	1
10126	26-Drawer Cabinet	20	10 ¹ / ₃₂	6 ³ / ₈	1
10144	44-Drawer Cabinet	20	15 ¹ / ₁₆	6 ³ / ₈	1
10164	64-Drawer Cabinet	20	15 ¹ / ₁₆	6 ³ / ₈	1

16-Drawer Cabinet has 8 dividers. All other cabinets have 8 small and 4 large dividers.



10116 – 16 Drawers

- Frame: 10⁹/₁₆" W x 8¹/₂" H x 6³/₈" D



10124 – 24 Drawers

- Frame: 20" W x 15¹/₁₆" H x 6³/₈" D



10126 – 26 Drawers

- Frame: 20" W x 10¹/₃₂" H x 6³/₈" D



10144 – 44 Drawers

- Frame: 20" W x 15¹/₁₆" H x 6³/₈" D



10164 – 64 Drawers

- Frame: 20" W x 15¹/₁₆" H x 6³/₈" D

features storage cabinet features



Frame back interlocks into face



Flexible, strong, see-through drawers with finger grip drawer pulls



Rugged, high-impact polystyrene frame

Additional Dividers (Plastic Cabinets)

Model No.	Description
40716	16-Pack additional dividers for small drawers
40717	6-Pack additional dividers for large drawers




Storage Cases

heavy duty bins, totes, containers & small parts storage

- Grid design in lid keeps items from spilling into other compartments
- Cases available in 3 sizes with different divider configurations
- Small and medium cases include 4 front-to-back adjustable dividers
- Large cases include 5 front-to-back adjustable dividers
- Clarified polypropylene for durability




Small & Medium Cases




2 Fixed Dividers
4 Adjustable Dividers

Medium Cases



2 Fixed Dividers
4 Adjustable Dividers

Large Cases




2 Fixed Dividers
5 Adjustable Dividers




Portable Organizers



- Unique design keeps parts and equipment from migrating to other compartments when lids are shut
- Separate lid compartment holds small items
- The main compartment holds larger, bulky items
- Dividers included for both levels
- Molded-in "feet" allow case to stand upright



Roto-Shelf



- Mobile storage unit can easily be moved to different work areas, ideal for assembly components
- 19% wide unit takes up very little floor space
- 3 shelves rotate on an independent central metal shaft
- Shelf depth – 2 1/2", Shelf diameter – 19%", 75 lbs. per shelf, 300 lb. total wt. capacity



Tote Caddy



- Hand-held tool and supply caddy
- Deep compartments hold loose parts, cleaning supplies or tools for easy transport
- Molded of heavy-duty, industrial-grade polypropylene for lasting durability
- Color: Blue

Storage Cases

Dimensions Inches

Model No.	Description	L	W	H	Max. Compartments	Ctn. Qty.
05705	Small Case – 2 Fixed Dividers	8%	5%	1%	15	12
05805	Medium Case – 2 Fixed Dividers	11	7	2%	15	6
05905	Large Case – 2 Fixed Dividers	14%	9 1/2	2 1/2	18	6

Order in carton quantities.

Portable Organizers

Inches

Model No.	Description	L	W	H	Max. Compartments	Ctn. Qty.
06115	Lid Storage Organizer	15	11 3/8	3 3/4	11 to 46	1
06118	Large Lid Storage Organizer	18 3/4	13 3/8	3 3/8	12 to 62	1
06217	Flat Bottom Organizer	11 1/8	15	3 3/8	9 to 32	6

Order in carton quantities.

Roto-Shelf

Inches

Model No.	Description	D	H	Ctn. Qty.
02420	Roto Shelf	19%	37 1/2	1

Tote Caddy

Inches

Model No.	Description	L	W	H	Ctn. Qty.
09185BLUE	Tote Caddy	13%	18%	9	6

Order in carton quantities





Wire Shelving Systems


shelving systems & cabinets

- More than 50 system options for bin and shelf configurations!
- Six customizable shelf sizes available: 14" x 36", 18" x 36", 24" x 36", 18" x 48", 24" x 48" and 24" x 60"
- Wide variety of heights and styles: 63" upright with casters and 74" upright stand alone to fit all locations
- Open wire design minimizes dust collection and improves visibility for stored contents
- NSF approved
- Stationary units hold a maximum of 2,000 lbs.
- Mobile units with casters have a maximum load capacity of 900 lbs.
- Max. weight capacity per shelf:
 - 48" or shorter = 800 lbs.
 - Longer than 48" = 600 lbs.




Make organization Easy and more Efficient

- Build complete work cell systems
- Constructed from steel with a chrome finish for durability and strength
- Works with a variety of Akro-Mils storage products to organize parts or products and increase workspace efficiency
- Streamlines workflow and order picking



Frames
Lightweight yet strong metal framework secures the shelving in place



Shelves
Adjustable to hold many Akro-Mils storage and organization products



Quick-Adjust Clips
Clips lock into the frame trunk, and unlock to adjust shelves



Leveling Bolts
Screws securely into uprights to level shelf system on uneven surfaces



Easy Set-up
Durable, versatile Wire Shelving allows quick, one-person set-up and installation

Create Easy, Durable Storage & Organization with Custom Wire Shelving Packages!


AkroBin® Wire Systems



Shorten Assembly Times

- Three sizes allow for a wide variety of Bin and Shelf configurations
- Durable AkroBins feature a curved-bottom hopper front, making it easy to retrieve small parts
- AkroBins, pgs. 4-6

Indicator™ Wire Systems



Shorten Assembly Times

- Effective inventory at a glance
- Holds (88) 36442BLUE bins and (55) 36462BLUE bins
- 2,000 lb. max. weight capacity per unit
- Indicator Bins, pg. 21

System Bin™ Wire Systems



Speed Set-Up & Organization

- Available with 11 Shelves
- Holds 10 System Bins
- Quickly organize with System Bins: one-piece, six-bin units
- System Bins, pg. 24

Stak-N-Store Wire Systems



Maximize Space Utilization

- Available with 5 Shelves
- Configure for 6, 8, 9 or 12 Bins
- Bins feature a wide hopper front for easy access – ideal for bulky items
- Stak-N-Store Bins, pg. 28

Shelf Bin Wire Systems



Sort Parts to Improve Efficiency

- Available with 12 Shelves
- Configure for 36, 48, 60 or 96 Bins
- Strong, polypropylene Shelf Bins outlast corrugated bins
- Shelf Bins, pgs. 12-14

Akro-Grid Wire Systems



Improve Productivity

- Available with 7, 9 or 12 Shelves
- Configure for 24 or 36 Akro-Grids
- Versatile, work-in-process containers with optional dividers for compartments
- Akro-Grids, pg. 30

Nest & Stack Wire Systems



Simplify Workflow

- Available with 4 or 9 Shelves
- Configure for 12 or 36 Nest & Stack Totes
- Industrial-grade totes are ideal for transfer applications. Optional tote lids protect contents from dust. Label Holders allow quick content ID
- Nest & Stack Totes, pg. 29

Straight Wall Container Wire Systems



Optimize Floor Space

- Configured with 6 Shelves
- Holds 12 Straight Wall Containers
- Containers available with smooth, solid sides or an open mesh pattern for high visibility and airflow
- Straight Wall Containers, pg. 32

VantageBin™ Wire Systems



Boost Organization

- Available with 11 Shelves
- Configure for 40 or 42 VantageBins
- Sturdy, functional bin customizable with up to 10 compartments to fit unique sizes of products
- VantageBins, pg. 22

Akro-Tub Wire Systems



Improve Inventory Control

- Available with 4 or 7 Shelves
- Configure for 12 or 24 Akro-Tubs
- Akro-Tubs feature extra-thick walls for strength. Rolled rims form comfortable handles
- Akro-Tubs, pg. 33

24" Super-Size AkroBin® Wire Systems



Increase Storage Capacity

- Available with 3, 4 or 5 shelves that are 24" deep
- Combine with stackable 24" Super-Size AkroBins to optimize spacing between shelves
- Super-Size AkroBins, pgs. 26-27

ShelfMax™ Wire Systems



6" Bins Maximize Storage Capacity

- Available with 8 Shelves
- Configure for 64 or 40 Bins
- 7 Bin Sizes & 5 Colors
- ShelfMax Bins, pg. 13



Wire Shelving Systems

shelving systems & cabinets



AkroBin® Wire Systems

Model Number	Description	AkroBin Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS143630320	Wire Shelving w/ 30320 Bins	B, R, Y, G, S, B	8¾	33	6	14	36	74	20	11
AWS143630240	Wire Shelving w/ 30240 Bins	B, R, Y, G, S, B, SC	14¾	8¼	7	14	36	74	36	4
AWS143630250	Wire Shelving w/ 30250 Bins	B, R, Y, G, S, B, SC	14¾	16½	7	14	36	74	18	4
AWS184830260	Wire Shelving w/ 30260 Bins	B, R, Y, G, S, B, SC	18	11	10	18	48	74	24	6
AWS183630265	Wire Shelving w/ 30265 Bins	B, R, Y, G, S, B, SC	18	8¼	9	18	36	74	18	5
AWS183630270	Wire Shelving w/ 30270 Bins	B, R, Y, G, S, B, SC	18	16½	11	18	36	74	9	5
AWS2460M30358	Mobile Wire Shelving w/ 30358 Bins	BEIGE	20½	11	7	24	60	68	30	6

Bin color code: R=Red, B=Blue, Y=Yellow, G=Green, W=White, GRY=Gray, S=Stone, B=Black, SC=Semi-Clear. Specify one bin color when ordering.



System Bin Wire Systems

Model Number	Description	System Bin Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS143630312	Wire Shelving w/ 30312 Bins	B, R, Y, G	33	12	5	14	36	74	10	11
AWS183630318	Wire Shelving w/ 30318 Bins	B, R, Y, G	33	18	5	18	36	74	10	11

Bin color code: R=Red, B=Blue, Y=Yellow, G=Green. Specify one bin color when ordering.



Stak-N-Store Wire Systems

Model Number	Description	Stak-N-Store Bin Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS184813017	Wire Shelving w/ 13017 Bins	GRY, R, B, W	15½	19¾	12¼	18	48	74	9	5
AWS183613014	Wire Shelving w/ 13014 Bins	GRY, R, B	17½	10¾	12½	18	36	74	12	5
AWS183613018	Wire Shelving w/ 13018 Bins	GRY, R, B	17½	16½	12½	18	36	74	8	5
AWS18365NS	Wire Shelving w/ 13014 & 13017* Bins	GRY, R, B	See Above			18	36	74	6/6	5

*13017 also available in White. Bin color code: R=Red, B=Blue, W=White, GRY=Gray. Specify one bin color when ordering.



Shelf Bin Wire Systems

Model Number	Description	Shelf Bin Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS143630120	Wire Shelving w/ 30120 Bins	B, R, Y, G, W	11¾	4¾	4	14	36	74	96	12
AWS143630130	Wire Shelving w/ 30130 Bins	B, R, Y, G, W	11¾	6¾	4	14	36	74	60	12
AWS143630150	Wire Shelving w/ 30150 Bins	B, R, Y, G, W	11¾	8¾	4	14	36	74	48	12
AWS143630170	Wire Shelving w/ 30170 Bins	B, R, Y, G, W	11¾	11¾	4	14	36	74	36	12
AWS183630128	Wire Shelving w/ 30128 Bins	B, R, Y, G, W	17¾	4¾	4	18	36	74	96	12
AWS183630138	Wire Shelving w/ 30138 Bins	B, R, Y, G, W	17¾	6¾	4	18	36	74	60	12
AWS183630158	Wire Shelving w/ 30158 Bins	B, R, Y, G, W	17¾	8¾	4	18	36	74	48	12
AWS183630178	Wire Shelving w/ 30178 Bins	B, R, Y, G, W	17¾	11¾	4	18	36	74	36	12
AWS244830124	Wire Shelving w/ 30124 Bins	B, R, Y, G, W	23¾	4¾	4	24	48	74	96	12
AWS244830164	Wire Shelving w/ 30164 Bins	B, R, Y, G, W	23¾	6¾	4	24	48	74	60	12
AWS244830184	Wire Shelving w/ 30184 Bins	B, R, Y, G, W	23¾	8¾	4	24	48	74	48	12
AWS244830174	Wire Shelving w/ 30174 Bins	B, R, Y, G, W	23¾	11¾	4	24	48	74	36	12


Bin color code: R=Red, B=Blue, Y=Yellow, G=Green, W=White. Specify one bin color when ordering.



Akro-Grid Wire Systems

Model Number	Description	Akro-Grid Tote Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS183633166	Wire Shelving w/ 33166 Grids	B, R, GRY	16½	10¾	6	18	36	74	36	9
AWS183633168	Wire Shelving w/ 33168 Grids	B, R, GRY	16½	10¾	8	18	36	74	24	7
AWS2460M33224	Mobile Wire Shelving w/ 33224 Grids	B, R, GRY	22¾	17¾	4	24	60	68	36	12

Bin color code: R=Red, B=Blue, GRY=Gray. Specify one bin color when ordering.



Indicator™ Wire Systems

Model Number	Description	Indicator Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS143636442B	Wire Shelving w/ 36442 Indicator Bins	Blue/Orange	11¾	4¾	4	14	36	74	96*	11
AWS143636462B	Wire Shelving w/ 36462 Indicator Bins	Blue/Orange	11¾	6¾	4	14	36	74	60*	11


*Bonus Bins Included





Wire Shelving Systems

shelving systems & cabinets



NEW
Sizes!



NEW
Sizes!

Nest & Stack Wire Systems

Model Number	Description	Nest & Stack Tote Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS183635180	Wire Shelving w/ 35180 Totes	B, R, GRY	18	11	6	18	36	74	36	9
AWS246035225	Wire Shelving w/ 35225 Totes	B, R, GRY	23½	19½	10	24	60	74	12	4

Lids sold separately. Bin color code: R=Red, B=Blue, GRY=Gray. Specify one bin color when ordering.

Straight Wall Container Wire Systems

Model Number	Description	Container Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS244837608	Wire Shelving w/ 37608 Containers	GRY	23¾	15¾	8¼	24	48	74	12	6

VantageBin™ Wire Systems

Model Number	Description	VantageBin Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS183630400	Wire Shelving w/ 30400 Bins	GRY, Y, W	16¾	7¼	5¾	18	36	74	40	11
AWS244830420	Wire Shelving w/ 30420 Bins	GRY, W	24	5½	7	24	48	74	40	11

Bin color code: Y=Yellow, W=White, GRY=Gray. Specify one bin color when ordering.

Akro-Tub Wire Systems

Model Number	Description	Akro-Tub Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS1836M34301	Mobile Wire Shelving w/ 34301 Tubs	GRY	17½	11	8	18	36	68	21	7
AWS2460M34240	Mobile Wire Shelving w/ 34240 Tubs	GRY	19	24½	9½	24	60	68	12	4

Super-Size AkroBin® Wire Systems

Model Number	Description	Super-Size AkroBin Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS184830280	Wire Shelving w/ 30280 Bins	R, B, Y	20	12¾	6	18	48	74	24	9
AWS184830281	Wire Shelving w/ 30281 Bins	R, B, Y	20	12¾	8	18	48	74	18	7
AWS184830282	Wire Shelving w/ 30282 Bins	R, B, Y	20	12¾	12	18	48	74	12	5
AWS184830283	Wire Shelving w/ 30283 Bins	R, B, Y	20	18	12	18	48	74	8	5
AWS18485AB	Wire Shelving w/ 30280, 281, 282, 283 Bins	R, B, Y	See Above			18	48	74	4 / 4 / 3 / 4	6
AWS24360284	Wire Shelving w/ 30284 Bins	R, B, Y	23¾	8¼	7	24	36	74	28	8
AWS24360287	Wire Shelving w/ 30287 Bins	R, B, Y	23¾	11	10	24	36	74	16	6
AWS24360288	Wire Shelving w/ 30288 Bins	R, B, Y	23¾	16½	11	24	36	74	12	3
AWS243605AB	Wire Shelving w/ 30287 & 30288 Bins	R, B, Y	See Above			24	36	74	12/6	3
AWS24361288	Wire Shelving w/ 30288 Bins	R, B, Y	23¾	16½	11	24	36	63	10	3

Bin color code: R=Red, B=Blue, Y=Yellow. Specify one bin color when ordering.

ShelfMax™ Wire Systems

Model Number	Description	ShelfMax Bin Colors	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AWS143630040	Wire Shelving w/ 30040	R, B, Y, G, W	11¾	4¾	6	14	36	74	64	8
AWS143630080	Wire Shelving w/ 30080	R, B, Y, G, W	11¾	8¾	6	14	36	74	32	8
AWS183630088	Wire Shelving w/ 30088	R, B, Y, G, W	17¾	8¾	6	14	36	74	32	8
AWS143630090	Wire Shelving w/ 30090	R, B, Y, G, W	11¾	6¾	6	14	36	74	40	8
AWS183630048	Wire Shelving w/ 30048	R, B, Y, G, W	17¾	4¾	6	18	36	74	64	8
AWS183630098	Wire Shelving w/ 30098	R, B, Y, G, W	17¾	6¾	6	18	36	74	40	8

Bin color code: R=Red, B=Blue, Y=Yellow, G=Green, W=White. Specify one bin color when ordering.

accessories



Footplates
Steel tips on bottom of frames prevent movement of stationary units



Locking Casters
Highly maneuverable, locking wheels create mobile or stationary units



Non-Locking Casters
Highly maneuverable, non-locking wheels create mobile units



Color Coding

Visual reference made simple! Color code work areas with Wire Shelving Systems for quick identification of stored items



Steel Shelving Systems

shelving systems & cabinets

- More than 40 system options for bin and shelf configurations
- Manufactured from high-grade, 22-gauge steel with a powder-coated finish
- Can be ordered independently or purchased with bins as a complete system
- Shelving units are easy to assemble, using nuts and bolts only on the top and bottom shelves
- Other shelves are quickly assembled, and can be adjusted when necessary, using compression clips
- All units feature a “sanitary” base that keeps debris and small parts from underneath the shelving
- 1236 Enclosure or 1836 Enclosure can be purchased separately for use with any AS1279 or AS1879 open shelving unit



Per Shelf Weight Capacity:


- 12 x 36 = 500
- 18 x 36 = 550
- 18 x 42 = 355
- 24 x 36 = 550
- 30 x 36 = 600

Super-Size & Organize with Steel Shelving Systems!

- Accommodates new 24” and 30” Super-Size AkroBins
- Efficiently organize large, heavy items and improve workflow



features



Easy Shelf Adjustment: Quickly change shelf height with compression clips



Shelving Units have 355-600 lb. capacity per shelf when assembled and installed per instructions



Steel Shelving Systems

shelving systems & cabinets

24" Super-Size Steel Shelf Unit



Expand Storage Options

- Available with 3 or 4 shelves
- Complete packages available with the 24" Super-Size AkroBins to efficiently organize large items and improve workflow
- Stacking AkroBins on top of each other on each shelf saves valuable space
- Super-Size AkroBins, pgs. 26-27

30" Super-Size Steel Shelf Unit



Lengthen Storage Capability

- Available with 3 or 4 shelves
- Complete packages available with the 30" Super-Size AkroBins to efficiently organize large items and improve workflow
- Stacking AkroBins on top of each other on each shelf saves valuable space
- Super-Size AkroBins, pgs. 26-27

12" System Bin™ Shelf Unit



Free Up Floor Space

- Available with 11 shelves
- Includes (10) 30312 System Bins
- Quickly organize with System Bins: one-piece, six-bin unit
- System Bins, pg. 24

18" System Bin™ Shelf Unit



Increase Work In Process Efficiency

- Available with 11 shelves
- Includes (10) 30318 System Bins
- Quickly organize with System Bins: one-piece, six-bin unit
- System Bins, pg. 24

Indicator™ Bin Shelf Unit



Never Run Out of Inventory

- Available with 12 shelves
- Holds (96) 36442BLUE bins and (60) 36462BLUE bins
- 500 lb. weight capacity per shelf, up to 8,500 lbs.
- Indicator Bins, pg. 21

36" Wide Stak-N-Store Systems



Boost Organization

- Available with 6 shelves
- Configure for 15, 10 or 6 Stak-N-Store bins depending on bin size selected
- Wide, hopper-front Stak-N-Store bins are perfect to store large, heavy or bulky items
- Stak-N-Store bins, pg. 28

42" Wide Stak-N-Store Systems



Maximize Space Utilization

- Available with 6 shelves
- Comes complete with 12 Stak-N-Store bins
- Wide, hopper-front Stak-N-Store bins are perfect to store large, heavy, or bulky items
- Stak-N-Store bins, pg. 28

AkroBin® Shelf Rack



Shorten Assembly Times

- Available with 4 shelves and solid top for extra workspace
- Configured to hold (12) 30240 AkroBins and (6) 30250 AkroBins
- Durable AkroBins feature a curved-bottom hopper front, making it easy to retrieve small parts
- AkroBins, pgs. 4-6

12" Shelf Bin System



Sort Parts To Improve Efficiency

- Available with 13 shelves
- Holds up to (96) 18" deep Shelf Bins or (144) 12" deep Shelf Bins
- Strong, polypropylene Shelf Bins outlast corrugated bins
- Shelf Bins, pgs. 12-14

ShelfMax™ Shelf Unit



6" Bins Maximize Storage Capacity

- Available with 10 shelves
- Configure for 40 to 80 bins
- 7 Bin Sizes & 5 Colors
- ShelfMax Bins, pg. 13



12" Shelf Bin Systems

Model Number	Description	Bin Model No.	Bin Dimensions (Inches)				Shelf Dimensions (Inches)			
			L	W	H	D	L	H	# of Bins	Shelves
AS1279	Shelving (no Bins)	-	-	-	-	12	36	79	-	13
AS1279110Y	Shelving with Bins	30110YELLO	11%	2%	4	12	36	79	144	13
AS1279120Y	Shelving with Bins	30120YELLO	11%	4%	4	12	36	79	96	13
AS1279130Y	Shelving with Bins	30130YELLO	11%	6%	4	12	36	79	60	13
AS1279150Y	Shelving with Bins	30150YELLO	11%	8%	4	12	36	79	48	13
AS1279170Y	Shelving with Bins	30170YELLO	11%	11%	4	12	36	79	36	13

12" System Bin Shelf Unit

Model Number	Description	Bin Model No.	Bin Dimensions (Inches)				Shelf Dimensions (Inches)			
			L	W	H	D	L	H	# of Bins	Shelves
AS1279312R	Shelving with System Bins	30312RED	33	12	5	12	36	79	10	11
AS1279312B	Shelving with System Bins	30312BLUE	33	12	5	12	36	79	10	11
AS1279312Y	Shelving with System Bins	30312YELLO	33	12	5	12	36	79	10	11
AS1279312G	Shelving with System Bins	30312GREEN	33	12	5	12	36	79	10	11



Steel Shelving Systems

shelving systems & cabinets



NEW
product!



NEW
Sizes!



18" Shelf Bin Systems

Model Number	Description	Bin Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AS1879	Shelving (no Bins)	-	-	-	-	18	36	79	-	12
AS1879128Y	Shelving with Bins	30128YELLO	17 $\frac{7}{8}$	4 $\frac{1}{8}$	4	18	36	79	96	12
AS1879138Y	Shelving with Bins	30138YELLO	17 $\frac{7}{8}$	6 $\frac{1}{8}$	4	18	36	79	60	12
AS1879158Y	Shelving with Bins	30158YELLO	17 $\frac{7}{8}$	8 $\frac{1}{8}$	4	18	36	79	48	12
AS1879178Y	Shelving with Bins	30178YELLO	17 $\frac{7}{8}$	11 $\frac{1}{8}$	4	18	36	79	36	12

18" System Bin Shelf Unit

Model Number	Description	Bin Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AS1879318R	Shelving with System Bins	30318RED	33	18	5	18	36	79	10	10
AS1879318B	Shelving with System Bins	30318BLUE	33	18	5	18	36	79	10	10
AS1879318Y	Shelving with System Bins	30318YELLO	33	18	5	18	36	79	10	10
AS1879318G	Shelving with System Bins	30318GREEN	33	18	5	18	36	79	10	10

Indicator™ Bin System

Model Number	Description	Bin Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AS127936442B	Shelving, with Indicator Bins	36442BLUE	11 $\frac{1}{8}$	4 $\frac{1}{4}$	4	12	36	79	96	12
AS127936462B	Shelving, with Indicator Bins	36462BLUE	11 $\frac{1}{8}$	6 $\frac{1}{4}$	4	12	36	79	60	12

36" Stak-N-Store System

Model Number	Description	Bin Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Bonus Bins
			L	W	H	D	L	H		
AS187936	Shelving (no Bins)	-	-	-	-	18	36	79	-	-
AS187913014	Shelving, with Bins	13014	17 $\frac{1}{2}$	10 $\frac{7}{8}$	12 $\frac{1}{2}$	18	36	79	15	1
AS187913018	Shelving, with Bins	13018	17 $\frac{1}{2}$	16 $\frac{1}{2}$	12 $\frac{1}{2}$	18	36	79	10	-
AS1879ASORT	Shelving, with Bin Mix	13014, 13018	See Above			18	36	79	6/6	2/0

42" Stak-N-Store System

Model Number	Description	Bin Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Bonus Bins
			L	W	H	D	L	H		
AS187942	Shelving (no Bins)	-	-	-	-	18	42	79	-	-
AS187913017	Shelving, with Bins	13017	15 $\frac{1}{4}$	19 $\frac{3}{8}$	12 $\frac{3}{16}$	18	42	79	10	2

AkroBin Shelf Rack

Model Number	Description	Unit Dimensions (Inches)			Shelf Dimensions (Inches)			Rack Weight Capacity
		L	W	H	L	W	H	
RABR5338	Holds twelve 30240 Bins and six 30250 Bins*	53 $\frac{1}{2}$	15 $\frac{1}{4}$	37 $\frac{3}{8}$	17 $\frac{1}{4}$	15 $\frac{1}{4}$	7 $\frac{3}{8}$	300 lbs.

*Bins sold separately.

24" Super-Size Shelving System

Model Number	Description	Bin Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AS2479	Shelving (no Bins)	-	-	-	-	24	36	79	-	-
AS2479284	Shelving with 30284 Bins	30284	23 $\frac{3}{8}$	8 $\frac{1}{4}$	10	24	36	79	24	3
AS2479287	Shelving with 30287 Bins	30287	23 $\frac{3}{8}$	11	10	24	36	79	24	3
AS2479288	Shelving with 30288 Bins	30288	23 $\frac{3}{8}$	16 $\frac{1}{2}$	11	24	36	79	12	4
AS2479ASSORT	Shelving with 30287/30288 Bins	30287/30288	See Above			24	36	79	12/6	3

30" Super-Size Shelving System

Model Number	Description	Bin Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AS3679	Shelving (no Bins)	-	-	-	-	30	36	79	-	-
AS3679292	Shelving with 30292 Bins	30292	29 $\frac{3}{8}$	11	10	30	36	79	24	3
AS3679293	Shelving with 30293 Bins	30293	29 $\frac{3}{8}$	16 $\frac{1}{2}$	11	30	36	79	12	4
AS3679ASSORT	Shelving with 30292/30293 Bins	30292/30293	See Above			30	36	79	12/6	3

Specify bin color.

ShelfMax™ Shelf Unit

Model Number	Description	Bin Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			# of Bins	Shelves
			L	W	H	D	L	H		
AS1279040	12" Steel Shelving	30040	11 $\frac{1}{8}$	4 $\frac{1}{8}$	6	12	36	79	80	10
AS1279080	12" Steel Shelving	30080	11 $\frac{1}{8}$	8 $\frac{1}{8}$	6	12	36	79	40	10
AS1279090	12" Steel Shelving	30090	11 $\frac{1}{8}$	6 $\frac{1}{8}$	6	12	36	79	50	10
AS1879048	18" Steel Shelving	30048	17 $\frac{7}{8}$	4 $\frac{1}{8}$	6	18	36	79	80	10
AS1879088	18" Steel Shelving	30088	17 $\frac{7}{8}$	8 $\frac{1}{8}$	6	18	36	79	40	10
AS1879098	18" Steel Shelving	30098	17 $\frac{7}{8}$	6 $\frac{1}{8}$	6	18	36	79	50	10
AS2479094	24" Steel Shelving	30094	23 $\frac{3}{8}$	6 $\frac{1}{8}$	6	24	36	79	50	10



Heavy-Duty Cabinets

shelving systems & cabinets

- Heavy-Duty Cabinets provide MAXIMUM space for storage of parts and protect contents from dust, damage and theft
- Powder-coated paint is resistant to cuts and scratches
- Industrial-strength lock and key ensure complete security
- Cabinets ship assembled, shelving and panels require installation
- Shelves are adjustable on 2" centers allowing the flexibility of securely storing multiple-sized objects
- 3 configurations – Shelves, Louvered Panels, Combination with Bins
- Removable louvered panels attach to solid steel back panel
- 16-gauge steel construction



Heavy-Duty Cabinet

- Model No. HD4824A
- Cabinet with shelves only



Heavy-Duty Cabinet

- Model No. HD4824E
- Cabinet with louvers and bins



Heavy-Duty Cabinet

- Model No. HD4824F
- Cabinet with louvers and bins

Heavy-Duty Cabinet 48"W x 24"D x 78"H

Bin Dimensions (Inches)

Model No.	Description	Bin Model No.	L	W	H	Qty. of Bins
HD4824A	Cabinet w/Shelves Only	–	–	–	–	–
HD4824E	Cabinet w/ Louvers	30220YELLO	7 $\frac{3}{4}$	4 $\frac{1}{4}$	3	160
		30230YELLO	10 $\frac{7}{8}$	5 $\frac{1}{2}$	5	24
		30240YELLO	14 $\frac{3}{4}$	8 $\frac{1}{4}$	7	20
		30235YELLO	10 $\frac{7}{8}$	11	5	12
HD4824F	Cabinet w/ Louvers	30220YELLO	7 $\frac{3}{4}$	4 $\frac{1}{4}$	3	160
		30230YELLO	10 $\frac{7}{8}$	5 $\frac{1}{2}$	5	48
		30240YELLO	14 $\frac{3}{4}$	8 $\frac{1}{4}$	7	20

Standard Cabinets

shelving systems & cabinets

- Made from 16-gauge steel
- Powder-coated finish

Heavy-Duty Cabinets and Standard Cabinets can accommodate:

- AkroBins pgs. 4-6
- Shelf Bins pgs. 12-14



AkroBin® Cabinet

- Model No. AC3624Y
- Louvered panels on back wall and doors hold up to 138 bins



AkroBin® Cabinet with 3 Shelves

- Model No. AC3624Y3AS
- Louvered panels and 3 full 24" shelves hold up to 102 bins



AkroBin® Cabinet with Flush Doors

- Model No. AC3618Y
- Louvered panel on back wall holds up to 42 bins



Quick-View Security Bin Cabinet

- Model No. AC3618QV240
- Lexan™ door panels; louvered back wall panel
- Holds up to 36 bins



Secure View Security Bin Cabinet

- Model No. AC3618SV250
- Steel mesh door panels; louvered back wall panel
- Holds up to 36 bins

accessories

- For use with Standard Cabinets only
- Easily convert large cabinets to mobile units!
- Bin Cabinet Dollies feature solid, powder-coated steel deck with 1¼" lip and welded corners



AkroBin Cabinet 36" W x 24" D x 78" H

Model No.	Description	Bin Model No.	Bin Dimensions (Inches)			Qty. of Bins
			L	W	H	
AC3624	Cabinet w/ Louvered Panels on Back & Doors, no Bins	-	-	-	-	-
AC3624Y	Cabinet w/ Louvered Panels on Back & Doors with Bins	30210YELLO	5¾"	4¾"	3"	48
		30220YELLO	7¾"	4¾"	3"	48
		30230YELLO	10¾"	5½"	5"	24
		30240YELLO	14¾"	8¾"	7"	12
		30250YELLO	14¾"	16½"	7"	6

AkroBin Cabinet w/ 3 Shelves 36" W x 24" D x 78" H

Model No.	Description	Bin Model No.	Bin Dimensions (Inches)			Qty. of Bins
			L	W	H	
AC36243AS	Cabinet w/ 3 Shelves, and Louvered Panels on Back Wall and Door, no Bins	-	-	-	-	-
AC3624Y3AS	Cabinet w/ 3 Shelves, and Louvered Panels on Back Wall and Door, with Bins	30210YELLO	5¾"	4¾"	3"	48
		30220YELLO	7¾"	4¾"	3"	48
		30250YELLO	14¾"	16½"	7"	6

AkroBin Cabinet w/ Flush Doors 36" W x 18" D x 78" H

Model No.	Description	Bin Model No.	Bin Dimensions (Inches)			Qty. of Bins
			L	W	H	
AC3618	Cabinet w/ Louvered Panels on Back Wall, no Bins	-	-	-	-	-
AC3618Y	Cabinet w/ Louvered Panels on Back Wall, with Bins	30230YELLO	10¾"	5½"	5"	24
		30240YELLO	14¾"	8¾"	7"	12
		30250YELLO	14¾"	16½"	7"	6

Quick-View Security Bin Cabinet 36" W x 18" D x 78" H

Model No.	Description	Bin Model No.	Bin Dimensions (Inches)			Qty. of Bins
			L	W	H	
AC3618QV	Cabinet w/ Quick View Doors, Louvered Back, no Bins	-	-	-	-	-
AC3618QV240	Cabinet w/ Quick View Doors, Louvered Back, with Bins	30240YELLO	14¾"	8¾"	7"	36
AC3618QV250	Cabinet w/ Quick View Doors, Louvered Back, with Bins	30250YELLO	14¾"	16½"	7"	18

Secure-View Security Bin Cabinet 36" W x 18" D x 78" H

Model No.	Description	Bin Model No.	Bin Dimensions (Inches)			Qty. of Bins
			L	W	H	
AC3618SV	Cabinet w/ Secure View Mesh Doors, Louvered Back, no Bins	-	-	-	-	-
AC3618SV240	Cabinet w/ Secure View Mesh Doors, Louvered Back, with Bins	30240YELLO	14¾"	8¾"	7"	36
AC3618SV250	Cabinet w/ Secure View Mesh Doors, Louvered Back, with Bins	30250YELLO	14¾"	16½"	7"	18

Bin Cabinet Dollies

Model No.	Description	Dimensions (Inches)			Polyolefin Casters	Weight Capacity
		L	W	H		
AC803618M26	18 x 36 Bin Cabinet Dolly	36½"	18½"	5¼"	3 x 1¼"	1000 lbs.
AC803624M26	24 x 36 Bin Cabinet Dolly	36½"	24½"	6½"	4 x 1¼"	1000 lbs.



ProCart™

mobile systems & work centers

- Hinged side gates on both shelves flip up or down to convert the ProCart to a flat-top or box-top cart
- A versatile work center for the assembly line, warehouse or wherever you need portable storage
- High-density polyethylene structural foam construction is dent-resistant, rust-proof and never needs painting
- 400 lb. maximum cart load. 200 lb. capacity per top and bottom shelf
- Assembly required
- Color: Gray

ProCart™




features



Deep, molded-in compartments keep items secured and within reach (Only large cart has mug holder.)



Comfortable, full-width handle gives complete handling control



Optional nine-rail system (sold separately) allows AkroBins® to hang



Toe-touch, locking swivel wheels



Smooth, rounded corners and edges



Durable, non-marking 5" wheels



I-beam post makes loading and unloading oversized boxes on the lower shelf easy



Small Cart
Model No. 30930



Large Cart
Model No. 30936
Shown with optional rail kit

AkroBins Ordering Information

To create a customized ProCart with AkroBins, use the chart below to determine the quantity of AkroBins that will fit your ProCart. Carts, rail kits and bins must be ordered separately. When ordering, please specify Red, Yellow, Blue, Stone, Green, Semi-Clear or Black bins.

Optional 9-Rail Hanging System Ordering Information


The 9-Rail Hanging System is required to hang AkroBins and modular cabinets on your ProCart. **For large cart rails, order Model No. 30906. For small cart rails, order Model No. 30900. Refer to pg. 34 for modular cabinets.**

ProCart

Dimensions Inches

Model No.	Description	L	W	H	Ctn. Qty.
30936	Large Cart	45½"	24"	34½"	1
30930	Small Cart	41½"	19"	34½"	1

Easy assembly – requires Phillips screwdriver and rubber mallet



Use this chart when ordering one size AkroBins for your ProCart

Bin Model No. Bin Dim. L x W x H	30210 5¾ x 4½ x 3	30220 7¾ x 4½ x 3	30224 10¾ x 4¾ x 4	30230 10¾ x 5½ x 5	30234 14¾ x 5½ x 5	30235 10¾ x 11 x 5	30239 10¾ x 8¼ x 7	30240 14¾ x 8¼ x 7	30250 14¾ x 16½ x 7	30255 10¾ x 16½ x 5	30320 8¾ x 33 x 5	19-Series Cabinet
30936 Large Cart	80	80	48	36	36	18	16	16	8	12	6	4
30930 Small Cart	70	70	42	30	-	12	12	-	-	-	-	2

Louvered Carts

mobile systems & work centers

- Industrial-grade mobile workstation with a welded-steel frame and steel reinforced premium hardwood work surface
- Available in two worktop sizes: 48" L x 24" W (for 12" AkroDrawers) and 36" L x 18" W (for 18" AkroDrawers)
- Features two stationary shelves for AkroDrawers
- Made from 16-gauge steel with durable powder-coated finish
- Non-marking casters allow weight capacity of 800 lbs.
- Small cart has four 4" casters
- Large cart has four 5" casters
- Ships fully assembled and ready to use
- Colors: Textured Charcoal Gray and Textured Putty



MA3618PAST

AkroDrawers™



MA4824C1

features




Louvered panels on cart ends can accommodate various sizes of AkroBins



Tubular push handle featured on end of carts with swivel casters for easy handling



Raised barriers near shelf edges keep AkroDrawers from sliding out when cart is in motion or during sudden stops or turns



Small Louvered Cart 37"L x 18" W x 36"H

Model No.	Description	Cart Color	Wt. Capacity	Qty. of Drawers	Drawer Color
MA3618C	Small Louvered Cart with no AkroDrawers	Textured Charcoal Gray	800 lbs.	–	–
MA3618CAST	Small Louvered Cart with 31168 & 31188 AkroDrawers	Textured Charcoal Gray	800 lbs.	12/4	R,B,Y,GRY,CRY

Model No.	Description	Cart Color	Wt. Capacity	Qty. of Drawers	Drawer Color
MA3618P	Small Louvered Cart with no AkroDrawers	Textured Putty	800 lbs.	–	–
MA3618PAST	Small Louvered Cart with 31168 & 31188 AkroDrawers	Textured Putty	800 lbs.	12/4	B,CRY

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cart. Blue or Crystal Clear available with Putty Cart. Only one color per unit.

Large Louvered Cart 49"L x 24" W x 37-1/2"H

Model No.	Description	Cart Color	Wt. Capacity	Qty. of Drawers	Drawer Color
MA4824C	Large Louvered Cart with no AkroDrawers	Textured Charcoal Gray	800 lbs.	–	–
MA4824C1	Large Louvered Cart with 31142 & 31162 AkroDrawers	Textured Charcoal Gray	800 lbs.	22/16	R,B,Y,GRY,CRY
MA4824C2	Large Louvered Cart with 31142 & 31182 AkroDrawers	Textured Charcoal Gray	800 lbs.	22/10	R,B,Y,GRY,CRY

Model No.	Description	Cart Color	Wt. Capacity	Qty. of Drawers	Drawer Color
MA4824P	Large Louvered Cart with no AkroDrawers	Textured Putty	800 lbs.	–	–
MA4824P1	Large Louvered Cart with 31142 & 31162 AkroDrawers	Textured Putty	800 lbs.	22/16	B,CRY
MA4824P2	Large Louvered Cart with 31142 & 31182 AkroDrawers	Textured Putty	800 lbs.	22/10	B,CRY

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cart. Blue or Crystal Clear available with Putty Cart. Only one color per unit.

Color code: B=Blue, CRY=Crystal Clear, GRY=Gray, R=Red, Y=Yellow

AkroDrawers Outside Dimensions Inches

Model No.	L	W	H
31142	11 $\frac{1}{8}$ "	3 $\frac{3}{4}$ "	4 $\frac{1}{2}$ "
31162	11 $\frac{1}{8}$ "	5 $\frac{5}{16}$ "	4 $\frac{1}{2}$ "
31182	11 $\frac{1}{8}$ "	8 $\frac{1}{2}$ "	4 $\frac{1}{2}$ "
31168	17 $\frac{1}{2}$ "	5 $\frac{5}{16}$ "	4 $\frac{1}{2}$ "
31188	17 $\frac{1}{2}$ "	8 $\frac{1}{2}$ "	4 $\frac{1}{2}$ "




Shelf & Multi-Shelf Carts


mobile systems & work centers

- Heavy-duty carts designed for daily work
- Welded steel cart rolls smoothly on long-wearing casters
- Built to withstand loads up to 2,200 lbs. with recommended casters
- Swayback-style tubular push handle (Models R1S5HR and R1S8MR have vertical handles)
- Choose from several caster options as well as rubber matting, a writing shelf and drawers
- Ships completely assembled and ready to use

features shelf & multi-shelf features



Durable powder-coated finish for lasting durability



Longitudinal stiffeners support bottom shelf



Heavy-duty, 13-gauge steel shelves



System Bin Multi-Shelf Carts
System Bins, see pg. 24



Cart Sizes - Specify size when ordering.

- Standard –
- 24" x 36"
 - 24" x 48"
 - 30" x 48"
 - 30" x 60"

Specify cart size when ordering. See page 61 for full description of casters and wheels.

Shelf Carts

Model No.	Weight Capacity (lbs.)	Caster	Shelves	Height		Shelf Clearance		Handle
				Inches	Inches	Inches	Inches	
R1S8FP2	1200	8" Full Pneumatic	2	33½	20%	20%		Swayback
R1S10FP2	1200	10" Full Pneumatic	2	35¼	20%	20%		Swayback
R1S5HR	1800	5" x 2" Polyolefin	2	30	20%	20%		Vertical
R1S5HR2LD	1800	5" x 2" Polyolefin	2	25	15½	15½		Swayback
R1S8MR	2200	8" x 2" Mold-On Rubber	2	33	20%	20%		Vertical
R1S8MR2**	2200	8" x 2" Mold-On Rubber	2	33	20%	20%		Swayback

**Low deck to minimize lifting & bending. Also available in 18 x 30 – not available in 30 x 60.



Swayback Handle

Multi-Shelf Carts

Model No.	Weight Capacity (lbs.)	Caster	Shelves	Height		Shelf Clearance		Handle
				Inches	Inches	Inches	Inches	
R2S5HR*	1800	5" x 2" Polyolefin	2	30	20%	20%		Horiz. Tubular
R3S5HR	1800	5" x 2" Polyolefin	3	30	9%	9%		Horiz. Tubular
R4S5HR	1800	5" x 2" Polyolefin	4	63¼	17	17		Horiz. Tubular
R4S8MR	2200	8" x 2" Mold-On Rubber	4	66¼	17	17		Horiz. Tubular
R5S5HR**	1800	5" x 2" Polyolefin	5	63¼	12½	12½		Horiz. Tubular
R5S8MR**	2200	8" x 2" Mold-On Rubber	5	66¼	12½	12½		Horiz. Tubular

*Only available in 18 x 30. **Also available in 36 x 72.



Horizontal Tubular Handle

System Bin Multi-Shelf Carts

Model No.	Weight Capacity (lbs.)	Caster	Shelves	Height		Handle	Bin/Qty.	Color
				Inches	Inches			
R5SY5HR2436**	1800	5" x 2" Polyolefin	5	40	40	Horiz. Tubular	30312/10	R Y B G
R5SY8MR2436**	2200	8" x 2" Mold-On Rubber	5	43	43	Horiz. Tubular	30312/10	R Y B G
R5SY5HR3636**	1800	5" x 2" Polyolefin	5	40	40	Horiz. Tubular	30318/10	R Y B G
R5SY8HR3636**	2200	8" x 2" Mold-On Rubber	5	43	43	Horiz. Tubular	30318/10	R Y B G

**Only available in 24" x 36" or 36" x 36" decks. Bin color code: R=Red, B=Blue, Y=Yellow, G=Green. Specify color when ordering.



Vertical Handle

Tray Service Cart

mobile systems & work centers



- Excellent for libraries and manufacturing operations
- 2 swivel, 2 fixed casters

Cart Sizes

Standard –

- 18" x 30"
- 24" x 36"
- 24" x 48"

Optional –

- 18" x 36"

Specify size when ordering

features

tray service cart features



12" deep tray



13-gauge steel



Tubular push handle



12 1/2" clear shelf spacing, with 1 1/2" lip

Tray Service Cart

Overall Dimensions (in.)

Model No.	L	W	H	Casters	Weight Capacity (lbs.)
R2T5HR1830	18	30	32 1/2	5" Polyolefin	1800
R2T5HR2436	24	36	32 1/2	5" Polyolefin	1800
R2T5HR2448	24	48	32 1/2	5" Polyolefin	1800
R2T8MR2448	24	48	35 1/2	8" Mold-On Rubber	2200

Casters & Wheels

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 61 for more caster information.

Box Trucks

features

box trucks



30 1/2" overall height, 24" interior depth



13-gauge steel with 2" hemmed edges



Available with optional lid



Secure lid with padlock or combination lock

- All box trucks have 2 swivel, 2 rigid, 5" x 2" polyolefin casters
- Solid steel or expanded metal sides available
- 1,800 lbs. capacity
- Available with optional lid



Expanded Metal Box

- Expanded metal for easy cleaning, good airflow and visibility of contents. 31 1/2" overall height; 25" inside depth

Box Trucks

Model No.	Description	Caster Type	Weight Capacity (lbs.)
R1B5HR	Steel Box Truck	5" Polyolefin	1800
R1B5HRL	Steel Box Truck with Lid	5" Polyolefin	1800
R1B5HRX	Expanded Metal Box Truck	5" Polyolefin	1800
R1B5HRXL	Expanded Metal Box Truck with Lid	5" Polyolefin	1800

Box Sizes

- 24" x 36"
- 24" x 48"
- 30" x 36"
- 30" x 48"

Specify size when ordering



Standard Caster Polyolefin

- See pg. 61 for more caster information

High-End Narrow Aisle Truck

- Extra-narrow aisle truck for order-picking and stocking where space is limited
- Slim design fits easily in tight areas
- Centered, 8" wheels and casters at each corner allow cart to turn within its own diagonal space
- Available in plywood deck with steel frame or all-steel deck
- 1,500 lb. capacity



Steel Deck



Plywood Deck

Cart Sizes

Standard –

- 18" x 48"
- 24" x 60"

Optional –

- 18" x 60"
- 24" x 48"

Specify size when ordering

High-End Narrow Aisle Trucks

Model No.	Description	Center Casters	Corner Casters	Weight Capacity (lbs.)
R215HE	Plywood Deck Steel Frame	8" Mold-On Rubber	4" Polyolefin	1500
R214HE	All-Steel	8" Mold-On Rubber	4" Polyolefin	1500



Dollies Wood

mobile systems & work centers

- Constructed from select kiln-dried hardwoods to prevent warping and shrinkage
- All boards are cut and planed to $\frac{3}{8}$ " with guaranteed consistent quality
- Four, 3" polyolefin swivel casters offer 900 lb. capacity (See caster options for up to 1,400 lb. capacity)
- Standard deck height 5 $\frac{3}{4}$ "
- Shipped fully assembled



Solid Dolly

- Three cross battens on 36" & 48" length
- Smooth, treated deck with countersunk bolts
- Deck boards run lengthwise



features



Hardwood deck with countersunk bolt holes for a smooth working surface



Non-marking 3" swivel casters with polyolefin wheels



Zinc-plated rigs and hardware resist corrosion



Flush Dolly

- Full, 4" wide by 1 $\frac{3}{4}$ " thick double length rails
- Smooth, open deck



Regular Dolly

- Strength and reliability at an economy price
- All rails are 4" wide



Carpet End Dolly

- Padded carpeting[†] protects furniture and appliances



Rubber Cap Dolly

- Non-skid reinforced 3" wide rubber caps keep slippery loads in place without damage



All-Carpet Solid Dolly

- Strength and reliability at an economy price
- Fully carpeted[†] deck prevents damage to cargo

[†]Pattern of carpet may vary

accessories



Wheel Locks



Tow Eye R1495

Wood Dollies

Dimensions Inches

Model No.	Description	L	W
RD2416S3P	Solid Dolly	24	16
RD2718S3P	Solid Dolly	27	18
RD3018S3P	Solid Dolly	30	18
RD3624S3P	Solid Dolly	36	24
RD4824S3P	Solid Dolly	48	24
RD2416F3P	Flush Dolly	24	16
RD2718F3P	Flush Dolly	27	18
RD3018F3P	Flush Dolly	30	18
RD3624F3P	Flush Dolly	36	24
RD4824F3P	Flush Dolly	48	24
RD2416R3P	Regular Dolly	24	16
RD3018R3P	Regular Dolly	30	18
RD3624R3P	Regular Dolly	36	24
RD3018CE3P	Carpet End Dolly	30	18
RD3624CE3P	Carpet End Dolly	36	24
RD2718RC3P	Rubber Cap Dolly	27	18
RD3018RC3P	Rubber Cap Dolly	30	18
RD3018AC3P	All-Carpet Solid Dolly	30	18
RD3624AC3P	All-Carpet Solid Dolly	36	24

Caster Options

Model No.	Description	Weight Capacity (lbs.)
3P	3" Polyolefin Casters	900
4P	4" Polyolefin Casters	1200
5P	5" Polyolefin Casters	1400
3R	3" Gray Non-Marking Rubber	900
35R	3 $\frac{1}{2}$ " Gray Non-Marking Rubber	900
4Rx	4" Blue Elastic Rubber	900
4R	4" Non-Marking Rubber Casters	1100
5R	5" Non-Marking Rubber Casters	1350

Casters & Wheels

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 61 for more caster and wheel information.


Brake Kits

Brake kits installed on two swivel casters – optional (non-returnable)	
R1130BRK	3" Brake Kits for Hard Rubber Casters
R1151BRK	3" Brake Kits for Polyolefin Casters



Dollies Polyethylene

mobile systems & work centers



- High-impact, durable polyethylene construction
- Steel-reinforced, one-piece deck design
- Easy to clean, non-porous platform will not rot, mildew or splinter
- 1,200 lb. weight capacity
- Quick, easy assembly
- Colors: Blue or Red



Dollies Steel

- Durable, powder-coated finish
- Open structural angle dollies, 1½" x 1½" x ½"
- Solid decks are smooth, 13-gauge steel
- 1½" lip turned down for a smooth surface. Order lips up for a contained area
- Up to 1,000 lb. weight capacity



Solid Deck – Lips Up



Solid Deck – Lips Down



Open Angle – Lips Up



Open Angle – Lips Down

Polyethylene Dollies

Model No.	Description	Dimensions Inches		Caster Type*	Inches	
		L	W		Overall Height	Weight Capacity (lbs.)
RMD3018F4PN	Flush Polyethylene w/ Casters	30	18	4" Polyolefin	7¾	1200
RMD3018RC4PN	Padded Polyethylene w/ Casters	30	18	4" Polyolefin	8¾	1200
RMD3018FN	Flush Polyethylene w/o Casters	30	18	–	2¾	–
RMD3018RCN	Padded Polyethylene w/o Casters	30	18	–	3¾	–
RMD3018F4RX	Flush Polyethylene w/ Casters	30	18	4" Blue Elastic Rubber	7¾	1200
RMD3018RC4RX	Padded Polyethylene w/ Casters	30	18	4" Blue Elastic Rubber	8¾	1200

Specify color when ordering

Plate-style 4" polyolefin swivel casters for maximum maneuverability and easy replacement

Steel Dollies

Style	Lips Down Model No.	Lips Up Model No.	Capacity	Caster Type*	Inches		
					Caster Size	Deck Height Up	Deck Height Down
Solid Dolly	RD843HR	RU843HR	900 lbs.	Polyolefin	3 x 1¼	5½	4¾
Solid Dolly	RD843SS	RU843SS	1000 lbs.	Semi-Steel	3 x 1¼	5½	4¾
Solid Dolly	RD844HR	RU844HR	1000 lbs.	Polyolefin	4 x 1½	6¾	5¼
Solid Dolly	RD844SS	RU844SS	1000 lbs.	Semi-Steel	4 x 1½	6¾	5¼
Open Angle	RD853HR	RU853HR	900 lbs.	Polyolefin	3 x 1¼	5¾	4¾
Open Angle	RD853SS	RU853SS	1000 lbs.	Semi-Steel	3 x 1¼	5¾	4¾
Open Angle	RD854HR	RU854HR	1000 lbs.	Polyolefin	4 x 1½	6¾	5½
Open Angle	RD854SS	RU854SS	1000 lbs.	Semi-Steel	4 x 1½	6¾	5½

Deck Sizes

Standard

- 16" x 27"
- 18" x 30"
- 18" x 24"
- 24" x 36"

Specify size when ordering

*Casters & Wheels

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 61 for more caster and wheel information.



Hand Trucks


mobile systems & work centers

accessories wheel specifications



Medium-Duty

- Medium-duty hand trucks for day-to-day work
- Welded-steel construction supports up to 300 lbs.
- Durable, powder-coated finish
- 7/8" OD structural pipe frame, 13-gauge wall
- Standard 7" x 14" steel nose plate
- Ships completely assembled and ready to use
- 5/8" diameter axle
- Two position bracket fits 8" or 10" wheels
- Heavy flat bar and tube for climbing stairs




Semi-Pneumatic
10" x 2 3/4"



Full Pneumatic
10" x 3 1/2"



Mold-On Rubber
8" x 2"



Heavy-Duty

- Heavy-duty hand trucks for all types of loads
- Welded-steel hand trucks support up to 500 lbs.
- Durable, powder-coated finish
- 1" OD structural pipe frame, 13-gauge steel
- 5/8" diameter axle
- Standard 8" x 14" steel nose plate
- Optional 10" x 14" or 14" x 14" noseplate available*
- Two position bracket fits 8" or 10" wheels

*Special-order products are not returnable.



Specialty



Single & Dual Gas Trucks

- Heavy-duty truck designed to handle 330 cu. ft. cylinders
- Available in single and dual cylinder models
- Includes heavy-duty holding chain
- Hard rubber swivel caster
- Color: Green



Single Cylinder Hand Truck

- Perfect for medium to large cylinders
- Also transports boxes or other bulky items
- Includes heavy-duty holding chain
- Color: Green



Flow Back (FB)



Dual Loop

Medium-Duty Hand Trucks – Flow Back		Inches	Inches	
Model No.	Wheel Type	Wheel Size	H	W
R3008MR	Mold-On Rubber	8	45	19%
R3010FP	Full Pneumatic	10	45	22
R3010SP	Semi-Pneumatic	10	45	20

Heavy-Duty Hand Trucks – Flow Back		Inches	Inches	
Model No.	Wheel Type	Wheel Size	H	W
R4008MR	Mold-On Rubber	8	45	19%
R4008MR2	Mold-On Rubber	8	52	19%
R4010FP	Full Pneumatic	10	45	22
R4010FP2	Full Pneumatic	10	52	22
R4010SP	Semi-Pneumatic	10	45	20
R4010SP2	Semi-Pneumatic	10	52	22

Heavy-Duty Hand Trucks – Dual Loop		Inches	Inches	
Model No.	Wheel Type	Wheel Size	H	W
R4510SP	Semi-Pneumatic	10	46	20
R4510SP2	Semi-Pneumatic	10	53	20

Single & Dual Gas Trucks			Inches
Model No.	Truck Type	Wheel Type	Wheel Size
RGTS10FP	Single	Full Pneumatic	10 x 3 1/2
RGTD10FP	Dual	Full Pneumatic	10 x 3 1/2
RGTS10SP	Single	Semi-Pneumatic	10 x 2 3/4
RGTD10SP	Dual	Semi-Pneumatic	10 x 2 3/4

- GTS Base Plate – 14" W x 6" D, OAH – 45" 1143
- GTD Base Plate – 29" W x 6" D, OAH – 45" 1143

Dual Cylinder Truck with T-Handle		Inches
Model No.	Wheel Type	Wheel Size
RCT40LW	Lightweight	8 x 1 1/4

- Base Plate – 17" W x 8" D, OAH – 43" 1092

Single Cylinder Hand Truck		Inches
Model No.	Wheel Type	Wheel Size
RCTV40SP	Semi-Pneumatic	10 x 2 3/4

- Base Plate – 14" W x 7" D, OAH – 48" 1219

Hand Trucks & Drum Handling Equipment

mobile systems & work centers



Cradle Combo Truck

- A drum truck and cradle in one
- Handles 30 and 55-gallon drums with ease
- Extra wheels assist in climbing curbs or loading pallets
- Adjustable clip keeps drum in place
- 1 5/16" OD tube frame
- Durable, powder-coated finish



Cradle Combo Truck

Cradle Combo Truck		Inches	Inches	
Model No.	Wheel Type	Wheel Size	Roller Bearing	Load Capacity
R9508MR2		8 x 2	3/4	1000 lbs.
		6 x 2	3/4	
R9510MR2		10 x 2 1/2	1	1200 lbs.
		6 x 2	3/4	



Drum Dolly



- For the ease of rolling 30 and 55-gallon drums
- Durable, powder-coated finish

Drum Dolly			
Model No.	Wheel Type	Load Capacity	Diameter
R9255HR	3" Swivel Polyolefin	900 lbs.	23 1/2" ID



Pail Truck

- Multi-purpose hand truck for carting 5-gallon pails
- Cross straps with supporting arms hold pails in place while in transit
- Welded, 1" structural pipe frame with 1/8" walls; durable, powder-coated finish
- Holds 4 pails, up to 300 lbs. capacity

Pail Truck		Inches	Inches	Inches
Model No.	Wheel Type	Wheel Size	Overall Height	Overall Width
RPT4010SP	Semi-Pneumatic	10	55 1/2	18 1/2



Dual-Purpose Hand Truck



- Dual-function hand truck converts to platform position for oversize loads
- Welded, 1 5/16" OD tube frame and 1" OD tube handle powder-coated finish for durability
- Up to 600 lbs. capacity in platform mode
- Large 7" x 14" nose plate
- Axle accommodates 8" or 10" wheels
- Color: Silver

Dual-Purpose Hand Truck		Inches	Inches	Inches
Model No.	Wheel Type	Wheel/Caster Size	Overall Height	Overall Width
RDT4008SP	Semi-Pneumatic	8/3	46	19 5/8
RDT4010FP	Full Pneumatic	10/5	46	22
RDT4010SP	Semi-Pneumatic	10/5	46	20



VERSA/Deck™


mobile systems & work centers

features

- Versatile, structural foam cart with multiple handle and caster options
- Sturdy, easy-to-clean deck resists most chemicals and damage from long-term weather exposure
- All decks are steel reinforced
- Designed with handles mounted outside of deck to maximize deck space
- Choose the deck size, caster type and handle style to create the exact configuration you need
- Decks are available in two sizes: 24" x 48" and 30" x 60"
- 1,000 lb. load capacity
- Deck color: Gray



24" x 48"
R90181 Deck
R92411 Handle



Non-skid platform surface



Powder-coated heavy-gauge steel handles and rails



Steel outside deck pockets are welded to underdeck reinforcements



HDPE molded structural foam deck is reinforced with steel for long-term durability

24" x 48" Decks & Casters*

Inches

Model No.	Caster Type	Caster Size	Ship Wt. w/o handles
R90181	Pneumatic	8	69 lbs.
R90162	Polyolefin	6	61 lbs.
R90163	Polyurethane	6	61 lbs.
R90182	Mold-On Rubber	8	81 lbs.
R90184	Polyolefin	8	65 lbs.
R90110	Pneumatic	10	77 lbs.
R90185	Thermo-Plastic	8	61 lbs.

30" x 60" Decks & Casters*

Inches

Model No.	Caster Type	Caster Size	Ship Wt. w/o handles
R90281	Pneumatic	8	93 lbs.
R90262	Polyolefin	6	85 lbs.
R90263	Polyurethane	6	85 lbs.
R90282	Mold-On Rubber	8	105 lbs.
R90284	Polyolefin	8	89 lbs.
R90210	Pneumatic	10	101 lbs.
R90285	Thermo-Plastic	8	85 lbs.

Handles & Rails for 24" x 48" VERSA/Deck Cart

Model No.	Size (inches)	Style	Handle	Color	Ship Wt.
Outside Deck					
R92411	18	Open	Swayback	Gray	5 lbs.
R92412	18	Crossbar	Swayback	Gray	6 lbs.
Handle Rails Index					
R94817	48	Crossbar	Straight	Gray	14 lbs.

Handles & Rails for 30" x 60" VERSA/Deck Cart

Model No.	Size (inches)	Style	Handle	Color	Ship Wt.
Outside Deck					
R93011	24	Open	Swayback	Gray	9 lbs.
R93012	24	Crossbar	Swayback	Gray	10 lbs.
Handle Rails Index					
R96017	60	Crossbar	Straight	Gray	16 lbs.

*Casters & Wheels

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 61 for more caster and wheel information.



How to Order

STEP 1 – pick a deck & casters*

Refer to charts above to select deck size and casters



Holes are drilled for handle ordered

Deck sizes

- 24" x 48"
- 30" x 60"
- Color: Gray

*Casters & Wheels

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 61 for more caster and wheel information.

STEP 2 – pick a handle & rails

Refer to charts above to select handle and rail configuration

Handle – Outside Deck




Open Style / Swayback



Crossbar / Swayback

Handle Rails – Indeck



Crossbar / Straight





Platform Trucks *Wood Deck*


mobile systems & work centers



- Safely transport product, minimize lifting/carrying
- Heavy-duty platform trucks with kiln-dried, tongue and groove hardwood decks
- Caster options allow 1,180 to 3,000 lb. capacities
- Choose from multiple options in deck type, size, handles, casters, running gear patterns, bumpers and wheel locks
- Decks are 4/4 (7/8" thick)
- Shipped completely assembled and ready to use
- Casters are bolted on for easy replacement



features



Removable crossbar handle



Hardwood deck with tongue and groove construction



Bolt heads are countersunk and secured with lock nuts for a smooth working surface



Heavy-duty casters



How to Order in 7 Easy Steps!

step 1 pick a deck size

Deck sizes

- 24" x 48" • 27" x 54"
- 30" x 60" • 36" x 72"

step 2 pick a deck style (series 1 or 2)

Styles

Series 1 – All Wood

- Standard with removable lattice pipe handle at swivel end
- Two swivel, two rigid casters
- See caster options for capacity

Series 2 – Wood Deck with Steel Frame


- 2" x 2" x 1/8" welded steel angle frame keeps cart square (On 36" x 72" deck, 2" x 2" x 3/16")
- Heavy-duty steel frame for additional deck support
- Standard with removable lattice pipe handle at swivel end
- The wood deck is reinforced with longitudinal stiffeners for maximum capacity. (See caster options for capacity)
- Two swivel, two rigid casters

step 3 pick superstructure (A-D)

Superstructure

Open pipe handle

Crossbar handle



step 4 pick running gears

Rigid caster

Swivel caster


4 Four Swivel

5 Two Rigid Two Swivel

6 Tilt

7 Tilt Quad

step 5 pick caster type & size



Casters & Wheels

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 61 for more caster and wheel information.

step 6 create your model number

Call your Akro-Mils distributor with your model number today to order

model #	step 1	step 2	step 3	step 4	step 5	step 6
Platform Truck	Size	Series	Super-structure	Running Gear Type	Caster Wheel	Caster Wheel Diameter
RPT	2448 2754 3060 3672	1 2	A B C D	4 5 6 7	P M Y N R S	5 6 8 10
RPT	3060	2	A	5	P	6



Platform Trucks *Steel*

mobile systems & work centers

- Heavy-duty steel trucks with longitudinal steel underdeck reinforcements
- Standard two swivel, two rigid casters
- Special-order platform trucks are available. See page 54 to select from multiple options in handles, casters and running gears (Special-order products are not returnable)

- Caster options allow 800 to 2,200 lbs. capacity
- Casters are bolted on for easy replacement



HEavy-DUty DECK SIZES

- 24" x 36" • 30" x 48" • 36" x 60"
- 24" x 48" • 30" x 60" • 36" x 72"
- 24" x 60"
- 27" x 54"

Specify size when ordering



Standard crossbar handle



features



Durable powder-coated finish



Smooth, 13-gauge steel deck and frame



Steel reinforcements run lengthwise under the deck



Heavy-duty industrial casters

Platform Trucks – Steel

Model No.	Description	Caster Type*	Inches	
			Caster Size	Deck Height
R2108FPB	Steel Platform	Full Pneumatic	8 x 2	1200
R2125MRB	Steel Platform	Mold-On Rubber	5 x 2	1200
R2168MRB	Steel Platform	Mold-On Rubber	8 x 2	2000

*See page 61 for full description of casters and wheels



Platform Trucks *Super-Heavy-Duty*

- Super-heavy-duty wood deck steel frame trucks
- Steel C-channel underdeck reinforcements
- Capacity – 1,200 to 4,000 lbs. depending on caster type

- High deck for minimum bending
- Load wheels on solid steel axle



Standard crossbar handle

Casters & Wheels

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 61 for more caster and wheel information.

accessories for either Steel or Super-Heavy-Duty




Floor Locks



Wheel Locks



Corner Bumpers



Continuous Bumpers

Platform Trucks – Super-Heavy-Duty Steel

Model No.	Description	Caster Type*	Inches	
			Caster/Wheel Size	Deck Height
R2178MRB	Wood Deck Steel Frame	Mold-On Rubber	8 x 2	2000
R219885MRB	Wood Deck Steel Frame	Mold-On Rubber	8 x 2 / 8 x 2½	2500
R221812MRB	Wood Deck Steel Frame	Mold-On Rubber	8 x 2 / 12 x 2½	3000
R2258516MRB	Wood Deck Steel Frame	Mold-On Rubber	8 x 2½ / 16 x 3	4000

*See page 61 for full description of casters and wheels

SUPER-HEavy-DUty DECK SIZES

- 24" x 48" • 30" x 60"
- 30" x 48" • 36" x 72"

Specify size when ordering

Platform Trucks *Work Height – Heavy-Duty*

mobile systems & work centers

- Ergonomic height reduces the strain of lifting and bending
- Welded tubular steel frame supports heavy loads
- Fixed and adjustable heights available
- Two deck sizes available: 24" x 48" and 30" x 60"
- Hardwood, steel or structural foam deck available
- Hardwood deck features tongue and groove design
- Heavy-duty structural foam will not splinter, chip or rot
- Steel frame features durable, powder-coated finish
- Optional expanded metal or solid steel lower shelf



features




Powder-coated welded steel frame – special colors available



Tubular Steel Frame

accessories



Expanded Metal Shelf



Optional Corner Bumper

Platform Trucks - Fixed Work Height - Tubular Steel Frame


Model No.	Deck Type	Inches			Caster Type*	Inches	
		L	W	H		Caster Size	Weight Capacity (lbs.)
RWHV24481A5M8	Wood	24	48	26%	Mold-On Rubber	8	1800
RWHV24481A5M8	Structural Foam	24	48	26%	Mold-On Rubber	8	1800
RWHV24481A5Y6	Structural Foam	24	48	24%	Polyurethane	6	2000
RWHS24481A5M8	Steel	24	48	25¼	Mold-On Rubber	8	1800
RWHS24481A5Y6	Steel	24	48	23¼	Polyurethane	6	1800
RWH30601A5M8	Wood	30	60	26%	Mold-On Rubber	8	1800
RWHV30601A5M8	Structural Foam	30	60	26%	Mold-On Rubber	8	1800
RWHV30601A5Y6	Structural Foam	30	60	24%	Polyurethane	6	2000
RWHS30601A5M8	Steel	30	60	25¼	Mold-On Rubber	8	1800
RWHS30601A5Y6	Steel	30	60	23¼	Polyurethane	6	1800

* See page 61 for full description of casters and wheels

Platform Trucks - Adjustable Work Height - Tubular Steel Frame

Model No.	Deck Type	Inches			Caster Type*	Inches	
		L	W	H		Caster Size	Weight Capacity (lbs.)
RWH24481A5M8A	Wood	24	48	26¼ to 32¾	Mold-On Rubber	8	1800
RWHV24481A5M8A	Structural Foam	24	48	27½ to 33½	Mold-On Rubber	8	1800
RWHV24481A5Y6A	Structural Foam	24	48	25½ to 31½	Polyurethane	6	2000
RWHS24481A5M8A	Steel	24	48	25% to 32	Mold-On Rubber	8	1800
RWHS24481A5Y6A	Steel	24	48	23% to 32	Polyurethane	6	1800
RWH30601A5M8A	Wood	30	60	26¼ to 32¾	Mold-On Rubber	8	1800
RWHV30601A5M8A	Structural Foam	30	60	27½ to 33½	Mold-On Rubber	8	1800
RWHV30601A5Y6A	Structural Foam	30	60	25½ to 31½	Polyurethane	6	2000
RWHS30601A5M8A	Steel	30	60	25% to 32	Mold-On Rubber	8	1800
RWHS30601A5Y6A	Steel	30	60	23% to 32	Polyurethane	6	1800

* See page 61 for full description of casters and wheels



Hardwood Deck



Structural Foam Deck



All-Steel Deck

Casters & Wheels

Caster & Wheel choices allow you to resolve problems of noise control, floor protection, impact or abrasion resistance, or load capacity. See page 61 for more caster and wheel information.



Platform Trucks *Work Height – Standard Duty*

mobile systems & work centers

- Ergonomic height reduces the strain of lifting and bending
- Fixed and adjustable heights available
- Two deck sizes available: 24" x 48" and 30" x 60"
- Hardwood, steel or structural foam deck available
- Optional expanded metal lower shelf



Angle Iron Frame



Platform Trucks - Fixed Work Height - Angle Iron Frame

Model No.	Deck Type	Inches			Caster Type*	Inches	
		L	W	H		Caster Size*	Weight Capacity (lbs.)
RWH2448EA5M6	Wood	24	48	24½	Mold-On Rubber	6	1500
RWHV2448EA5M6	Structural Foam	24	48	24¾	Mold-On Rubber	6	1500
RWHS2448EA5M6	All-Steel	24	48	22	Mold-On Rubber	6	1500
RWH3060EA5M6	Wood	30	60	24½	Mold-On Rubber	6	1500
RWHV3060EA5M6	Structural Foam	30	60	24¾	Mold-On Rubber	6	1500
RWHS3060EA5M6	All-Steel	30	60	22	Mold-On Rubber	6	1500

* See page 61 for full description of casters and wheels

Platform Trucks - Adjustable Work Height - Angle Iron Frame

Model No.	Deck Type	Inches			Caster Type*	Inches	
		L	W	H		Caster Size*	Wt. Capacity (lbs.)
RWH2448EA5M6A	Wood	24	48	24½ to 30½	Mold-On Rubber	6	1500
RWHV2448EA5M6A	Structural Foam	24	48	24¾ to 30¾	Mold-On Rubber	6	1500
RWHS2448EA5M6A	All-Steel	24	48	22 to 28	Mold-On Rubber	6	1500
RWH3060EA5M6A	Wood	30	60	24½ to 30½	Mold-On Rubber	6	1500
RWHV3060EA5M6A	Structural Foam	30	60	24¾ to 30¾	Mold-On Rubber	6	1500
RWHS3060EA5M6A	All-Steel	30	60	22 to 28	Mold-On Rubber	6	1500

* See page 61 for full description of casters and wheels



Skids *Semi-Live*

mobile systems & work centers

- Tongue and groove hardwood deck
- Temporary storage and transport of raw materials and finished goods
- Lift Jack available for easy transport of most semi-live skids
- Can be used with a forklift or handjack



Deck Sizes

Semi-Live Skids 2 Wheels
Standard

- 24" x 48"
- 30" x 60"

Specify size when ordering


Semi-Live Skids – 2 wheels

Model No.	Description	Caster Type*	Inches	
			Caster Size	Weight Capacity (lbs.)
RA778MR	Tongue & Groove Hardwood Deck	Mold-On Rubber	8	2200
RA756MR	Tongue & Groove Hardwood Deck	Mold-On Rubber	6	1800

Lift Jacks

Model No.	Description	Handle Style	Inches	
			Caster Type*	Caster Size
RM718MR‡	Male Lift Jack	(T) or (Loop)	Mold-On Rubber	8
RF718MR‡	Female Lift Jack	(T) or (Loop)	Mold-On Rubber	8

* See page 61 for full description of casters and wheels ‡ - Specify Handle Style (T) or (Loop) when ordering



Lift Jacks

- For easy transport of most semi-live skids
- Specify "T" or loop handle style
- For female socket, change Model No. prefix to "RF"
- Pipe is 43" long



Portable Tables & Carts

mobile systems & work centers

- Durable carts for pulling stock, assembly operations or other heavy tasks
- Welded steel frame construction with soft rubber casters for easy maneuverability
- Overall height: 36"
- Ships completely assembled and ready-to-use
- 800 lb. capacity with recommended casters



RMD2ST5SR w/ optional drawer

- 5" x 1¼" soft rubber casters
- Shelf spacing
- 16-gauge steel
- 2" hemmed lip



RMD2ST5SR w/ optional writing shelf

accessories




Drawer:

Easily accessible storage drawer. 15½"W x 5½"H x 16½"D O.D.



Writing Shelf:

Handy, angled-shelf with pencil edge



Rubber Matting:

For all standard size shelves



Wheel Locks:

Control truck movement and prevent wheels from turning. Available on all wheels. Normal installation on two swivel wheels

features

portable tables & carts features



Angle posts for added strength and rigidity



Tubular push handle – MD series only



Powder-coated finish resists wear

Portable Tables

Model No.	Weight Capacity (lbs.)	Caster	Shelves	Height (Inches)	Shelf Clearance (Inches)	Handle	Cart Size (Inches)
RMD2ST5SR	800	2 Swivel / 2 Rigid	2	36	27	Tubular	24 x 36
RMD3ST5SR	800	2 Swivel / 2 Rigid	3	36	12½	Tubular	24 x 36



Mobile Work Tables *Heavy-Duty*



RHWB2448P5PY0G

- Industrial-grade mobile workstation with a welded-steel frame and steel-reinforced premium oak top – ships fully assembled
- 24" L x 48" W work area with 9 adjustable height settings from 36" x 48"
- 5" x 2" bolted on polyurethane casters; two rigid, two swivel with total lock brakes
- Wraparound steel backstop keeps items from falling behind work table
- Gray powder-coated finish

features




Hardwood work surface extends 2" to accommodate vise or clamps



Hardwood work surface with premium 1¼" (5/4) thick oak boards and rounded edges



21" D x 36" W bottom shelf



13½" D x 37" W, tilted middle shelf for easy access to bins



Mobile Work Tables *Medium-Duty*



RMWB24485SRTPG

- Industrial-grade work table with steel-reinforced hardwood top – ships fully assembled
- 24" L x 48" W x 36" H
- 2 steel drawers – 15½" W x 5½" H x 16½" D
- 2 swivel, 2 rigid bolted-on soft rubber casters; 5" x 1¼" total lock brakes on swivel casters
- Optional butcher block top available
- Gray powder-coated finish




Heavy-Duty Work Benches


mobile systems & work centers



features




11-gauge steel work surface extends 1/2" on front and sides to accommodate a vise or clamps (Hardwood extends 2")




Wraparound steel backstop keeps items from falling behind work bench



Adjustable work height telescoping C-channel legs provide a range of work heights from 30" - 40"



12-gauge welded steel shelves



13 1/2" deep middle shelf is sloped for easy access to bins or containers



Anchor pads on each leg secure bench in a fixed position

- Heavy-duty, steel frame work bench
- Steel, premium hardwood, butcher block or composition work surface
- 34" fixed or adjustable work heights
- Bench sizes: 30" x 60" and 30" x 72"
- Gray powder-coated finish


Work Surface Thickness

Wood - 2 1/4"
 Butcher Block - 1 3/4"
 Composition - 1 3/4"



How to order create your model number

Example: For an adjustable height 30" x 60" gray frame work bench with a hardwood work surface, your model number would be RHWB3060GA1P



H-D Work Bench	Size	Frame Color	Height Style	Shelf Options	Work Surface
RHWB	3060 3072	G (gray)	F (fixed) A (adjustable)	1 (Both shelves forward) 2 (Both shelves back) 3 (Middle fwd, Bottom back) 4 (Middle back, Bottom fwd)	S (Steel) P (Hardwood) B (Butcher Block) C (Composition)
RHWB	3060	G	A	1	P

example

RHWB3060GA1P

Call your Akro-Mils distributor with your model number to order



Akro-Tilt Trucks

waste transport systems

- Lightweight tipping trucks for heavy-weight jobs
- Caster wheel has roller bearings for extra stability when pushing, pulling or turning
- Handle is arc welded and reinforced for optimum durability
- Wrap-around tubular frame is constructed of 1" or 1¼" powder-coated steel for enhanced appearance and rust protection
- All trucks available in: Gray

Trucks tip for easy manual emptying



Akro-Tilt Trucks		Inches			Inches		Capacity		
Model No.	Description	W	D	H	Wheel Diameter	Wheel Type*	Gallons	Cu. Yds.	Load Rating
77405	Medium-Duty 100	27	54	36	12	SP	100	½	600 lbs.
77410	Medium-Duty 200	33	66	42	12	SP	200	1	600 lbs.
77505	Heavy-Duty 100	27	54	36	10	MR	100	½	1000 lbs.
77510	Heavy-Duty 200	33	66	42	10	MR	200	1	1000 lbs.
77610	Super Heavy-Duty 200	33	66	42	12	MR	200	1	2000 lbs.
77710	Heavy-Duty 300	39	85	51	12	MR	300	1½	2000 lbs.
77810	Heavy-Duty 400	48	85	51	12	MR	400	2	2000 lbs.

*SP = Semi-Pneumatic MR = Mold-On Rubber



Akro-Carts



- Medium-duty and heavy-duty styles to fit your needs
- Latch bars extend around the frame for added strength
- Wide mouth and low profile for easy loading
- All carts available in Gray, Blue and Green. All lids are Black



Heavy-duty piano hinge keeps lid propped open during use

Akro-Carts		Inches					
Model No. without Lid*	Model No. with Lid	Description	W	D	H	Load Rating	
76460	76461	Medium-Duty 60 Gal. Cap.	30½	48	33½	300 lbs.	
76490	76491	Medium-Duty 90 Gal. Cap.	30½	47	39½	350 lbs.	
76590	76591	Heavy-Duty 90 Gal. Cap.	30½	47	39½	450 lbs.	

Please specify colors when ordering.

*Carts without lids cannot have lids added after production. Single units are shipped completely assembled. When multiple units are ordered, lids are shipped separately and require assembly.



MegaKart®



- 96-gallon carts designed for residential waste management
- Compatible with automated and semi-automated systems
- Attached lid swings out of the way for easy dumping
- Injection-molded for exceptional durability and cost effectiveness
- Resists damage from oil and most chemicals
- Engineered for rigidity and strength



Patented design allows carts to nest with installed lids and latchbars for compact shipping and storage

MegaKart®		Inches			Inches		
Model No.	Capacity Gallons	W	D	H	Colors	Wheel Diameter	Load Rating
79596	96	28	32	46	Blue, Green	12	335 lbs.

Please specify colors when ordering.



Foot Tilt Pocket molded above axle for maximum leverage and utility



Materials Definitions & Benefits

material definitions & benefits

Each resin has properties that make it ideal for a specific purpose. We manufacture our plastic products using the grade most suited to the product's end use. Listed below are the quality resins we use and their attributes. NOTE: The "Use Temperature Range" defined below is dependent, and may vary with the end user's application. Akro-Mils reserves the right to change product materials without notice.

Polystyrene (GPS) – General Purpose Styrene:

- Water Clear in Clarity
- Surface Finish – High Gloss
- Highly Rigid Material
- Low Resistance to Impact
- Chemical/Abrasion Resistance – Low
- Use Temperature Range -30° to 115° F

High-Density Polyethylene (HDPE):

- Opaque
- Surface Finish – High Gloss
- Moderately Rigid Material
- Highly Resistant to Impact
- Chemical Resistance – High Below 140°
- Abrasion Resistance – High
- Use Temperature Range -40° to 140° F

High-Impact Polystyrene (HIPS):

- Opaque
- Surface Finish – Satin
- Highly Rigid Material
- Highly Resistant to Impact
- Chemical Resistance – Low
- Abrasion Resistance – Low to Medium
- Use Temperature Range -30° to 180°

Polypropylene (PP) – Block Copolymer; High Impact:

- Opaque
- Surface Finish – Medium to High Gloss
- Moderately Rigid Material
- Highly Resistant to Impact
- Chemical Resistance – High Below 175° F
- Abrasion Resistance – Medium
- Use Temperature Range -20° to 150° F

Recycled Polypropylene (PP):

- Opaque
- Surface Finish – Medium to High Gloss
- Moderately Rigid Material
- Mildly Resistant to Impact
- Chemical Resistance – High Below 175° F
- Abrasion Resistance – Moderate
- Use Temperature Range -0° to 150° F

Acrylic Blend Material:

- Water Clear in Clarity
- Surface Finish – High Gloss
- Rigid Material
- Medium Resistance to Impact
- Chemical Resistance – Medium
- Abrasion Resistance – Medium
- Use Temperature Range -20° to 180° F

Acrylonitrile Butadiene Styrene (ABS):

- Opaque
- Surface Finish – High Gloss
- Highly Rigid Material
- Highly Resistant to Impact
- Chemical Resistance – Medium
- Abrasion Resistance – Medium
- Use Temperature Range -40° to 180° F

Polypropylene (PP) – Random Copolymer; Medium Impact:

- Relatively Clear
- Surface Finish – High Gloss
- Moderately Rigid Material
- Mildly Resistant to Impact
- Chemical Resistance – High Below 175°
- Abrasion Resistance – Moderate
- Use Temperature Range 0° to 150° F

ESD Materials:

- Highest Degree of Electrostatic Discharge Protection with Uniform Surface Resistivities in the Static Dissipative Range of 10⁶ to 10⁹ ohms/sq.
- Use Temperature Range -20° to 150° F

Structural Foam:

- Plastic and Nitrogen Gas Form a Cellular Core
- Withstands Heavy Loads and Abuse
- HDPE – Use Temperature Range -20° to 120° F
- HIPS – Use Temperature Range -20° to 160° F

FDA-Approved Materials:

- We use FDA materials for NSTs, Grid Boxes and Akro-Tubs, as well as Straight Wall Containers
- Other Products produced in FDA-compliant materials only available with Custom Orders

Linear Low Density Polyethylene (LLDPE):

- Highly Flexible
- Highly Resistant to Impact
- Chemical Resistance – Moderate
- Corrosion Resistance – High
- Use Temperature Range -55° to 170° F



Casters & Wheels

material definitions & benefits

A generous selection of caster and wheel options allows Platform Trucks, Hand Trucks, Dollies and Shelf Carts to be customized to fit hundreds of applications, surfaces and conditions. Caster and wheel choices allow you to resolve problems of noise control, floor protection, impact and abrasion resistance or load capacity.



Mold-On Rubber

Designed for medium to heavy loads, these wheels with cushioned rubber tread are quiet and provide good floor protection.



Pneumatic

Air-filled for excellent shock protection, floor protection and easy operation over rough surfaces.



Polyurethane

Chemically bonded to a metal core, polyurethane wheels are more durable than other materials, deliver excellent mobility, a cushioned ride and long life when subjected to heavy loads.



Phenolic

For demanding applications, a less expensive wheel that offers high strength, is non-marking, non-conductive and protects floors.



Polyolefin

A heavy-duty, lightweight, non-marking plastic wheel that resists most chemicals and oils, and has excellent impact resistance.



Steel

Wheels offer least rolling resistance. A good choice for warehouses and manufacturing operations and where noise or floor protection are not a concern.



Thermo-Plastic

Gray rubber wheel provides excellent floor protection and a cushioned ride while resisting chemicals, acids, oils and caustic substances.

Caster Composition	Floor Surface				Floor Coverings				Other Factors To Consider							
	Asphalt	Brick/Ceramic Tile	Carpet	Concrete	Linoleum – Non-Marking	Steel Grates/Dock Plate	Chemicals	Metal Shavings	Oil & Grease	Water & Steam	Floor Protection	Noise	Cushion Load	Impact Resistance	Capacity	Rolling Ease
Standard Caster/Wheels																
Polyolefin	NR	NR	G	E	G	NR	G	F	G	E	G	F	NR	G	G	E
Mold-On Rubber	E	E	NR	E	NR	F	NR	NR	F	G	G	E	E	E	G	F
Pneumatic	E	E	NR	E	NR	E	NR	NR	F	G	G	E	E	E	F	NR
Steel	NR	NR	NR	E	NR	NR	F	E	G	F	NR	F	NR	NR	E	E
Polyurethane	E	E	G	E	E	F	G	G	G	G	E	E	G	E	E	G
Phenolic	NR	NR	G	E	G	NR	F	NR	F	F	G	F	NR	F	E	E
Thermo-Plastic	E	E	G	E	E	G	E	G	E	G	E	E	E	E	G	G



Caster Types Akro-Mils offers other premium casters for your custom products – call 800-253-2467 for details.

Model Nos.	Pg No.				
02420	35	30210RECY	6	30553235S	10
05705	35	30211	5, 6	30553LF	10
05805	35	30220	5	30600BRACKET	25
05905	35	30220ESD	23	30600DOLLY	25
06115	35	30220RECY	6	30618	9, 11
06118	35	30221	5, 6	30636	9, 11
06217	35	30224	5	30638	9
09185BLUE	35	30230	5	30651	9
10116	34	30230ESD	23	30653	9
10124	34	30230RECY	6	30661	9
10126	34	30231	5, 6	30676	9
10144	34	30234	5	30716BLACK	23
10164	34	30235	5	30718BLACK	23
13014	28	30235ESD	23	30776BLACK	23
13017	28	30236	5	30778BLACK	23
13018	28	30239	5	30796BLACK	23
17018	34	30240	5	30812	8
17136	34	30240ESD	23	30930	45
19109	34	30240RECY	6	30936	45
19228	34	30250	5	31142	16
19320	34	30250RECY	6	31162	16
19416	34	30255	5	31168	16
19715	34	30260	5	31182	16
19909	34	30265	5	31188	16
20228	34	30270	5	31620	25
20320	34	30280	27	31625	25
20416	34	30281	27	31625RACK	25
20502	34	30282	27	33101	30
20715	34	30283	27	33105	30
20902	34	30284	27	33161	30
20909	34	30286	27	33164	30
21280	27	30287	27	33166	30
21281	27	30288	27	33168	30
21282	27	30289	27	33220	30
21283	27	30290	27	33221	30
21284	27	30292	27	33224	30
21286	27	30293	27	33226	30
21287	27	30312	24	33228	30
21288	27	30318	24	34240	33
21289	27	30320	5	34301	33
30008	8	30321	5	34302	33
30016	8	30330RED	7	34303	33
30040	13	30348BEIGE	23	34304	33
30048	13	30358BEIGE	23	35010	29, 30
30080	13	30400GRY10PK	22	35011	29, 30
30088	13	30400WHI10PK	22	35180	29
30090	13	30400YEL10PK	22	35181	29
30094	13	30420GRY6PK	22	35185	29
30098	13	30420WHI6PK	22	35190	29
30101	12, 14	30424	8	35191	29
30102	12, 14	305A1	11	35195	29
30110	12	305A2	11	35200	29
30118	9	305A3	11	35201	29
30120	12	305A4	11	35225	29
30120RECY	14	305A5	11	35230	29
30124	12	305A6	11	35231	29
30124RECY	14	305B1	11	35240	29
30128	12	305B2	11	35241	29
30128RECY	14	30536	10	35300	29
30130	12	30536A1	11	35301	29
30130RECY	14	30536A3	11	35R	49
30138	12	30536A5	11	36442BLUE	21
30138RECY	14	30536B1	11	36462BLUE	21
30148	8	30536210S	10	37208	32
30150	12	30536220S	10	37278	32
30158	12	30536230S	10	37288	32
30161	9	30536235S	10	37608	32
30164	12	30536320S	10	37612	32
30164RECY	14	30553	10	37616	32
30170	12	30553A1	11	37672	32
30174	12	30553A3	11	37676	32
30178	12	30553A5	11	37678	32
30184	12	30553B1	11	37682	32
30210	5	30553210S	10	37686	32
30210ESD	23	30553220S	10	37688	32
		30553230S	10	39085	31
				39120	31
				39160	31
				39170	31
				39175	31
				39280	31
				3P	49
				3R	49
				40020	13
				40030	13
				40040	13
				40120	12, 14, 21
				40130	12, 14, 21
				40150	12
				40170	12
				40210	5, 6
				40220	5, 6
				40228	34
				40230	5, 6
				40239	5
				40245	5, 6
				40260	5
				40265	5
				40270	5
				40280	27
				40281	27
				40282	27
				40286	27
				40287	27
				40289	27
				40290	27
				40292	27
				40312	24
				40320	34
				40321	5
				40330	7
				403302PK	7
				40348	23
				40358	23
				40410	12, 14
				40416	34
				40420	22
				40445	12, 14
				405A1	11
				405A3	11
				405A5	11
				405B1	11
				40501	34
				40715	34
				40716	34
				40717	34
				40901	34
				40909	34
				41105	30
				41164	30
				41166	30
				41168	30
				41220	30
				41224	30
				41226	30
				41228	30
				41284	27
				41286	27
				41287	27
				41288	27
				41289	27
				41440	16
				41460	16
				41480	16
				415A1	11
				415B1	11
				42105	30
				42164	30
				42166	30
				42168	30
				42220	30
				42224	30
				42226	30
				42228	30
				4P	49
				4R	49
				4Rx	49
				5P	49
				5R	49
				76460	60
				76461	60
				76490	60
				76491	60
				76590	60
				76591	60
				77405	60
				77410	60
				77505	60
				77510	60
				77610	60
				77710	60
				77810	60
				79596	60
				98100	23
				98536	10
				98536210SD	10
				98536210SS	10
				98536220SD	10
				98536220SS	10
				98536230SD	10
				98536230SS	10
				98536235SD	10
				98536235SS	10
				98536320SD	10
				98536320SS	10
				98600	9, 11
				98636	9




A

AC3618	44
AC3618QV	44
AC3618QV240	44
AC3618QV250	44
AC3618SV	44
AC3618SV240	44
AC3618SV250	44
AC3618Y	44
AC3624	44
AC36243AS	44
AC3624Y	44
AC3624Y3AS	44
AC803618M26	44
AC803624M26	44
ACQV4C	19
ACQV4C42	19
ACQV4C62	19
ACQV4C82	19
ACQV4CAST	19
ACQV4P	19
ACQV4P42	19
ACQV4P62	19
ACQV4P82	19
ACQV4PAST	19
ACS4C	19
ACS4C42	19
ACS4C62	19
ACS4C82	19
ACS4CAST	19
ACS4P	19
ACS4P42	19
ACS4P62	19
ACS4P82	19
ACS4PAST	19
AD1811C	17
AD1811C62	17
AD1811C82	17
AD1811CAST	17
AD1811P	17
AD1811P62	17

AD1811P82.....	17	AS1279.....	41	AWS1836SNS.....	38	R3008MR.....	51	RD854SS.....	50
AD1811PAST.....	17	AS1279040.....	42	AWS184813017.....	38	R3010FP.....	51	RDT4008SP.....	52
AD1817C.....	17	AS1279080.....	42	AWS184830260.....	38	R3010SP.....	51	RDT4010FP.....	52
AD1817C68.....	17	AS1279090.....	42	AWS184830280.....	39	R3ST5HR.....	47	RDT4010SP.....	52
AD1817C88.....	17	AS1279110Y.....	41	AWS184830281.....	39	R4008MR.....	51	RF718MR.....	57
AD1817CAST.....	17	AS1279120Y.....	41	AWS184830282.....	39	R4008MR2.....	51	RGTD10FP.....	51
AD1817P.....	17	AS1279130Y.....	41	AWS184830283.....	39	R4010FP.....	51	RGTD10SP.....	51
AD1817P68.....	17	AS1279150Y.....	41	AWS1848SAB.....	39	R4010FP2.....	51	RGTS10FP.....	51
AD1817P88.....	17	AS1279170Y.....	41	AWS24360284.....	39	R4010SP.....	51	RGTS10SP.....	51
AD1817PAST.....	17	AS1279312.....	24, 41	AWS24360287.....	39	R4010SP2.....	51	RM718MR.....	57
AD2311C.....	17	AS127936442B.....	42	AWS24360288.....	39	R4510SP.....	51	RMD2ST5SR.....	58
AD2311C42.....	17	AS127936462B.....	41	AWS24360SAB.....	39	R4510SP2.....	51	RMD3018F4PN.....	50
AD2311C62.....	17	AS1879.....	42	AWS24361288.....	39	R4ST5HR.....	47	RMD3018F4RX.....	50
AD2311CAST.....	17	AS1879048.....	42	AWS244830124.....	38	R4ST8MR.....	47	RMD3018FN.....	50
AD2311P.....	17	AS1879088.....	42	AWS244830164.....	38	R5ST5HR.....	47	RMD3018RC4PN.....	50
AD2311P42.....	17	AS1879094.....	42	AWS244830174.....	38	R5ST8MR.....	47	RMD3018RC4RX.....	50
AD2311P62.....	17	AS1879098.....	42	AWS244830184.....	38	R5SYT5HR2436.....	24, 47	RMD3018RCN.....	50
AD2311P82.....	17	AS1879098.....	42	AWS244830184.....	38	R5SYT5HR3636.....	24, 47	RMD3ST5SR.....	58
AD2311PAST.....	17	AS1879128Y.....	42	AWS244830420.....	39	R5SYT8MR2436.....	24, 47	RPT4010SP.....	52
AD3511BS.....	18	AS187913014.....	42	AWS244837608.....	39	R5SYT8HR3636.....	24, 47	RU843HR.....	50
AD3511C.....	18	AS187913017.....	42	AWS246035225.....	39	R90110.....	53	RU843HR1519.....	28
AD3511C42.....	18	AS187913018.....	42	AWS2460M30358.....	39	R90162.....	53	RU843HR1617.....	28
AD3511C62.....	18	AS1879138Y.....	42	AWS2460M33224.....	38	R90163.....	53	RU843HR2018.....	27
AD3511C82.....	18	AS1879158Y.....	42	AWS2460M34240.....	39	R90181.....	53	RU843HR2918.....	27
AD3511CAST.....	18	AS1879178Y.....	42			R90182.....	53	RU843SS.....	50
AD3511P.....	18	AS1879318.....	24, 42	H		R90184.....	53	RU843TP1721.....	27
AD3511P42.....	18	AS187936.....	42	HD4824A.....	43	R90185.....	53	RU843TP1727.....	27
AD3511P62.....	18	AS187942.....	42	HD4824E.....	43	R90210.....	53	RU843TP1821.....	27
AD3511P82.....	18	AS1879ASORT.....	42	HD4824F.....	43	R90262.....	53	RU843TP2122.....	27
AD3511PAST.....	18	AS2479.....	42			R90263.....	53	RU843TP2227.....	27
AD3517BS.....	18	AS2479284.....	42	M		R90281.....	53	RU844HR.....	50
AD3517C.....	18	AS2479287.....	42	MA3618C.....	46	R90282.....	53	RU844SS.....	50
AD3517C68.....	18	AS2479288.....	42	MA3618CAST.....	46	R90284.....	53	RU853HR.....	50
AD3517C88.....	18	AS2479288.....	42	MA3618P.....	46	R90285.....	53	RU853SS.....	50
AD3517CAST.....	18	AS2479ASSORT.....	42	MA3618PAST.....	46	R92411.....	53	RU854HR.....	50
AD3517P.....	18	AS3679.....	42	MA4824C.....	46	R92412.....	53	RU854SS.....	50
AD3517P68.....	18	AS3679292.....	42	MA4824C1.....	46	R9255HR.....	52	RWH24481A5M8.....	56
AD3517P88.....	18	AS3679293.....	42	MA4824C2.....	46	R93011.....	53	RWH24481A5M8A.....	56
AD3517PAST.....	18	AS3679ASSORT.....	42	MA4824P.....	46	R93012.....	53	RWH2448EA5M6.....	57
APRBENCH.....	15, 24	ASC1279.....	20	MA4824P1.....	46	R94817.....	53	RWH2448EA5M6A.....	57
APRBENCH040.....	15	ASC1279142.....	20	MA4824P2.....	46	R9508MR2.....	52	RWH30601A5M8.....	56
APRBENCH090.....	15	ASC1279162.....	20			R9510MR2.....	52	RWH3060EA5M6.....	57
APRBENCH120.....	15	ASC1279182.....	20	R		R96017.....	53	RWH3060EA5M6A.....	57
APRBENCH150.....	15	ASC1279AST.....	20	R1130.....	49	RA6TR4MR.....	33	RWH3060EA5M6A.....	57
APRD.....	15	ASC1879.....	20	R1151.....	49	RA756MR.....	57	RWHS24481A5M8.....	56
APRD040.....	15	ASC1879168.....	20	R1B5HR.....	48	RA778MR.....	57	RWHS24481A5M8A.....	56
APRD080.....	15	ASC1879188.....	20	R1B5HRL.....	48	RABR5338.....	42	RWHS24481A5Y6.....	56
APRD090.....	15	ASC1879AST.....	20	R1B5HRXL.....	48	RACR5MR.....	33	RWHS24481A5Y6A.....	56
APRD110Y.....	15	AWS143630040.....	39	R1S10FP2.....	47	RCT40LW.....	51	RWHS2448EA5M6.....	57
APRD120Y.....	15	AWS143630080.....	39	R1S5HR.....	47	RCTV40SP.....	51	RWHS2448EA5M6A.....	57
APRD130Y.....	15	AWS183630090.....	39	R1S5HR2LD.....	47	RD2416F3P.....	49	RWHS30601A5M8.....	56
APRD142.....	20	AWS143630102.....	38	R1S8FP2.....	47	RD2416R3P.....	49	RWHS30601A5M8A.....	56
APRD150Y.....	15	AWS143630110.....	38	R1S8MR.....	47	RD2416S3P.....	49	RWHS30601A5Y6.....	56
APRD162.....	20	AWS143630130.....	38	R1S8MR2.....	47	RD2718F3P.....	49	RWHS30601A5Y6A.....	56
APRD170Y.....	15	AWS143630170.....	38	R2108FPB.....	55	RD2718RC3P.....	49	RWHS3060EA5M6.....	57
APRD182.....	20	AWS143630240.....	38	R2125MRB.....	55	RD2718S3P.....	49	RWHS3060EA5M6A.....	57
APRDAST.....	20	AWS143630312.....	38	R214CS1841.....	27	RD3018AC3P.....	49	RWHV24481A5M8.....	56
APRDAST00.....	15	AWS143630320.....	38	R214CS1859.....	27	RD3018CE3P.....	49	RWHV24481A5M8A.....	56
APRDMOBILE.....	15	AWS143636442B.....	38	R214CS1878.....	27	RD3018F3P.....	49	RWHV24481A5Y6.....	56
APRD36442B.....	21	AWS143636462B.....	38	R214CS2841.....	27	RD3018R3P.....	49	RWHV24481A5Y6A.....	56
APRD36462B.....	21	AWS183613014.....	38	R214CS2859.....	27	RD3018RC3P.....	49	RWHV2448EA5M6.....	57
APRS.....	15	AWS183613018.....	38	R214CS2878.....	27	RD3018S3P.....	49	RWHV2448EA5M6A.....	57
APRS040.....	15	AWS183630048.....	39	R214HE.....	48	RD3624AC3P.....	49	RWHV30601A5M8.....	56
APRS080.....	15	AWS183630088.....	39	R215HE.....	48	RD3624CE3P.....	49	RWHV30601A5M8A.....	56
APRS090.....	15	AWS183630098.....	39	R2168MRB.....	55	RD3624F3P.....	49	RWHV30601A5Y6.....	56
APRS110Y.....	15	AWS183630128.....	38	R216CS2236.....	27	RD3624R3P.....	49	RWHV30601A5Y6A.....	56
APRS120Y.....	15	AWS183630138.....	38	R216CS2239.....	27	RD3624S3P.....	49	RWHV3060EA5M6.....	57
APRS130Y.....	15	AWS183630158.....	38	R216CS2836.....	27	RD4824F3P.....	49	RWHV3060EA5M6A.....	57
APRS142.....	20	AWS183630178.....	38	R2178MRB.....	55	RD4824S3P.....	49		
APRS150Y.....	15	AWS183630265.....	38	R219885MRB.....	55	RD843HR.....	50		
APRS162.....	20	AWS183630270.....	38	R221812MRB.....	55	RD843SS.....	50		
APRS170Y.....	15	AWS183630318.....	38	R2258516MRB.....	55	RD844HR.....	50		
APRS182.....	20	AWS183630400.....	39	R2ST5HR.....	47	RD844SS.....	50		
APRSAST.....	20	AWS183633166.....	38	R2T5HR1830.....	48	RD853HR.....	50		
APRSAST00.....	15	AWS183633168.....	38	R2T5HR2436.....	48	RD853SS.....	50		
APRS36442B.....	15	AWS183635180.....	39	R2T8MR2448.....	48	RD854HR.....	50		
APRS36462B.....	15	AWS1836M34301.....	39						

Ready, Set, Organize!™

Our broad range of durable plastic containers combined with metal cabinets, shelving and racks, will improve storage and organization efficiency, shorten assembly times and optimize parts protection. Akro-Mils will help you improve your productivity and your bottom line!



A. ProHANGER..... p. 7	G. Steel Shelving Systems p. 40-42	L. Platform Truck..... p. 56-57	Q. Akro-Grids p. 30	W. ReadySpace Wall Unit..... p. 10
B. Heavy-Duty Work Bench..... p. 59	H. Security Bin Cabinet p. 43-44	M. Storage-Go-Round p. 34	R. Wire Shelving Systems..... p. 36-39	X. Shelf Cart..... p. 47
C. Super-Size AkroBin Cart..... p. 27	I. Super Modular Cabinet p. 17	N. Roto-Shelf..... p. 35	S. Stak-N-Store Bins..... p. 28	Y. ReadySpace Bench Unit..... p. 10
D. Louvered Hanging Systems..... p. 9	J. System Bins p. 24	O. Single-Sided Louvered Floor Rack p. 9	T. Attached Lid Containers..... p. 31	Z. VantageBin p. 22
E. AkroBins..... p. 4-6	K. Double-Sided Louvered Floor Rack p. 9	P. ShelfMax Bins..... p. 13	U. Pick Rack with System Bins... p. 15	AA. 33" Wide AkroBin p. 4-5
F. Super-Size AkroBins..... p. 26-27			V. AkroDrawers p. 16-20	BB. Quick-View Mini Cabinet..... p. 19
				CC. ProCart..... p. 45



To learn more, contact us today: **800.253.2467**

1293 South Main Street, Akron, Ohio 44301 • www.akro-mils.com • Fax: 330.761.6348 • sales@akro-mils.com

In Canada: 8030 Torbram Road, Brampton, Ontario L6T 3T2 • Tel: 877.877.9680 • Fax: 905.791.4084 • sales@akro-milscanada.com