

MSI CX640-018UK 15.6 I5-2410M 4GB W7HP

- Product Group: Notebooks
- Manufacturer: MSI
- SKU: SB04663
- Product Name: MSI 15.6" Windows 7 Home Premium (i5 2410M/500GB/4GB DDR3/6 Cell/Geforce GT520M)
- Web Address: www.msi.com.tw
- Model Number: CX640-018UK
- Package Type: Retail
- Display: 15.6" HD (1366x768, 16:9, Glare Type)
- CPU: Intel Core i5 2410M (2.3GHz)
- Hard Drive: 500GB SATA
- Optical Drive: DVD Super Multi
- Memory Supplied: 2 x 2GB DDR3 1333
- Operating System: Microsoft Windows 7 Home Premium
- Memory Socket: 2 x SO-DIMM DDR3 1333
- Max. Memory Support: 8GB
- Graphics Chipset: NVIDIA Geforce GT520M
- Graphics Memory: 1GB DDR3
- Chipset: Intel HM65
- Speaker: 2 x Speakers
- Microphone: Built-in
- LAN: 10/100/1000
- Wireless NIC: Integrated IEEE 802.11 b/g/n
- Interface:
 - 1 x VGA
 - 1 x HDMI
 - 4 x USB 2.0 Ports
 - 1 x Microphone-in Jack
 - 1 x Line-in Jack
- Pointing Device: Built-in Touch Pad
- Battery Pack & Life: 6 cells
- Card Reader: MMC/SD/SDHC/SDXC/MS/MS Pro/HG
- Web Camera: 1.3 Megapixel
- Product Width: 380mm
- Product Height: 34mm
- Product Depth: 260mm
- Net Weight: 2.6Kg
- Gross Weight: 4.43Kg
- Package Contents:
 - Notebook
 - Battery
 - Driver and Utility CD
 - User Manual
 - Power Adaptor
 - Power Lead