


ALL MATERIAL ARE RoHS AND CALIFORNIA PROP.65 COMPLIANT

CUSTOMER'S APPROVAL: \_\_\_\_\_ DATE: \_\_\_\_\_

FIRST ARTICLE SAMPLE REQUIRED:  YES,  NO.



Farnell Code 1956245 - 2m; 1956246 - 3m; 1956247 - 6m;  
1956295 - 15m; 1956248 - 20m; 1956249 - 30m; 1956250 - 50m

| HD15 (90°) MALE | HD15 FEMALE                         |
|-----------------|-------------------------------------|
| 1               | Red Video                           |
| 2               | Green Video                         |
| 3               | Blue Video                          |
| 4               | Ground                              |
| 5               | Red Ground                          |
| 6               | Green Ground                        |
| 7               | Blue Ground                         |
| 8               | +5 VDC                              |
| 9               |                                     |
| 10              |                                     |
| 11              |                                     |
| 12              | DDC Serial Data Line                |
| 13              | Horizontal Sync (or Composite Sync) |
| 14              | Vertical Sync                       |
| 15              | DDC Data Clock Line                 |
| SHELL           | DRAIN+BRAID                         |
|                 | SHELL                               |

WIRE MARKING:  
VDC LONDON WWW.VDCTRADING.COM  
E193793 RJ AWM 2919 80°C 30V VW-1

UNIT: mm

| ITEM | DESCRIPTION   | QTY. | UNIT |
|------|---|------|------|
| 1    | HD15 MALE CONNECTOR   | 1    | PCS. |
| 2    | HD15 FEMALE CONNECTOR   | 1    | PCS. |
| 3    | PANTONE BLUE 072U MOLDED PVC HOOD W/VDC LOGO (90°)            | 1    | PCS. |
| 4    | PANTONE BLUE 072U MOLDED PVC HOOD W/VDC LOGO                  | 1    | PCS. |
| 5    | PANTONE BLUE 072U #4/40 THUMBSCREW                            | 1    | PCS. |
| 6    | BLUE #4/40 THUMBSCREW   | 2    | PCS. |
| 7    | PAT. NO.:US 6,287,148 B1 RF-BLOK™ SHIELDING METAL CAN         | 1    | PCS. |
| 8    | UL2919 (28AWG COAX+AL-FOIL+65%BRAID+INNER JACKET)x3C SEE DWG. | SEE  | DWG. |
|      | +(28AWG WIRE)x8C+AL-FOIL+DRAIN+BRAID OVERALL;                 |      |      |
|      | PANTONE BLUE 072U PVC JACKET                                  |      |      |

