

Philips
Sleek micro music system



MC235B

Obsessed with sound

Sound that fits your home

Trendy and progressive, unique innovation and style appeals to you. The vivid and chic Philips sleek micro music system, with dynamic sound performance, is packed in a sleek design that can also be wall mounted.

Enrich your sound experience

- Play CD, CD-R and CD-RW discs
- Digital Sound Control for optimised music style settings
- Dynamic Bass Boost for deep and dramatic sound
- 2 x 5 W RMS/2 x 10 W music power/400 W PMPO

Start the day your way

- Wake-up and sleep timer functions
- Digital tuning with 40 pre-set stations for extra convenience

Design that blends into your interior

- Wall-mountable option for flexible placement
- Motorised sliding front door adding style and elegance

PHILIPS
sense and simplicity

Specifications

Sound

- Output power: 2 x 5 W RMS, 2 x 10 W music power
- Sound enhancement: digital sound control 4 modes, Dynamic Bass Boost

Loudspeakers

- Speaker drivers: 3" woofer, Piezo tweeter
- Speaker types: bass reflex speaker system

Audio playback

- Playback media: CD, CD-R, CD-RW
- Disc playback modes: repeat/shuffle/programme

Tuner/Reception/Transmission

- Tuner bands: FM stereo, MW
- Station presets: 40
- Antenna: FM antenna, MW antenna
- Tuner enhancement: auto digital tuning, auto scan

Connectivity

- Audio/Video output: Headphone (3.5 mm)
- MP3 Link: 3.5 mm stereo line in

Convenience

- Alarms: CD alarm, radio alarm

- Backlight colour: Blue
- Loader type: front, motorised
- Clock: on main display, sleep timer
- Display type: LCD display

Accessories

- Remote control: 23-key with lithium battery
- User Manual: English
- Others: AM/FM antenna, Quick start guide, screws for wall mounting x 2, stand
- Guaranteed: Worldwide Guarantee booklet

Dimensions

- Gross weight: 5.3 kg
- Packaging width: 328 mm
- Packaging height: 313 mm
- Packaging depth: 300 mm
- Main speaker dimensions (W x D): 166 x 90 mm
- Main speaker height: 245 mm
- Main unit depth: 96 mm
- Main unit height: 245 mm
- Main unit width: 250 mm

Power

- Power supply: 50 Hz
- Power supply: 220 - 240 V

Highlights

Digital Sound Control

Digital Sound Control offers you a choice of pre-set Jazz, Rock, Pop and Classical controls you can use to optimise the frequency ranges for different musical styles. Each mode uses graphic equalizing technology to automatically adjust the sound balance and enhance the most important sound frequencies in your chosen music style. Ultimately, Digital Sound Control makes it easy for you get the most out of your music by precisely adjusting the sound balance to match the type of music you are playing.

Dynamic Bass Boost

Dynamic Bass Boost maximises your music enjoyment by emphasising the bass content of the music throughout the range of volume settings - from low to high - at the touch of a button! Bottom-end bass frequencies usually get lost when the volume is set at a low level. To counteract this, Dynamic Bass Boost can be switched on to boost bass levels, so you can enjoy consistent sound even when you turn down the volume.



Issue date 2011-09-23

Version: 2.1.9

12 NC: 8670 000 31337
EAN: 87 12581 34448 1

© 2011 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com