

External Micrometers



Pearl chrome finish with insulated pads. Complete with ratchet and locking lever. Cut-away frame to facilitate usage in narrow slots. All M&W micrometers detailed below can be supplied with either a standard steel spindle or tungsten carbide faced. Conform to BS870 DIN863/1.

Steel Anvils

488396

Capacity	Graduations	Order Code	Price Each
0-25mm	0.01mm	137-6762	
0-25mm	0.002mm	137-6763	
0-1in	0.001in	137-6764	
0-1in	0.0001in	137-6765	

Tungsten Carbide Anvils

Capacity	Graduations	Order Code	Price Each
0-1in	0.001in	443-098	
0-25mm	0.01mm	443-104	
0-1in	0.0001in	137-6766	
0-25mm	0.002mm	137-6845	