

Adjustable Micrometers



Enamelled frame. Complete with ratchet and locking lever. Setting gauges included. Range from two to six times greater than the fixed anvil type. Range is obtained by use of separate anvils. These anvils are located in a hardened and lapped bush. Conform to BS870 DIN863/1.

Metric

Graduations 0.01mm.

489383

Capacity(mm)	Setting Gauges	Anvils	Order Code	Price Each
0 - 50	1	2	137-6768	
0 - 100	3	4	137-6769	
50 - 150	4	4	137-6770	
100 - 200	4	4	137-6771	
0 - 150	5	6	137-6772	
150 - 300	6	6	137-6773	

Imperial

Graduations 0.001in.

Capacity(mm)	Setting Gauges	Anvils	Order Code	Price Each
0 - 2	1	2	137-6774	
0 - 4	3	4	137-6775	
2 - 6	4	4	137-6776	
0 - 6	5	6	137-6777	
6 - 12	6	6	137-6778	