

Straight Blade Devices
60 Ampere, 125/250 Volts, 3Ø 250 and 120/208 Volts AC
 3 Pole, 4 Wire Grounding and 4 Pole, 4 Wire Non-Grounding
 Single Receptacles and Plugs



60A, 125/250V
3 Pole, 4 Wire Grounding
Receptacles and Plugs

IP20
 SUITABILITY




60A 125/250V
NEMA 14-60R
 UL CSA
 3(2) HP



60A 125/250V
NEMA 14-60P
 UL CSA
 3(2) HP

| Description | Cord Diameter | Catalog Numbers |
|---------------------------------|-------------------------------|-------------------|
| Receptacle, black RTP. | - | HBL9460A - |
| Plug, nylon. | .625" - 1.310" (15.9-33.3) | - HBL9461C |
| Plug, nylon, angle, 4-position. | .625" - 1.310" (15.9-33.3) | - HBL9462C |



HBL9461C

60A, 3Ø 250V AC
3 Pole, 4 Wire Grounding
Receptacles and Plugs

IP20
 SUITABILITY




60A 3Ø 250V AC
NEMA 15-60R
 UL CSA
 10 HP




60A 3Ø 250V AC
NEMA 15-60P
 UL CSA
 10 HP

| Description | Cord Diameter | Catalog Numbers |
|---------------------------------|-------------------------------|-------------------|
| Receptacle, black RTP. | - | HBL8460A - |
| Plug, nylon. | .625" - 1.310" (15.9-33.3) | - HBL8461C |
| Plug, nylon, angle, 4-position. | .625" - 1.310" (15.9-33.3) | - HBL8462C |



HBL8462C


60A, 3ØY 120/208V AC
4 Pole, 4 Wire Non-Grounding
Receptacles and Plugs

IP20
 SUITABILITY




60A 3ØY
120/208V AC
NEMA 18-60R
 UL Listed
 7.5 HP



60A 3ØY
120/208V AC
NEMA 18-60P
 UL Listed
 7.5 HP

| Description | Cord Diameter | Catalog Numbers |
|---------------------------------|-------------------------------|-------------------|
| Receptacle, black RTP. | - | HBL7301A - |
| Plug, nylon. | .625" - 1.310" (15.9-33.3) | - HBL7303C |
| Plug, nylon, angle, 4-position. | .625" - 1.310" (15.9-33.3) | - HBL7302C |



HBL7301A

Note: See page A-47 for accessories.
 RTP is an abbreviation for reinforced thermoplastic polyester.