

**MARTINDALE**  
ELECTRIC

## Specification CB12 Checkbox



### Resistance Settings:

0.5 $\Omega$ , 1 $\Omega$ , 2 $\Omega$ , 20 $\Omega$ , 200 $\Omega$ , 1k $\Omega$ , 10k $\Omega$ , 20k $\Omega$ , 100k $\Omega$ , 1M $\Omega$ , 2M $\Omega$ , 10M $\Omega$

### Accuracy:

0.5 $\Omega$  - 2 $\Omega$   $\pm$  0.025 $\Omega$

20 $\Omega$  - 10M $\Omega$   $\pm$  2%

**Maximum Voltage Input:** 1000V DC

**Case:** Impact Resistant ABS