

List Price \$360.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

Application	Conveyor systems, packaging, textiles, transfer machines, presses, woodworking equipment, paint lines and test laboratories
Ampere Rating	10A
Contact Configuration	1 N.O./1 N.C.
Approvals	UL Listed File Number: E164353 CCN NKCR - CSA Certified File Number: LR44087 Class 3211 03 - CE Marked
Height	2.70 Inches
Reset Operator	Pushbutton
Orientation	Field Selectable
Connection Type	(3) 0.5 Inch NPT
Contact Operation	Slow Make - Slow Break
Contact Rating	A300 - Q300
Maximum Voltage Rating	300V
Depth	1.57 Inches
Enclosure Type	Water tight and Dust tight (Indoor/Outdoor)
Features	Emergency Stop (latching)
Mounting Type	Surface
Pilot Light	No
Terminal Type	Screw Clamp
Type	XY2
Cable Length	50 Feet (max)
Enclosure Rating	NEMA 1/4/12

Shipping and Ordering

Category	22441 - Limit Switches, Cable Pull, Type XY2
Discount Schedule	T
GTIN	00785901992639
Package Quantity	1
Weight	2.17 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.