

RCD Protection

RCD08MPV Valiance RCD Twin Metal - Passive

Shares all the features and benefits of the RCD07MAV **with the addition of latching (power is immediately restored to the appliance/equipment at the end of a power failure).**

- Supplied with a 40mm BS metal surface wall box.
- Provides two protected switched socket outlets for convenience and extra safety.
- Protects appliances from possible fire hazard.
- Manual reset.
- Extra fast action – trips out within 40 milliseconds (BS7288).
- Automatically disconnects both Live and Neutral connections leaving Earth connection intact.
- Remains latched when the power supply is temporarily lost. Ideal for freezers where power needs to be automatically restored.
- Test button for safety checks.
- Still protects with lost neutral.
- Still protects with pulsating DC earth fault currents.
- Complies with BS7288 and BS1363.
- **Part No. RCD08MPV**



Specification

Type	Passive – Latching
Operating Voltage	230V AC
Current Rating	Fully complies with BS1363
Rated Trip Current	30mA
Trip Speed	BS 7288 – 40ms
Contact Break	Double Pole
Continues to Protect With	Lost Neutral & Pulsating DC Earth Fault
Cable Capacity	Up to 10.5mm ²
Conforms To	BS1363, BS7288
Dimensions (mm)	Height 87, Width 148, Depth 56