

**Tower Pipe / Cylinder Thermostat PCT**

**TOWER CONTROLS**

**SWITCH ON  
TO COMFORT**

**Pipe / Cylinder Thermostat 240V AC / 16A**

General Performances	
Temperature range	10/90°C
Differential	5°C
Sensing element max. temperature resistance	110°C
Thermostat pin rotation	270°
Cover material	ABS UL94 V0
Base material	galvanised steel
Protection grade	IP40
Contacts rating	16(4)A 250V~ 6(1)A 400V~

**Wiring Diagram**

