



Mounting hole (inch)	0.5512"
Mounting hole (metric)	14mm
Indicator type	tri-color
Mounting type	with bezel
Bezel type	prominent
Bezel material	metal
Bezel color	satın chrome
Bezel size	M14
Protection	IP40
Lens type	round
Lens color	white diffused
Lens size	10mm
Connector Tpe	tab terminals 2.8x0.8
Connector number	3
Connector for lamp test	no
Number LED chip	2
Indicator color	red/green/yellow

Drawn : ROJ	Ch'd : ROJ	Datasheet : 1924	Print date : 08/05/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :



Part Number : 19240354
 Serial Number : 1924
 LEDs Indicators

Dom wave length	625/568nm
Peak Wave Lenght (mA)	
Op. voltage (V)	24V DC
Forward volt max.	
Rectifier	-
AC current	-
DC current	20/20/40mA
Lum in min (mcd)	
Lum in type (DC)	90/60/150mcd
Voltage tolerance (%)	10%
Op. temperature (°C)	-25°C...+60°C
Storage temperature (°C)	-25°C...+60°C
Narrative	
Viewing angle (°)	

Drawn : ROJ	Ch'd : ROJ	Datasheet : 1924	Print date : 08/05/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :