

TECHNICAL DATA SHEET

GD5351VAI/DV

Internal Day/Night Mini Dome Camera with Varifocal Lens



KEY FEATURES

- 1/3" Sony Super HAD CCD
- Super High Resolution
- Digital Noise Reduction
- Easy To Fit
- O.S.D.
- Privacy Masking, Mirror
- Three Axis Gimbal

TECHNICAL DATA SHEET

TECHNICAL SPECIFICATION

Model Number	GD5351VAI/DV
Image Sensor	Sony 1/3-inch Super HADCCD
Horizontal Resolution	540 TVLines
Effective Pixels (H x V)	752 x 582
Electronic Shutter	Auto / Manual - 1/50 " 1/100,000 Seconds
Sensitivity	0.3LuxColour, 0.1Lux B/W, 0.002Lux Using Sens-Up
Signal To Noise Ratio	Greater than 50dB (AGC Off)
Lens Options	2.9-10mm DC Auto Iris Varifocal IRCorrective F1.2
Power Consumption	AC24V/DC12V (170mA/250mA)
Video Output	1V p-p ~ 75 Ohm (Video 0.714V Sync 0.286V)
Dimensions (D x H)	140 x 120 mm
Power Supply	DC12V / AC24V
Operating Conditions	Temperature: -10°C ~ +50°C, Humidity: 30% ~ 90%
Weight	360g

Features and specification are subject to change for further improvement without any notice.