

a vital part of your world

Text Search:

Friday, 25 November, 2005

**CATALOG**

## Cross Reference

[Competitive Products](#)  
[Military Spec P/Ns](#)  
[Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

[Home](#)

 e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

**Soft Shell Connectors**
**↳ .200" Centerline, 250 V, 13 A max. (Commercial MATE-N-LOK)**
**60619-1**


Active

**Directive 2002/95/EC  
Compliant**

RoHS Compliant

**(Corporate P/N: 60619-1)**
[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

**Related Part Information**

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>➤ <a href="#">General Info</a></li> <li>➤ <a href="#">Sales Info</a></li> <li>➤ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Pricing &amp; Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Tooling</a></li> </ul>

**Photos & Line Drawings** - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)
**Searchable Features:**

<b>Brand:</b>	AMP
<b>RoHS/ELV Compliance:</b>	RoHS compliant, ELV compliant
<b>Lead Free Solder Processes:</b>	Not relevant for lead free process
<b>Product Type:</b>	Contact
<b>Contact Diameter (mm [in]):</b>	2.13 [0.084]
<b>Packaging Method:</b>	Loose Piece
<b>Contact Type:</b>	Socket
<b>Wire Range (mm [AWG]):</b>	0.50-2.00 <sup>2</sup> [20-14]
<b>Contact Material:</b>	Brass
<b>Wire Insulation Diameter (mm [in]):</b>	2.54 – 3.30 [0.100 – 0.130]

**Other Properties:**

<b>RoHS/ELV Compliance History:</b>	Always was RoHS compliant
<b>Connector Line:</b>	Commercial MATE-N-LOK
<b>Contact Termination Area Plating:</b>	Pre-Tin
<b>Stock Thickness (mm [in]):</b>	0.30 [0.012]
<b>Voltage (VAC):</b>	250
<b>Current Rating (Amps.):</b>	13
<b>Comment:</b>	Extraction Tools: Pins- No. 1-305183-1 (IS 7158); Sockets- No. 1-305183-2 (IS 7158); Pins and Sockets-No. 465644-1 (IS 7211). Insertion Tools: No. 455830-1 (IS 7984)

Copyright and Privacy Statement  
 Visit [Tyco International Ltd.](#)