

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

[Home](#)

e-bulletin newsletter

Soft Shell Connectors

↳ .163" Centerline, 600 V, 9.5 A max. (Mini Universal MATE-N-LOK)

**AMP** 170363-1 [Active](#)

**Directive 2002/95/EC  
Compliant**

[RoHS Compliant](#)

(Corporate P/N: 170363-1)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>↳ <a href="#">General Info</a></li> <li>↳ <a href="#">Sales Info</a></li> <li>↳ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>↳ <a href="#">Pricing &amp; Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>↳ <a href="#">Tooling</a></li> </ul>

Searchable Features:

<b>Brand:</b>	AMP
<b>RoHS/ELV Compliance:</b>	RoHS compliant, ELV compliant
<b>Lead Free Solder Processes:</b>	Not relevant for lead free process
<b>Product Type:</b>	Contact
<b>Connector Line:</b>	Mini-Universal MATE-N-LOK
<b>Gender:</b>	Pin
<b>Packaging Method:</b>	Loose Piece
<b>Wire Range (mm [AWG]):</b>	0.12-0.35 <sup>2</sup> [26-22]
<b>Contact Material:</b>	Brass
<b>Wire Insulation Diameter (mm [in]):</b>	1.20 – 1.75 [0.047 – 0.069]
<b>Contact Termination Area Plating:</b>	Pre-Tin

Other Properties:

<b>RoHS/ELV Compliance History:</b>	Always was RoHS compliant
<b>Contact Diameter (mm [in]):</b>	0.99 [0.039]
<b>Stock Thickness (mm [in]):</b>	0.25 [0.010]
<b>Voltage (VAC):</b>	600
<b>Current Rating (Amps.):</b>	9.5
<b>CompactPCI:</b>	No

[Copyright](#) and [Privacy Statement](#)  
 Visit [Tyco International Ltd.](#)

