



Electronics

a vital part of your world

Find Answers:

Wednesday, 16 November, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

**RF Connectors**  
 ↳ **Multiple Coaxial Contacts (COAXICON)**

**AMP** 226537-1 Active

**Directive 2002/95/EC Compliant**

RoHS Compliant

**(Corporate P/N: 226537-1)**

Search for Parts

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>➤ <a href="#">General Info</a></li> <li>➤ <a href="#">Sales Info</a></li> <li>➤ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Pricing &amp; Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Tooling</a></li> </ul>

**Photos & Line Drawings** - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:	
<b>Brand:</b>	AMP
<b>RoHS/ELV Compliance:</b>	RoHS compliant, ELV compliant
<b>Lead Free Solder Processes:</b>	Not relevant for lead free process
<b>Product Type:</b>	Contact
<b>Pin/Socket:</b>	Pin
<b>Terminate To:</b>	Coaxial Cable, Shielded Wire
<b>Cable Type:</b>	161, 174, 174DB, 179, 179A, 179B, 187, 187A, 187DB, 188, 188A, 316, Belden 9221, RD-316
<b>Wire/Cable Type:</b>	Shielded
<b>Wire Range (mm [AWG]):</b>	0.12-0.15 <sup>2</sup> [26]
<b>Connector Impedance:</b>	Non-Matched

Other Properties:	
<b>RoHS/ELV Compliance History:</b>	Always was RoHS compliant
<b>Dielectric Material:</b>	TPX
<b>Center Conductor Material:</b>	Beryllium Copper per QQ-C-533
<b>Center Conductor Plating:</b>	Gold (30) over Copper (100)
<b>Outer Shell Material:</b>	Brass per MIL-C-50
<b>Outer Shell Plating:</b>	Gold (30) over Nickel (50)
<b>Comment:</b>	A ferrule is required for each pin and socket. Extraction Tool No. 305183

<b><a href="#">Body Style:</a></b>	Straight
<b><a href="#">Mating Contact Retention:</a></b>	Without
<b><a href="#">Contact Type:</a></b>	Coax
<b><a href="#">Contact Size:</a></b>	16
<b>Contact Mating Area Plating:</b>	Gold (30)
<b><a href="#">Connector Family:</a></b>	CPC, G Series, M Series, Metrimate

Copyright and Privacy Statement  
Visit [Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]