



Electronics

a vital part of your world

Find Answers:

Friday, 14 October, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

Soft Shell Connectors

➔ .250" Centerline, 600 V, 19 - 36 A max. (Universal MATE-N-LOK)

**AMP** 350690-2 Active

**Directive 2002/95/EC Compliant**

RoHS Compliant

(Corporate P/N: 350690-2)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>➤ <a href="#">General Info</a></li> <li>➤ <a href="#">Sales Info</a></li> <li>➤ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Pricing</a></li> <li>➤ <a href="#">Product Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Tooling</a></li> </ul>

**Photos & Line Drawings** - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:	
Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Contact
Connector Line:	Universal MATE-N-LOK
CompactPCI:	No
Contact Type:	Pin
High Current:	No
Wire Range (mm [AWG]):	0.20-0.80 <sup>2</sup> [24-18]
Insulation Diameter (mm [in]):	1.02-2.54 [.040-.100]
Contact Material:	Brass

Other Properties:	
Contact Diameter (mm [in]):	2.13 [0.084]
Stock Thickness (mm [in]):	0.30 [0.012]
Voltage (VAC):	600
Packaging Method:	Loose Piece
Contact Termination Area Plating:	Gold (30)
Comment:	Contacts can be used with Splash Proof Seals if insulation diameter range is .060-.100.

<b>Sealable:</b>	No
<b>Current Rating (Amps.):</b>	19

[Copyright and Privacy Statement](#)  
[Visit Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]

▪