



Electronics

a vital part of your world

Find Answers:

Monday, 31 October, 2005

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Subminiature and Microminiature D Connectors

↳ Subminiature D Pin/Socket Connectors for MIL-C-24308 and MIL-C-39029

AMP 205161-1 [Active](#)

[Not ELV or RoHS Compliant](#)

(Corporate P/N: 205161-1)

[Search for Compliant \(RoHS/ELV\)](#)

[Alternates](#)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ❖ General Info ❖ Sales Info ❖ Assembly Subcontractors 	<ul style="list-style-type: none"> ❖ Pricing & Availability 	<ul style="list-style-type: none"> ❖ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

[Insert Arrangement](#)

Searchable Features:

Brand:	AMP
Government/Industry Qualification:	Yes
Government/Industry Part Number:	M24308/2-281F
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Wave solder capable to 240°C, Wave solder capable to 265°C
Product Type:	Connector
Product Series:	109
Density:	Standard
Terminate To:	Wire
Number of Positions:	9

Other Properties:

NASA Qualification:	No
Mount Style:	Mounting Holes
Mounting Hole Diameter (mm [in]):	3.05 [.120]
Retention Clip Material:	Stainless Steel

<u>Gender:</u>	Receptacle
<u>Blindmate:</u>	No
<u>Non-Magnetic:</u>	No
<u>Sockets:</u>	Without
<u>Shell Size:</u>	1
<u>Rear Grommet:</u>	No
<u>Power/Signal/Coax Combination:</u>	No
<u>Shell Material:</u>	Steel
<u>Shell Plating:</u>	Cadmium
<u>Contact Size:</u>	20
<u>Wire Termination Type:</u>	Crimp
<u>Contact Style:</u>	Crimp Snap-in

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]