

a vital part of your world

Text Search:

Wednesday, 11 January, 2006

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

Part Number Search

- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

Soft Shell Connectors

➔ 5mm (.197") Centerline, 600 V, 14 A max. (Metrimate)



207359-1



Active

Directive 2002/95/EC  
Compliant

RoHS Compliant

(Corporate P/N: 207359-1)

[CAD Geometry](#) | [Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>➤ <a href="#">General Info</a></li> <li>➤ <a href="#">Sales Info</a></li> <li>➤ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Pricing &amp; Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>➤ <a href="#">Tooling</a></li> </ul>

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)

Searchable Features:

<b>Brand:</b>	AMP
<b>RoHS/ELV Compliance:</b>	RoHS compliant, ELV compliant
<b>Lead Free Solder Processes:</b>	Not relevant for lead free process
<b>Product Type:</b>	Housing
<b>Connector Configuration:</b>	In-Line
<b>Number of Positions:</b>	3
<b>Gender:</b>	Receptacle
<b>Coaxial Socket:</b>	Without
<b>Keyed:</b>	No
<b>Mount:</b>	Free Hanging
<b>Mounting Ears:</b>	Without
<b>Centerline (mm [in]):</b>	5.00 [0.197]
<b>Mating Connector Lock:</b>	With
<b>Jackscrew:</b>	Without
<b>8/32 Insert:</b>	No
<b>PCB Retention Feature:</b>	No

Other Properties:

<b>RoHS/ELV Compliance History:</b>	Always was RoHS compliant
<b>Mating Connector Lock Type:</b>	Locking Tab
<b>Voltage (VAC):</b>	600
<b>Housing Material:</b>	Thermoplastic
<b>Housing Color:</b>	Red
<b>Housing Flammability Rating:</b>	UL 94V-0
<b>Packaging Quantity:</b>	150

[Copyright and Privacy Statement](#)  
Visit [Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]