



Electronics

a vital part of your world

Find Answers:

Sunday, 16 October, 2005

CATALOG

- Cross Reference
 - Competitive Products
 - Military Spec P/Ns
 - Tyco Brand P/Ns

- Part Number Search
- Document Search
- Product Type Search
- Product Family Search
- Alphabetical Search
- RoHS/ELV Compliance & Alternates
- CAD Model Search
- Brand Search
- Tool Search
- Multiple Part Comparison
- Lead Free Solutions
- Help/Glossary

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Switches, Shunts, and Knobs

↳ Pushbutton Switches

Alcoswitch **MPA206N** Active

[Not ELV or RoHS Compliant](#)

(Corporate P/N: 3-1437567-1)

[Search for Compliant \(RoHS/ELV\)](#)

[Alternates](#)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> General Info Sales Info 	<ul style="list-style-type: none"> Pricing Product Availability 	<ul style="list-style-type: none"> Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product View](#)

Searchable Features:	
Brand:	Alcoswitch
RoHS/ELV Compliance:	Not ELV/RoHS compliant
Lead Free Solder Processes:	Wave solder capable to 240°C
Product Type:	Switch
Tactile:	No
Configuration (Pole-Throw):	Double Pole - Double Throw
Contact Rating:	6A
Process Sealed:	No
Operating Function:	Push On/Push Off
Ganged:	No
Series:	MPA6
Mount Style:	Panel

Other Properties:	
Contact Plating:	Silver Clad with Gold Flash
Case Material:	Thermoset
Actuator Material:	Nickel plated copper alloy
Temperature Rating:	Standard
Comment:	Order cap model C22 or C23.

Mount Angle:	Vertical
Termination Type:	Wire Lugs
ESD Grounding Terminal:	Without
Low Profile:	No
Packaging Method:	Loose Piece
Actuator Style:	Cap - Order Separately
Actuator Length (mm [in]):	13.97 [0.550]
Actuator Profile:	Extended
Actuator Force (g [oz]):	590.00 – 1224.00 [20.800 – 43.180]
Number of Actuators:	Single
Illuminated:	No
Dust Proof:	No
Support Bracket:	Without
Bushing Style:	Threaded
Bushing Diameter:	1/4-40
Snap Action:	No

[Copyright and Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]

