

CATALOG

Cross Reference

- [Competitive Products](#)
- [Military Spec P/Ns](#)
- [Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

Home

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Terminals and Splices

↳ Ring and Spade Tongue Terminals



33462

[Active](#)

Directive 2002/95/EC Compliant

[RoHS Compliant](#)

(Corporate P/N: 33462)

[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ↳ General Info ↳ Sales Info ↳ Assembly Subcontractors 	<ul style="list-style-type: none"> ↳ Pricing & Availability 	<ul style="list-style-type: none"> ↳ Tooling

Searchable Features:	
Brand:	AMP
Government/Industry Qualification:	No
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Terminal Shape:	Ring Tongue
Receptacle Style:	Straight
Body Style:	SOLISTRAND
Barrel Type:	Closed Barrel
Wire/Cable Type:	Regular Wire
Wire Range (mm [AWG]):	6.64 - 10.5 ² [8]
Wire Range (CMA):	13,100 – 20,800
Insulation:	No
Insulation Support:	Non-Insulation Support
Stud Size:	5/16 [M8]

Other Properties:	
Barrel I.D. Min. (mm [in]):	4.37 [0.172]
Stock Thickness (mm [in]):	1.22 [0.048]

<u>Stud Diameter (mm [in]):</u>	8.33 [0.328]
<u>Shape:</u>	RING-048
<u>Heavy Duty:</u>	No
<u>Packaging Method:</u>	Loose Piece
<u>Material:</u>	Copper
<u>Finish:</u>	Tin

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]