

Straight Blade Devices

Accessories

For 15 and 20 Ampere, 125 and 250 Volts and 277 Volts AC Devices



NP8I



NP7

SS7



HBL52CM22



HBL5206WO



HBL7423WO

**Wallplates, 1-Gang**

Description	Color	Duplex Receptacles	Style Line® Receptacles	Single Receptacles with Face Dia. 1.39 in. (35.3)	
Smooth nylon.	Almond	–	NP26AL	–	
	Black	NP8BK	NP26BK	NP7BK	
	Brown	NP8	NP26	NP7	
	Gray	NP8GY	NP26GY	NP7GY	
	Ivory	NP8I	NP26I	NP7I	
	Light Almond	–	NP26LA	–	
	Office White	NP8OW	NP26OW	NP7OW	
	Orange	NP8OR	–	–	
	Red	NP8R	NP26R	NP7R	
	White	NP8W	NP26W	NP7W	
	Stainless steel 302/304 satin, smooth, 1-gang.		SS8	SS26	SS7
		Brass .040 in. (1.02) smooth, 1-gang	SB8	SB26	SB7
Aluminum, anodized, smooth.		SA8	–	SA7	

Weatherproof Covers

Description	Duplex Receptacles	Single Receptacles with Face Dia. 1.39 in. (35.3)
RTP, gray, for FS/FD box mounting.	HBL5221	HBL7423WO
RTP, yellow, for FS/FD box mounting.	HBL52CM21	HBL74CM23WO
RTP, gray, for device mounting.	HBL5222	–
RTP, yellow, for device mounting.	HBL52CM22	–
Cast aluminum for FS/FD box mounting.	HBL5206WO	HBL7420
Cast aluminum for device mounting.	HBL5205WO	–

Notes: All weatherproof plates are UL Listed for Wet Locations.

Those with suffix WO are listed for use with cover open, all others with cover closed. Refer to Section K for more details on cover plates.

RTP is an abbreviation for reinforced thermoplastic polyester.