




Sta-Kon®

T&B Catalog Number: 10RC-250T
UPC Number: 78621083934
Description: Insulated Vinyl Male - 250 Series Male Tabs For Wire Range 12-10 Length 1.08, Tab Size .250 x .032 , Yellow
Status: Active



WEB_USE

-T&B Product Line	029
-US Cutsheet PDF Catalog Link	http://www-public.tnb.com/contractor/docs/stakon.pdf

General

-Style	Male - 250 Series
-Insulation Type	Insulated Vinyl
-Terminal Series	RC
-Material	Brass
-Finish	Electro -Tin Plated
-Color	Yellow
-Wire Range	12-10
-Tab Size	.250 x .032

Dimension Information

-Maximum Insulation (inches)	.250
-Stock Thickness	.04
-A (inches)	1.08

Specifications

-Temperature Rating	105°C
-Voltage Rating	600V
-Flammability Rating	UL 94 V-0

Tooling

-Tool Charts	Available on Website
-Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
-Recommended Tool	ERG4001

Packaging

-T&B Order Multiple	50
-T&B Inner Pack	50
-Package in Units	250
-Package Type	Standard
-T&B Sold in UOM	Each
-T&B Weight Per UOM	0.51 lbs. per 100
-Alternate Package Qty	RC2517

Application Support

-Overview	Available on Website
-Wire Guide Tables	Available on Website

Certifications

-RoHS Compliance	Yes
------------------	-----

Certifications



File Nbr:
E66716

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com