



### Color-Keyed®



**T&B Catalog Number:** 54106UB  
**UPC Number:** 78621086871  
**Description:** Copper One-Hole Lug - 90 degree Standard Barrel - max 35KV, #4 AWG Wire, 1/4" Bolt Size, Tin Plated with Inspection Hole, Grey 29  
**Status:** Active



#### WEB\_USE

-T&B Product Line 007

#### General

-Material Copper  
 -Finish Tin Plated  
 -Wire Size #4 AWG  
 -Number of Studs 1  
 -Stud Size 1/4  
 -Tongue Angle 90  
 -Barrel Length Standard  
 -Barrel Shape Standard  
 -Tongue Width Standard  
 -Peep Hole Y  
 -Marking Standard  
 -Hole Shape Round  
 -Die Color Grey  
 -Die Code 29

#### Dimension Information

-A (inches) 1  
 -B (inches) 0.563  
 -C (inches) 0.563  
 -D (inches) 0.094  
 -E (inches) 0.359  
 -F (inches) 0.25

#### Tooling

-Connector & Tooling Chart Available on Website

#### Packaging

-T&B Inner Pack 50  
 -Package in Units 500  
 -T&B Sold in UOM Each  
 -T&B Weight Per UOM 1.9 lbs. per 100

#### Application Support

-Overview Available on Website  
 -Connector & Tooling Chart Available on Website

#### Notes

- Dimensions given for reference only. Dimensions may vary up to +/- .030.

#### Certifications

-RoHS Compliance Yes

### Certifications



File Nbr:  
E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)