


Color-Keyed®



T&B Catalog Number:
UPC Number:
Description:

54108
 78621054108
 Copper One-Hole Lug - Straight Standard Barrel - max 35KV, #1 AWG Wire, 1/4" Bolt Size, Tin Plated with Inspection Hole, Green 37
Status: Active



WEB_USE

-T&B Product Line 007

General

-Material Copper
 -Finish Tin Plated
 -Wire Size #1 AWG
 -Number of Studs 1
 -Stud Size 1/4
 -Tongue Angle Straight
 -Barrel Length Standard
 -Barrel Shape Standard
 -Tongue Width Standard
 -Peep Hole Y
 -Marking Standard
 -Hole Shape Round
 -Die Color Green
 -Die Code 37

Dimension Information

-B (inches) 0.65
 -E (inches) 0.47
 -F (inches) 0.25

Tooling

-Connector & Tooling Chart Available on Website

Packaging

-T&B Inner Pack 20
 -Package in Units 200
 -T&B Sold in UOM Each
 -T&B Weight Per UOM 3.7 lbs. per 100

Application Support

-T&B Instruction Sheets ta00675-tb2
 -Overview Available on Website
 -Connector & Tooling Chart Available on Website

Notes

- Dimensions given for reference only. Dimensions may vary up to +/- .030.

Certifications

-RoHS Compliance Yes

Certifications



File Nbr:
 E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com