


Color-Keyed®



T&B Catalog Number:
UPC Number:
Description:

54112
 78621054112
 Copper One-Hole Lug - Straight Standard Barrel - max 35KV, 4/0 AWG Wire, 3/8" Bolt Size, Tin Plated with Inspection Hole, Purple 54
Status: Active



WEB_USE

-T&B Product Line 007

General

-Material Copper
 -Finish Tin Plated
 -Wire Size 4/0 AWG
 -Number of Studs 1
 -Stud Size 3/8
 -Tongue Angle Straight
 -Barrel Length Standard
 -Barrel Shape Standard
 -Tongue Width Standard
 -Peep Hole Y
 -Marking Standard
 -Hole Shape Round
 -Die Color Purple
 -Die Code 54

Dimension Information

-A (inches) 2.18
 -B (inches) 0.93
 -C (inches) 1.03
 -D (inches) 0.14
 -E (inches) 0.7
 -F (inches) 0.375

Tooling

-Connector & Tooling Chart Available on Website

Packaging

-T&B Inner Pack 10
 -Package in Units 100
 -T&B Sold in UOM Each
 -T&B Weight Per UOM 10.25 lbs. per 100

Application Support

-T&B Instruction Sheets ta00675-tb2
 -Overview Available on Website
 -Connector & Tooling Chart Available on Website

Notes

- Dimensions given for reference only. Dimensions may vary up to +/- .030.

Certifications

-RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com