




Sta-Kon®

T&B Catalog Number: RA250TB
UPC Number: 78621082999
Description: Insulated Nylon Female - 250 Series Disconnects For Wire Range 22-18 Length 0.91, Tab Size .250 x .032 , Red
Status: Active



WEB_USE	
-T&B Product Line	029
-US Cutsheet PDF Catalog Link	http://www-public.tnb.com/contractor/docs/stakon.pdf

Features	
-	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

General	
-Disconnect Type	Female - 250 Series
-Insulation Type	Insulated Nylon
-Terminal Series	RA
-Material	Brass
-Finish	Electro -Tin Plated
-Color	Red
-Wire Range	22-18
-Tab Size	.250 x .032

Dimension Information	
-Maximum Insulation (inches)	.136
-Stock Thickness	.03
-A (inches)	.91
-B (inches)	.29

Specifications	
-Temperature Rating	105°C
-Voltage Rating	600V
-Flammability Rating	UL 94 V-2

Tooling	
-Tool Charts	Available on Website
-Application Tools	WT145C, WT2000, WT112M, ERG4001, ERG4003
-Recommended Tool	ERG4001

Packaging	
-T&B Order Multiple	1000
-T&B Inner Pack	1000
-Package in Units	10000
-Package Type	Bulk
-T&B Sold in UOM	Each
-T&B Weight Per UOM	0.3 lbs. per 100
-Alternate Package Qty	RA18250F

Application Support	
-Overview	Available on Website
-Wire Guide Tables	Available on Website

Notes

Bulk catalog numbers can be put on Mylar Tape for reel-fed applications (i.e. 12050 tool and application dies). Please add the suffix M for Mylar tape.

Certifications

-RoHS Compliance Yes

Certifications



File Nbr:
E66716

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com