



Sta-Kon®

T&B Catalog Number: RG9711
UPC Number: 78621082112
Description: Insulated Nylon Ring Terminal For Wire Range 1 Stud Size 1/4, Red, Military Specified (MIL-SPEC MS25036-126)
Status: Active

WEB_USE

-T&B Product Line -- 029
 -US Cutsheet PDF Catalog Link -- <http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

- -- Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.

General

-Insulation Type -- Insulated Nylon
 -Terminal Series -- RG
 -Material -- Copper
 -Finish -- Electro -Tin Plated
 -Color -- Red
 -Wire Range -- 1
 -Stud Size -- 1/4

Dimension Information

-Maximum Insulation (inches) -- .453
 -Stock Thickness -- .05
 -A (inches) -- 2.07
 -B (inches) -- .69
 -C (inches) -- .40
 -M (inches) -- 1.74

Specifications

-Temperature Rating -- 105°C
 -Voltage Rating -- 600V
 -Flammability Rating -- UL 94 V-2
 -MIL Specification -- MS-25036-126

Tooling

-Tool Charts Available on Website
 -Application Tools -- TBM6, TBM6S, ERG4007
 -Recommended Tool -- TBM6S

Packaging

-T&B Order Multiple -- 50
 -T&B Inner Pack -- 50
 -Package in Units -- 500
 -Package Type -- Standard
 -T&B Sold in UOM -- Each
 -T&B Weight Per UOM -- 3.76 lbs. per 100

Application Support

-T&B Sales Drawings wsd-000543
 -Overview Available on Website
 -Wire Guide Tables Available on Website

Notes

- -- Not available on Mylar Tape.

Certifications

-RoHS Compliance -- Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com