

**CBX200 USB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



The CBX 100/CBX 200 USB interfaces for PC-based configuring and calibrating of the ITXPlus universal signal isolating converters, WAVE TTA and the ACT20 series. The CBX 100/200 USB interface converters have a status LED to display the transmit/receive mode. The driver software is available for on our web site.

**General ordering data**

Order No.	<a href="#">8978580000</a>
Type	CBX200 USB
GTIN (EAN)	4032248813759
Qty.	1 pc(s).

## CBX200 USB

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

## Technical data

### Input

Type	USB 2.0 (USB type A plug)	Input resistance	22 kΩ
Input current	≤ 100 mA	Input voltage	1.6 ... 5.6 V

### Output

Type	RS232 (4-pole 2.5-mm jack plug)	Activation signal	9...15 V typ. 12 V / 4 mA
Level on interfaces	1.8...5.6 V (automatically adapted)	Output voltage, note	3.3 V regulated
Output current	3 A	Baud rate	≤ 115 kBd

### General data

Baud rate	≤ 115 kBd	Humidity	10...90 % (no condensation)
Input/Output	Interfaces		

### Insulation coordination

Insulation voltage	2.5 kV (input / output)	Standards	DIN EN 50178, DIN EN 61000-4-2
--------------------	-------------------------	-----------	--------------------------------

### Classifications

eClass 6.0	90-25-13-90		
------------	-------------	--	--