

Main

Range of product	GV2L GV2LE GV2ME GV2P TeSys D TeSys U GV2RT
Device short name	GV2
Product or component type	Busbars
Accessory / separate part type	Connection accessories
Poles description	3P
Product compatibility	2 contactors LC1D09...D18 2 contactors LC1D25...D38 GV2L GV2LE GV2ME GV2P GV2RT LS1D32 TeSys U starter-controller

Complementary

Mounting location	On terminal
Number of tap-offs	2
[Isc] thermal withstand current	104 x I ² t
Permissible current	11 A
[Ith] conventional free air thermal current	63 A
[Ui] rated insulation voltage	690 V
Connection pitch	45 mm
Product weight	0.036 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.