



Item number

**134910**

Item name

boxxser 80 5x10-14

EAN unitnumber

5733439134910

Colour

raaco Blue

Description of the item

No description

BOM items

| <u>Item number</u> | <u>Product</u>                      | <u>Quantity</u> |
|--------------------|-------------------------------------|-----------------|
| 279604             | Base 80 5x10 Boxxser                | 1               |
| 279109             | Lid raaco 80/55 5x10 Boxxser        | 1               |
| 279581             | Handle gasm. 5x10/BA8-8 Boxxser     | 1               |
| 279598             | Lock 55 5x10/80 5x10/80 8x8 Boxxser | 1               |
| 279697             | Prop 8x8/5x10 Boxxser               | 1               |
| 279734             | ID-Corner Boxxser                   | 1               |
| 279741             | ID-Corner Boxxser                   | 1               |
| 279710             | ID-Corner Boxxser                   | 1               |
| 225137             | INSERT BA8-1 PP                     | 6               |
| 225144             | INSERT BA8-2 PP                     | 2               |
| 225151             | INSERT BA8-3 PP                     | 1               |
| 225168             | INSERT BA7-1 PP                     | 4               |
| 225175             | INSERT BA7-2 PP                     | 1               |

Materials

| <u>Item number</u> | <u>Material</u>         |
|--------------------|-------------------------|
| 600170             | Polypropylene - PP      |
| 600552             | Polycarbonate - PC      |
| 600019             | Polystyrene impact - SB |
| 600163             | Polystyrene - PS        |
| 600132             | Polypropylene - PP      |

Item alternative

| <u>Item number</u> | <u>Product</u>     | <u>Quantity</u> |
|--------------------|--------------------|-----------------|
| 280303             | Boxxser 80 5x10-14 | 1               |

Item dimensions

|                         |       |
|-------------------------|-------|
| Net. Depth (mm) .....   | 361,0 |
| Net. Width (mm) .....   | 421,0 |
| Net. Height (mm) .....  | 78,0  |
| Inner Depth (mm) .....  | 273,0 |
| Inner Width (mm) .....  | 393,0 |
| Inner Height (mm) ..... | 67,0  |

Weight

|                          |       |
|--------------------------|-------|
| Net weight (Kgs) .....   | 2,026 |
| Tare weight (Kgs) .....  | 0,133 |
| Gross weight (Kgs) ..... | 2,159 |

Volume

|                         |         |
|-------------------------|---------|
| Multiple (Pieces) ..... | 3,00    |
| Volume (m3) .....       | 0,01300 |

Capacity load

|                         |       |
|-------------------------|-------|
| Carr. Load (Kgs) .....  | 15,00 |
| Carr. Load (Ltrs) ..... | 0,00  |

**Sales**

raaco Great Britain  
 VAT No.: GB 232 6219 86  
 Wenisc House - Meadow Court  
 High Street - Witney  
 Oxfordshire OX28 6ER  
 Tel: (01993) 776333  
 Fax: (01993) 776444

**Headquarters:**

raaco International A/S  
 CVR No.: DK 22 12 28 19  
 VAT No.: DK 91 42 64 55  
 Platanvej 19 - Ø. Toreby  
 DK-4800 Nykøbing F  
 Tel.: +45 54 88 84 00  
 Fax: +45 54 88 85 00