

THE BT DECT PORTFOLIO



BT Sonus 1500



Colour: Gun Metallic/Silver

Type II Caller display
 50 Number calls list
 20 Number redial list
 Directory: 250 Name & number
 with copy between handsets

GAP compatible:	yes	Handsfree:	yes		
Max. number of handsets:	5	Headset socket:	no		
Max. number of bases:	4	Auto answer:	yes		
Conference call:	yes	Secrecy:	yes	Call waiting indicator:	yes
Call transfer:	yes	Handset naming:	yes	PBX access code:	yes
Internal calls:	yes	Keypad lock:	yes	Repeater compatible:	no
Music on hold:	yes	Power on/off:	yes	Wall mount:	no
Indoor range* (Metres):	50	Inductive coupler:	no		
Outdoor range* (Metres):	300	Earpiece volume control:	yes	Talktime (hours):	15
		Handsfree volume control:	yes	Standby (hours):	150
Display type:	mono	Call timer:	yes	Battery type:	NiMH
Display - number of lines #:	5	Clock:	yes	Battery size:	AAA
Backlit:	yes	Alarm:	yes	Battery capacity (mAh):	750
Contrast control:	yes	Calendar:	no	Base PSU item code:	
		Appointments:	no	Charger PSU item code:	
		Illuminated keypad:	yes		
		Keypad confirmation tone:	yes	Recording machine	
Handset polyphonic ringtones:	10	Low battery indicator:	yes	Recording time (mins):	up to 30
Handset standard ringtones:	5	Low battery alert:	yes	Playback:	handset & base
Handset ringer on/off:	yes	Out of range indicator:	yes	Outgoing messages:	2
Handset ringer volume control:	yes	Out of range alert:	yes	Recordable outgoing messages:	yes
Visual ring indicator:	yes	Handset settings PIN protected:	no	Answer delay:	yes
Associated ring tone:	yes	Belt clip:	no		
Base ringtones:	5			Remote access:	yes
Base ringer on/off:	yes			Message advice:	indicator
Base ringer volume control:	yes			Call screening:	yes
		Base settings PIN protected:	yes	Memo:	yes
		Find key on base:	yes	Audable message alert:	yes
SIM card:	no				
Caller groups:	yes				
Quick dial memories	8				

Notes:

* In ideal conditions

Including icons and soft keys, as appropriate

Technical support: Is available from the BT Helpdesk on Freephone 08002182182 or via the email link on the product page at www.bt.com/producthelp

Status: Development



THE BT DECT PORTFOLIO

BT Sonus 1500

Weights and dimensions

Base (gms): 120
Handset (gms): 115
Charger (gms): 76

Base (cm): 4.2 x 8.7 x 9.86
Handset (cm): 15 x 4.6 x 31.5
Charger (cm): 4.2 x 8.67 x 9.86

Giftbox - dimensions/complete/empty

1 Pack: 21 x 18 x 5.5 (cms) / 639 (gms) / 0 (gms)
2 Pack: 21 x 18 x 9.5 (cms) / 954 (gms) / 0 (gms)
3 Pack: 21 x 18 x 15.5 (cms) / 1375 (gms) / 0 (gms)
4 Pack: 21 x 18 x 15.5 (cms) / 1700 (gms) / 0 (gms)
Additional handset not available

Overpack - dimensions/complete

1 Pack: 23.5 x 35 x 19.5 (cms) / 4300 (gms)
2 Pack: 23.5 x 37.5 x 30.5 (cms) / 612 (gms)
3 Pack: 23.5 x 37.5 x 32.5 (cms) / 5900 (gms)
4 Pack: 23.5 x 37.5 x 32.5 (cms) / 7000 (gms)
Additional handset not available

No. of giftboxes per overpack

1 Pack: 6
2 Pack: 6
3 Pack: 4
4 Pack: 4
Additional handset not available

Pallet Ti's x Hi's

1 Pack: 15 x 5
2 Pack: 9 x 5
3 Pack: 9 x 5
4 Pack: 9 x 5
Additional handset not available

Item code

1 Pack: 061958
2 Pack: 061959
3 Pack: 061960
4 Pack: 061961
Additional handset not available

CSS code

1 Pack not available
2 Pack not available
3 Pack not available
4 Pack not available
Additional handset not available

Barcode

1 Pack: 5016351615010
2 Pack: 5016351615027
3 Pack: 5016351615034
4 Pack: 5016351615041
Additional handset not available

Overpack barcode

1 Pack: 05016351821138
2 Pack: 05016351821145
3 Pack: 05016251821152
4 Pack: 05016351821169
Additional handset not available

Country of manufacture: China