


# PCI-1720U

# PCI-1724U

12-bit, 4-ch Isolated Analog Output  
Universal PCI Card

14-bit, 32-ch Isolated Analog Output  
Universal PCI Card



PCI-1720U



## Specifications

### Analog Output

- **Channels** 4 isolated
- **Resolution** 12 bits
- **Output Rate** Static update
- **Output Range** (Software programmable)

<b>Bipolar (V)</b>	±5, ±10
<b>Unipolar (V)</b>	0 ~ 5, 0 ~ 10
<b>Current Loop (mA)</b>	0 ~ 20, 4 ~ 20

- **Slew Rate** 2 V/μs
- **Isolation Protection** 2,500 V<sub>DC</sub>
- **Driving Capability** 5 mA
- **Operation Modes** Software polling
- **Accuracy** Relative: ±1 LSB; Differential Non-Linearity: ±1 LSB (monotonic)
- **Excitation Voltage** 50 V (max.)

### General


- **Bus Type** Universal PCI V2.2
- **I/O Connectors** 1 x DB37 female connector
- **Dimensions (L x H)** 175 x 100 mm (6.9" x 3.9")
- **Power Consumption** 5 V @ 350 mA (typical), 500 mA (max.)  
12 V @ 200 mA (typical), 350 mA (max.)
- **Operating Temperature** 0 ~ 60° C (32 ~ 140° F) (refer to IEC 68-2-1, 2)
- **Storage Temperature** -20 ~ 70° C (-4 ~ 158° F)
- **Storage Humidity** 5 ~ 95% RH, non-condensing (refer to IEC 68-2-3)

## Ordering Information

- **PCI-1720U** 12-bit, 4-ch Isolated AO Universal PCI Card

### Accessories

- **PCL-10137-1** DB37 Cable, 1 m
- **PCL-10137-2** DB37 Cable, 2 m
- **PCL-10137-3** DB37 Cable, 3 m
- **ADAM-3937** DB37 DIN-rail Wiring Board



PCI-1724U



## Specifications

### Analog Output

- **Channels** 32 isolated
- **Resolution** 14 bits
- **Output Rate** Static update
- **Output Range** (Software programmable)

<b>Bipolar (V)</b>	±10
<b>Current Loop (mA)</b>	0 ~ 20, 4 ~ 20

- **Isolation Protection** 1,500 V<sub>DC</sub> system isolation
- **Output Impedance** 0.1 Ω max.
- **Operation Modes** Software polling, synchronized output
- **Accuracy** Relative: ±4 LSB  
Differential Non-linearity: ±2 LSB (monotonic)
- **Driving Capacity** 10 mA

### General

- **Bus Type** Universal PCI V2.2
- **I/O Connectors** 1 x DB62 female connector
- **Dimensions (L x H)** 175 x 100 mm (6.9" x 3.9")
- **Power Consumption** 5 V @ 400 mA, 12 V @ 270 mA max.
- **Operating Temperature** 0 ~ 60° C (32 ~ 140° F) (refer to IEC 68-2-1, 2)
- **Storage Temperature** -20 ~ 70° C (-4 ~ 158° F)
- **Storage Humidity** 5 ~ 95 % RH, non-condensing (refer to IEC 68-2-3)

## Ordering Information

- **PCI-1724U** 14-bit, 32-ch Isolated AO Universal PCI Card

### Accessories

- **PCL-10162-1** DB62 Cable, 1 m
- **PCL-10162-3** DB62 Cable, 3 m
- **ADAM-3962** DB62 DIN-rail Wiring Board