





- Control inventories, shorten assembly times and minimize parts handling
- Heavy-duty bins securely stack atop each other, sit on shelving and hang from Akro-Mils racks, panels, rails and carts
- Molded of high-impact polypropylene, AkroBins are unaffected by weak acids and alkalis
- Products made of polypropylene block copolymer are autoclavable up to 250° F
- Sturdy, one-piece construction is water, rust and corrosion-proof
- Guaranteed not to crack or break under normal load conditions as stated in our 1-year limited warranty
- Available in 14 sizes and 7 colors: Red, Yellow, Blue, Stone, Green, Semi-Clear and Black

## accessories



**"See-through" Crystal Styrene Lids** keep contents dust-free and protected



**Lengthwise Dividers** keep items separated in the bin



**30320 Wide AkroBins: Dividers** available in two sizes



## 33" Wide AkroBin

### Great Lengths to Organize More Efficiently

- 1 to 8 compartments, depending on divider placement
- Optional lid sold separately
- 2½" and 4" dividers available (comes with two 4" dividers)
- Fits on standard Akro-Mils rail, louvered and 36" shelf systems
- Reinforced sides for secure stacking



**30320 33" Wide AkroBin** with Optional Lid


## features




Anti-slide stop prevents stacked bins from shifting forward



Full-width hanger lip supports bin on hanging system



Reinforced side ribs add strength and prevent spreading when stacked



Extra-wide stacking ledge saves space and prevents spills





Large front label area for easy coding and scanning



Curved-bottom hopper front makes it easy to retrieve small parts



Dividers allow you to create customizable compartment sizes



AkroBins	Model No.	Outside Dimensions Inches			Bottom Dimensions Inches				Bin Load Capacity On Rack	Bin Ctn. Qty.	Accessories			
		L	W	H	L	W	H	X			Dividers**	Divider Pkg. Qty.	Bin Lids***	Lid Pkg. Qty.
	A 30210	5 $\frac{3}{8}$	4 $\frac{1}{8}$	3	4 $\frac{3}{8}$	3 $\frac{7}{8}$	2 $\frac{13}{16}$	4	10 lbs.	24	40210 (1)	6	30211	24
	30220	7 $\frac{3}{8}$	4 $\frac{1}{8}$	3	6 $\frac{3}{8}$	3 $\frac{7}{8}$	2 $\frac{13}{16}$	6	10 lbs.	24	40220 (1)	6	30221	24
	30224	10 $\frac{7}{8}$	4 $\frac{1}{8}$	4	10 $\frac{1}{4}$	3 $\frac{3}{8}$	3 $\frac{3}{4}$	9	30 lbs.	12	-	-	-	-
	B 30230	10 $\frac{7}{8}$	5 $\frac{1}{2}$	5	10 $\frac{1}{4}$	4 $\frac{3}{8}$	4 $\frac{3}{8}$	9	30 lbs.	12	40230 (1)	6	30231	12
	30234	14 $\frac{3}{8}$	5 $\frac{1}{2}$	5	14 $\frac{1}{16}$	4 $\frac{3}{8}$	4 $\frac{3}{8}$	12 $\frac{13}{16}$	50 lbs.	12	-	-	-	-
	C 30239	10 $\frac{3}{4}$	8 $\frac{1}{4}$	7	10	6 $\frac{5}{8}$	6 $\frac{3}{4}$	8	50 lbs.	6	40239 (1)	6	-	-
	30240	14 $\frac{3}{4}$	8 $\frac{1}{4}$	7	14	6 $\frac{5}{8}$	6 $\frac{3}{4}$	12	60 lbs.	12	40245 (1)	6	-	-
	30265	18	8 $\frac{1}{4}$	9	17 $\frac{1}{8}$	6 $\frac{3}{4}$	8 $\frac{1}{4}$	14 $\frac{1}{2}$	60 lbs.	6	40265 (1)	6	-	-
	D 30235	10 $\frac{7}{8}$	11	5	10 $\frac{1}{4}$	10	4 $\frac{3}{8}$	9	50 lbs.	6	40230 (3)	6	30236	6
	30260	18	11	10	17	9 $\frac{1}{2}$	9 $\frac{3}{8}$	14 $\frac{3}{16}$	60 lbs.	6	40260 (3)	6	-	-
	E 30255	10 $\frac{7}{8}$	16 $\frac{1}{2}$	5	9 $\frac{3}{4}$	15	4 $\frac{3}{8}$	9	60 lbs.	6	40230 (3)	6	-	-
	30250	14 $\frac{3}{4}$	16 $\frac{1}{2}$	7	14	14 $\frac{3}{4}$	6 $\frac{3}{4}$	12	75 lbs.	6	40245 (3)	6	-	-
	30270	18	16 $\frac{1}{2}$	11	17 $\frac{1}{8}$	14 $\frac{3}{4}$	10 $\frac{1}{4}$	14	100 lbs.*	3	40270 (3)	6	-	-
	F 30320	8 $\frac{3}{8}$	33	5	7	31 $\frac{1}{2}$	4 $\frac{3}{8}$	6	80 lbs.	4	40321 & 40220 (7)	7	30321	4

One color per carton: Specify Red, Blue, Yellow, Stone, Semi-Clear, Green or Black. Order in carton quantities. \*Note 30265 & 30270 are not designed for use with hanging systems.  
 CAUTION: When using bins with hanging systems, do not exceed the weight capacity for the rack, which may be less than the total sum of bin capacities.  
 \*\* ( ) = Max. # of dividers per bin. \*\*\*Assembly required - hinge pins included.



## products related products

Create the perfect storage system – mix and match your selection of AkroBins with compatible products including:

- Rail Hanging Systems..... pg. 8
- Louvered Hanging Systems ..... pg. 9
- ReadySpace Storage Systems .... pg. 10
- Wire Shelving Systems ..... pgs. 36-39
- Steel Shelving Systems ..... pgs. 40-42
- Bin Cabinets ..... pgs. 43-44
- ProCart..... pg. 45



# EarthSaver™ Series: AkroBins®

storage bins, racks & hanging systems



- AkroBins now made from 100% recycled material
- Three color options – Hunter Green, Sandstone and Terra Cotta
- Optional dividers keep items neatly separated
- An eco-friendly choice in storage and organization products



## Go Green With 100% Recycled Bins – Boost Productivity, Reduce Waste!

Feeling the need to “Go Green”? Akro-Mils introduces the **EarthSaver Series** – AkroBins and Shelf Bins (see pg. 14) made from 100% recycled plastic. Make a positive impact on the environment!

### related products


Create the perfect storage system – mix and match your selection of AkroBins with compatible products including:

- Rail Hanging Systems..... pg. 8
- Louvered Hanging Systems ..... pg. 9
- ReadySpace Storage Systems .... pg. 10
- Wire Shelving Systems ..... pgs. 36-39
- Steel Shelving Systems ..... pgs. 40-42
- Bin Cabinets..... pgs. 43-44
- ProCart..... pg. 45

### accessories




“See-through” Crystal Styrene Lids keep contents dust-free and protected



Lengthwise Dividers keep items separated in the bin

AkroBins	Model No.	Outside Dimensions Inches			Inside Dimensions Inches				Bin Load Capacity On Rack	Bin Ctn. Qty.	Accessories			
		L	W	H	L	W	H	X			Dividers**	Divider Pkg. Qty.	Bin Lids***	Lid Pkg. Qty.
	30210RECVSS	5½	4½	3	4¾	3¾	2¾	4	10 lbs.	24	40210 (1)	6	30211	24
	30210RECYTC	5½	4½	3	4¾	3¾	2¾	4	10 lbs.	24	40210 (1)	6	30211	24
	30210RECYHG	5½	4½	3	4¾	3¾	2¾	4	10 lbs.	24	40210 (1)	6	30211	24
	30220RECVSS	7½	4½	3	6¾	3¾	2¾	6	10 lbs.	24	40220 (1)	6	30221	24
	30220RECYTC	7½	4½	3	6¾	3¾	2¾	6	10 lbs.	24	40220 (1)	6	30221	24
	30220RECYHG	7½	4½	3	6¾	3¾	2¾	6	10 lbs.	24	40220 (1)	6	30221	24
	30230RECVSS	10½	5½	5	10¼	4¾	4¾	9	30 lbs.	12	40230 (1)	6	30231	12
	30230RECYTC	10½	5½	5	10¼	4¾	4¾	9	30 lbs.	12	40230 (1)	6	30231	12
	30230RECYHG	10½	5½	5	10¼	4¾	4¾	9	30 lbs.	12	40230 (1)	6	30231	12
	30240RECVSS	14¾	8¼	7	14	6¾	6¾	12	60 lbs.	12	40245 (1)	6	–	–
	30240RECYTC	14¾	8¼	7	14	6¾	6¾	12	60 lbs.	12	40245 (1)	6	–	–
	30240RECYHG	14¾	8¼	7	14	6¾	6¾	12	60 lbs.	12	40245 (1)	6	–	–
	30250RECVSS	14¾	16½	7	14	14¾	6¾	12	75 lbs.	6	40245 (3)	6	–	–
	30250RECYTC	14¾	16½	7	14	14¾	6¾	12	75 lbs.	6	40245 (3)	6	–	–
	30250RECYHG	14¾	16½	7	14	14¾	6¾	12	75 lbs.	6	40245 (3)	6	–	–



One color per carton: SS = Sandstone, TC = Terra Cotta and HG = Hunter Green. Order in carton quantities. CAUTION: When using bins with hanging systems, do not exceed the weight capacity for the rack, which may be less than the total sum of bin capacities.

\*\*() = Max. # of dividers per bin. \*\*\*Assembly required – hinge pins included.

# ProHANGER®

storage bins, racks & hanging systems

- ProHANGERS can be placed side-by-side on walls, rail rack or panel systems to support extra-long parts, supplies or materials
- Unique “J-hook design” cradles various shapes and sizes of contents
- Available End Cap inserts keep items from sliding out
- One-piece construction; molded of high-impact plastic for durability
- Each ProHANGER is capable of supporting up to 75 lbs.



## Easy Long Parts Storage Wherever You Need It!

- ProHANGER can be used alone or with a variety of Akro-Mils products, including a wide range of AkroBins®
- ProHANGER can even be mounted (using Louvered Hanging System) in service trucks for maintenance workers, plumbers, electricians, carpenters or other tradespeople

# ProHANGER®




ProHANGER shown with Louvered Hanging Panel and 33" Wide AkroBin

ProHANGER End Cap



ProHANGER

ProHANGER®				Inches			
	Model No.	Description	Ctn. Qty.	L	W	H	Capacity (lbs.)
	30330RED	ProHANGER	6	8¼	7¾	5	75
	40330	End Cap	6	6¾	¼	4¼	-
	403302PK	End Cap	2	6¾	¼	4¼	-

## related products

Use your ProHANGER with:


- AkroBins..... pgs. 4-6
- Rail Hanging Systems..... pg. 8
- Louvered Hanging Systems..... pg. 9

\* US patent pending.

## features




Smooth surface protects suspended parts or products




End Caps help keep items contained and fit easily into molded-in slots



Full-width hanger lip supports ProHANGER on hanging systems



Notches provided in hanger lip for mounting to wall surface with screws



Substantial ribbing in base gives added strength to support heavier items




# Rail Hanging Systems

storage bins, racks & hanging systems



- Rail Hanging Systems allow for fast, easy organization and parts retrieval
- Single-sided rail units are ideal for placement against a wall to save space
- Double-sided rail units can “float” in any room environment and be picked from both sides
- Mobile Kit available to mobilize two-sided racks
- Steel rail is ideal for workstations
- AkroBins sold separately



## features



Rails securely support AkroBins



Heavy-duty steel for strength and durability



Attractive, durable powder-coated finish stands up to heavy-duty use



- 30008**
- 1-Sided, can be assembled as 12 or 16 Rail
  - 250 lb. capacity



- 30016**
- 2-Sided, can be assembled as 12 or 16 Rail
  - 500 lb. capacity



- 30812 Bin Cart with Casters**
- 14-gauge steel worktop
  - 250 lb. capacity



- 30812 Bin Cart**  
Shown with 30230 AkroBins

- 30148 Steel Rail**  
Wall-mountable unit accepts 7 sizes of AkroBins. 110 lb. capacity

### Rail Hanging Systems

Model No.	Description	Ctn. Qty.	Dimensions Inches			AkroBins Model No. (Bin Weight Capacity)										
			L	W	H	30210 (10 lbs.)	30220 (10 lbs.)	30224 (30 lbs.)	30230 (30 lbs.)	30234 (50 lbs.)	30235 (60 lbs.)	30239 (50 lbs.)	30240 (60 lbs.)	30250 (75 lbs.)	30255 (60 lbs.)	
	<b>30008*</b>	1	36	14 $\frac{1}{2}$	53	96	96	48	48	48	24	24	24	12	16	
	<b>30016*</b>	1	36	20	53	192	192	96	96	96	48	48	48	24	32	
	<b>30148</b>	1	47 $\frac{3}{16}$	5 $\frac{1}{8}$	3	11	11	11	8	6	3	-	-	-	3	
	<b>30812</b>	1	38 $\frac{1}{2}$	24	36 $\frac{1}{2}$	96	96	64	48	48	24	24	24	12	16	

\*Can be assembled as a 12 or 16 rail rack.

### Mobile Kit

Model No.	Description	Ctn. Qty.	Fits Hanging System No.	Castors
<b>30424</b>	Mobile Kit - Casters & Handle	1	30016	4" Polyolefin



Two-Sided Racks can be mobilized with the **Mobile Kit**

# Louvered Hanging Systems

storage bins, racks & hanging systems

- Louvered Hanging Systems allow for easy placement and configuration of AkroBins\*
- Wall-mounted units keep items out of the way, off the floor and off the work table
- Floor standing racks can be placed near work areas to improve productivity
- Single-sided floor racks can be placed against wall to save floor space
- Double-sided units allow for picking from both sides
- Bench racks are used on work tables to keep parts within easy reach
- 11 different models available – accommodates up to 288 AkroBins
- Easy, one-person assembly



\*AkroBins sold separately, see pg. 4-6

## related products

Use the following products with Louvered Hanging Systems:

- AkroBins..... pgs. 4-6
- 33" Wide AkroBins..... pgs. 4-5
- ProHANGER..... Pg. 7

**30636**  
Louvered Panel  
Shown with 33" Wide AkroBins  
(see pg. 4 for details)








**98636**  
Bench Rack



### Louvered Hanging Systems

### Dimensions (Inches)

### AkroBins Model No. (Bin Weight Capacity)

Model No.	Description	Ctn. Qty	L	W	H	Rack Wt. Cap.(lbs.)	30210 (10 lbs.)	30220 (10 lbs.)	30224 (30 lbs.)	30230 (30 lbs.)	30234 (50 lbs.)	30235 (60 lbs.)	30239 (50 lbs.)	30240 (60 lbs.)	30250 (75 lbs.)	30255 (60 lbs.)	30320 (80 lbs.)	
 <b>30618*</b>	Louvered Panel	4	18	5/8	19	160	16	16	12	9	9	3	4	4	2	3	-	
 <b>30636*</b>	Louvered Panel	4	35 3/4	5/8	19	160	32	32	24	18	18	9	8	8	4	6	3	
	2 Panels		35 3/4	5/8	37		72	72	36	36	36	18	16	16	8	12	5	
	3 Panels		35 3/4	5/8	55		104	104	54	54	54	27	28	28	14	18	8	
	4 Panels		35 3/4	5/8	73		144	144	72	72	72	36	36	36	18	24	11	
 <b>98600*</b>	Bench Rack	1	27 1/8	8 3/8	19 1/8	120	30	30	18	12	12	6	6	6	-	-	0	
	<b>98636</b>	Bench Rack	1	36	8	20	120	40	40	24	18	18	9	8	8	4	6	3
 <b>30161</b>	Louvered Panel	1	36	5/8	61	120	96	96	72	60	60	28	24	24	12	18	10	
	<b>30118</b>	Louvered Panel	1	18	5/8	61	160	48	48	36	30	30	14	12	12	6	9	-
 <b>30653</b>	Louvered Floor Rack	1	35 3/4	32	75 1/2	2000	288	288	192	144	144	72	72	72	36	48	0	
	<b>30661</b>	Louvered Rack Single-Sided	1	36 3/8	13 1/2	66 3/8	500	96	96	72	54	54	28	24	24	12	18	10
	<b>30638</b>	Louvered Rack Single-Sided	1	18	13 1/2	66 3/8	250	48	48	36	30	30	14	12	12	6	9	-
	<b>30676</b>	Louvered Rack Double-Sided	1	36 3/8	25	66 3/8	1000	192	192	144	108	108	56	48	48	24	36	20
	<b>30651</b>	Heavy Duty Louvered Rack Single-Sided	1	35 3/4	17	75 1/2	1000	144	144	98	72	72	36	36	36	18	24	11

\*Also available in Beige.


## features



Formed from 16-gauge cold-rolled steel for strength and durability



Attractive, durable powder-coated finish stands up to heavy-duty use



Horizontal ribs provide added strength



Louvers securely support AkroBins

## Bin Retainer Clip

### Hold bins safely on louvered panels

- Made of durable engineering grade plastic
- Easy to use
- Will work with any size AkroBin or ProHANGER
- Perfect for service vans; maintenance workers, plumbers, electricians or other tradesmen who store and transport supplies and materials



**40599**  
Bin Retainer Clip

# ReadySpace™ Storage System

storage bins, racks & hanging systems

- Wall, Bench or Mobile Floor Units can be purchased alone or with AkroBins
- Create a neat, attractive storage space in any environment – customer-friendly appearance
- Frees up valuable workspace
- Pre-configured packages with Stone color AkroBins are available or create your own custom system – see pg. 4-6 for more AkroBins!

**Ideal For the Healthcare Industry!**



## Ready, Set, Organize!™

- Quickly create organized storage space virtually anywhere!
- Steel louvered storage system for hospitals, laboratories and medical offices
- Designed for use with a wide variety of Akro-Mils AkroBins®
- Clean, sleek look with a durable white, powder-coated finish
- Set up and installation are quick and easy
- ReadySpace Bench or Mobile Floor Units can double as a privacy wall!



### 98536 Bench Unit

- Can be assembled single- or double-sided



### Wall Unit

- Accommodates multiple sizes of AkroBins



### 30553 Mobile Floor Unit

- Quickly transports supplies

## features



Casters come standard with the Mobile Floor Unit



Wall Unit is shipped complete with its own mounting bracket for easy installation



Bench Unit has a two-piece base for placement against or away from wall for assembly as single- or double-sided



Durable white, powder-coated finish

### ReadySpace™ Wall Unit

Model No.	Description (L x W x H)	No. of Ctns.	Ship Weight (lbs.)	Bin Qty.
30536	37½" x 1¾" x 25¾", Panel	1	35	N/A
30536210S	Unit with 30210STONE Bins	3	45	48
30536220S	Unit with 30220STONE Bins	3	51	48
30536230S	Unit with 30230STONE Bins	3	55	24
30536235S	Unit with 30235STONE Bins	3	55	12
30536320S	Unit with 30320STONE Bins	2	47	4

### ReadySpace™ Mobile Floor Unit

Model No.	Description (L x W x H)	No. of Ctns.	Ship Weight (lbs.)	Bin Qty.
30553	24¾" x 23" x 52"	1	82	N/A
30553210S	Unit with 30210STONE Bins	6	117	120
30553220S	Unit with 30220STONE Bins	6	122	120
30553230S	Unit with 30230STONE Bins	6	142	60
30553235S	Unit with 30235STONE Bins	6	127	30
30553LF	Leveling Feet for Floor Unit	-	1	-

### ReadySpace™ Bench Unit (Assemble as Single or Double-Sided)

Model No.	Description (L x W x H)	No. of Ctns.	Ship Weight (lbs.)	Bin Qty.
98536	37¾" x 12" x 26¾" (Single)	1	51	N/A
	37¾" x 22½" x 26¾" (Double)	1	51	N/A

### ReadySpace™ Single-Sided Bench Unit Kits

Model No.	Description	No. of Ctns.	Ship Weight (lbs.)	Bin Qty.
98536210SS	Unit with 30210STONE Bins	3	61	48
98536220SS	Unit with 30220STONE Bins	3	67	48
98536230SS	Unit with 30230STONE Bins	3	71	24
98536235SS	Unit with 30235STONE Bins	3	71	12
98536320SS	Unit with 30320STONE Bins	2	63	4

### ReadySpace™ Double-Sided Bench Unit Kits

Model No.	Description	No. of Ctns.	Ship Weight (lbs.)	Bin Qty.
98536210SD	Unit with 30210STONE Bins	5	71	96
98536220SD	Unit with 30220STONE Bins	5	83	96
98536230SD	Unit with 30230STONE Bins	5	91	48
98536235SD	Unit with 30235STONE Bins	5	91	24
98536320SD	Unit with 30320STONE Bins	3	75	8



# InSight™

storage bins, racks & hanging systems



### Wall Unit (30536A3 shown)

- Frees up valuable workspace
- Clean, sleek look with a white powder-coated finish
- Four bin size packages available



### Mobile Floor Unit (30553B1 shown)

- Organizes, shares and transports supplies and products
- Perfect for "high-demand" items
- Panel easily locks into posts on base without tools
- Four bin size packages available



### Louvered Panel Unit (30636BEIGE Louvered Panel shown with 305A3 bins)

- Louvers securely support InSight™ bins
- Use alone or side-by-side with additional louvered panels
- Easy one-person assembly

- Provide easy and maximum visibility to users in a sleek, modern design
- Can be stacked, sit on shelving or hang on Akro-Mils rails and louvered panels or ReadySpace™ Storage System
- Optional lids protect contents from dust – will stack with lids in place
- Patent Pending: No tip feature when bins are stacked
- Clear length and width dividers available
- Large label area for part identification and bar code scanning
- Autoclavable
- Available in 4 sizes



insight™  
by Akro-Mils

## A Visible Difference in Storage & Organization!

- Perfect for a variety of settings – from industrial to healthcare
- Bins made of durable polycarbonate material

## features



Bins stack with lids in place



Rear lip supports bin on hanging systems



Lids protect bin contents from dust




Dividers allow you to create customizable compartment sizes

### Outside Dimensions Inside Dimensions Inches Inches

Model No.	L	W	H	L	W	H	Capacity (lbs.)	Width Divider	Length Divider	Lid
305A1	5¾	4¾	3¼	4¼	3¾	2¾	10	415A1 (1)	405A1 (1)	305A2
305A3	7¾	4¾	3¼	6¼	3¾	2¾	10	415A1 (2)	405A3 (1)	305A4
305A5	10¾	4¾	3¼	9¼	3¾	2¾	15	415A1 (3)	405A5 (1)	305A6
305B1	10¾	5½	5¼	9¾	4¾	4¼	25	415B1 (3)	405B1 (1)	305B2

# in ( ) represents divider slots per bin



### Louvered Panel and Bin Combinations

Model No.	305A1	305A3	305A5	305B1
30618BEIGE	16	16	16	9
30636BEIGE	32	32	32	18
98600BEIGE	30	30	30	12

Bins sold separately

### ReadySpace™ Packages

Model No.	Description
30536A1	ReadySpace Wall Unit with 48ea. 305A1
30536A3	ReadySpace Wall Unit with 48ea. 305A3
30536A5	ReadySpace Wall Unit with 48ea. 305A5
30536B1	ReadySpace Wall Unit with 24ea. 305B1
30553A1	ReadySpace Mobile Floor Unit with 120ea. 305A1
30553A3	ReadySpace Mobile Floor Unit with 120ea. 305A3
30553A5	ReadySpace Mobile Floor Unit with 120ea. 305A5
30553B1	ReadySpace Mobile Floor Unit with 64ea. 305B1

\* US Patent Pending



# Shelf Bins

storage bins, racks & hanging systems




## features



Wide hopper front allows easy access



Built-in rear hanger allows bin to tilt out for complete access




Molded-in label area identifies contents

## accessories



**Dividers** create additional storage compartments. Each Bin accepts up to 7 dividers (except 30110)




**Extended Label Holders** are designed for larger bar code scanning



**Bin Cups** lift out easily for parts retrieval (see chart)

- Shelf Bins outlast corrugated bins – paying for themselves in reduced replacement costs
- Superior construction allows Shelf Bins to be fully loaded without spreading or cracking
- Durable polypropylene bins provide an attractive, neat appearance
- Works with 12", 18" and 24" deep shelving or vertical storage and retrieval units
- One-piece construction is waterproof and unaffected by grease or oil
- Available in 13 sizes and 5 colors: Red, Yellow, Blue, Green and White



## related products

Expand your sorting options with:

- Pick Rack Systems.....pg. 15
- Wire Shelving Systems.....pgs. 36-39
- Steel Shelving Systems .....pgs. 40-42

Shelf Bins & Accessories		Outside Dimensions Inches			Bottom Dimensions Inches			Cups per Bin		Accessories			
Ltr	Model No.	L	W	H	L	W	H	Ctn. Qty.	Small 30101	Large 30102	Optional Dividers*	Divider Pkg. Qty.	
	A	30110	11½"	2¾"	4"	10¼"	1½"	4"	24	3	–	–	–
		30120	11½"	4½"	4"	10¼"	3"	4"	24	5	2	40120	24
		30130	11½"	6½"	4"	10¼"	5½"	4"	12	9	4	40130	24
		30150	11½"	8½"	4"	10¼"	7½"	4"	12	11	4	40150	24
		30170	11½"	11½"	4"	10¼"	10"	4"	12	15	6	40170	24
	B	30128	17½"	4½"	4"	16½"	3"	4"	12	8	3	40120	24
		30138	17½"	6½"	4"	16½"	5½"	4"	12	15	6	40130	24
		30158	17½"	8½"	4"	16½"	7½"	4"	12	15	6	40150	24
		30178	17½"	11½"	4"	16½"	10"	4"	12	25	12	40170	24
	C	30124	23½"	4½"	4"	22½"	3"	4"	12	11	4	40120	24
		30164	23½"	6½"	4"	22½"	5½"	4"	6	21	8	40130	24
		30184	23½"	8½"	4"	22½"	7½"	4"	6	25	8	40150	24
		30174	23½"	11½"	4"	22½"	10"	4"	6	35	16	40170	24
	D	30101	2"	3¼"	3"	–	–	–	48	–	–	–	–
		30102	2¾"	5"	3"	–	–	–	24	–	–	–	–
Extended Label Holder	10°	40410	–	4"	2¼"	–	–	–	24	–	–	–	–
	45°	40445	–	4"	2¼"	–	–	–	24	–	–	–	–

\* 24 Dividers per package. One color per carton: Specify Red, Blue, Yellow, Green or White. Order in carton quantities.

# ShelfMax™

storage bins, racks & hanging systems

ShelfMax can be used with steel shelving, wire shelving, bench racks or pick racks



- Go deep! Expand your storage capacity up to 85% over traditional 4" bins
- Holding capacity is up to 25% more than comparable 6" bins
- Front opening is .75" higher than comparable products
- Superior, durable construction compared to corrugated bins
- Seven sizes and five color options: Red, Blue, Yellow, Green and White
- Optional width dividers keep items neatly separated
- Rolled ridge for added strength when filled to maximum capacity



## Maximize Your Storage Capacity!

- Available in five colors with optional width dividers – ShelfMax offers you the versatility you need to make the most of your storage space and keep everything in its place!
- Easy to label for quick inventory identification



APRBENCH with 30040 ShelfMax Bins  
See pg. 15

ShelfMax™	Model No.	Outside Dimensions Inches			Bottom Dimensions Inches			Storage Capacity			
		L	W	H	L	W	H	Cubic Inches	Ctn. Qty.	Optional Dividers	Divider Pkg. Qty.
	30040	11½"	4½"	6"	9¾"	2½"	5⅝"	175	16	40020	12
	30048	17½"	4½"	6"	16"	2½"	5⅝"	280	8	40020	12
	30080	11½"	8½"	6"	9¾"	6"	5⅝"	398	8	40040	12
	30088	17½"	8½"	6"	16"	6"	5⅝"	648	8	40040	12
	30090	11½"	6"	6"	9¾"	5"	5⅝"	310	10	40030	12
	30094	23½"	6"	6"	21¾"	5"	5⅝"	686	10	40030	12
	30098	17½"	6"	6"	16"	5"	5⅝"	505	10	40030	12

## features



Easy to carry with large handle




Large label area on front of bin



Dividers keep items neatly separated



Built-in rear hanglock allows bin to tilt out for complete access



Reinforced side ribs for added strength

## products related products

Use your ShelfMax bins with:

- Bench Pick Rack Systems ..... pg. 15
- Pick Rack Systems..... pg. 15
- Wire Shelving Systems ..... pgs. 36-39
- Steel Shelving Systems..... pgs. 40-42

# EarthSaver™ Series: Shelf Bins

storage bins, racks & hanging systems



- Shelf Bins now made from 100% recycled material
- Three color options – Hunter Green, Sandstone and Terra Cotta
- Optional dividers keep items neatly separated
- An eco-friendly choice in storage and organization products






## products related products

Create the perfect storage system – mix and match your selection of bins with compatible products including:

- Wire Shelving Systems ..... pgs. 36-39
- Steel Shelving Systems ..... pgs. 40-42
- Bin Cabinets ..... pgs. 43-44

## Go Green With 100% Recycled Bins – Boost Productivity, Reduce Waste!


Feeling the need to “Go Green”? Akro-Mils introduces the **EarthSaver Series** – Shelf Bins and AkroBins (see pg. 6) made from 100% recycled plastic. Make a positive impact on the environment!

Shelf Bins & Accessories	Model No.	Outside Dimensions Inches			Inside Dimensions Inches			Ctn. Qty.	Cups per Bin		Accessories	
		L	W	H	L	W	H		Small 30101	Large 30102	Optional Dividers*	Divider Pkg. Qty.
 12" Shelf Bins	30120RECYSS	11½"	4¾"	4"	10¼"	3"	4"	24	5	2	40120	24
	30120RECYTC	11½"	4¾"	4"	10¼"	3"	4"	24	5	2	40120	24
	30120RECYHG	11½"	4¾"	4"	10¼"	3"	4"	24	5	2	40120	24
	30130RECYSS	11½"	6"	4"	10¼"	5½"	4"	12	9	4	40130	24
	30130RECYTC	11½"	6"	4"	10¼"	5½"	4"	12	9	4	40130	24
	30130RECYHG	11½"	6"	4"	10¼"	5½"	4"	12	9	4	40130	24
 18" Shelf Bins	30128RECYSS	17½"	4¾"	4"	16½"	3"	4"	12	8	3	40120	24
	30128RECYTC	17½"	4¾"	4"	16½"	3"	4"	12	8	3	40120	24
	30128RECYHG	17½"	4¾"	4"	16½"	3"	4"	12	8	3	40120	24
	30138RECYSS	17½"	6"	4"	16½"	5½"	4"	12	15	6	40130	24
	30138RECYTC	17½"	6"	4"	16½"	5½"	4"	12	15	6	40130	24
	30138RECYHG	17½"	6"	4"	16½"	5½"	4"	12	15	6	40130	24
 24" Shelf Bins	30124RECYSS	23½"	4¾"	4"	22½"	3"	4"	12	11	4	40120	24
	30124RECYTC	23½"	4¾"	4"	22½"	3"	4"	12	11	4	40120	24
	30124RECYHG	23½"	4¾"	4"	22½"	3"	4"	12	11	4	40120	24
	30164RECYSS	23½"	6"	4"	22½"	5½"	4"	6	21	8	40130	24
	30164RECYTC	23½"	6"	4"	22½"	5½"	4"	6	21	8	40130	24
	30164RECYHG	23½"	6"	4"	22½"	5½"	4"	6	21	8	40130	24

One color per carton: SS = Sandstone, TC = Terra Cotta and HG = Hunter Green. Order in carton quantities.

Bin Cups	L	W	H	Ctn. Qty.
30101	2"	3¾"	3"	48
30102	2¾"	5"	3"	24

Extended Label Holder	W	H	Ctn. Qty.	
10°	40410	4"	2¼"	24
45°	40445	4"	2¼"	24





# Pick Rack Systems

storage bins, racks & hanging systems

- Improve workspace organization and efficiency with rack and bin systems
- Angled shelves keep parts at the front of bins for easy access
- Convenient, high-density storage with up to 192 bins
- Easy to assemble
- Choose from 3 styles available separately or with bin packages
- 16-gauge steel construction
- Compatible with:



Shelf Bins, pgs. 12-14



ShelfMax™, pg. 13



Indicator™ Bins, pg. 21


## features



Angled shelves keep parts at front of bin



**NEW**  
product!



### Single-Sided Pick Rack

- Model No. APRS36442BLU
- Holds up to 64 Indicator Bins on 8 shelves
- Holds up to 64 ShelfMax Bins
- Maximum 400 lb. weight capacity

**NEW**  
product!



### Double-Sided Pick Rack & Mobile Kit

- Model No. APRD120Y
- Creates a mobile, double-sided pick rack with APRDMOBILE
- Holds up to 192 Shelf Bins
- Holds up to 128 ShelfMax Bins
- Maximum 800 lb. weight capacity for Double-Sided Pick Rack, 500 lb. weight capacity when used with Mobile Kit

**NEW**  
product!



### Bench Pick Rack

- Model No. APRBENCH040
- 12" D x 36 $\frac{3}{4}$ " W x 25" H
- Holds up to 24 Shelf Bins or ShelfMax Bins
- Holds up to (3) 30312 System Bins

### Single-Sided 12" D x 36 $\frac{3}{4}$ " W x 60 $\frac{1}{4}$ " H

### Bin Dimensions (Inches)

Model No.	Description	Bin Model No.	L	W	H	Bin Qty.	Bonus Bins*
APRS	Single-Sided Pick Rack (no bins)	-	-	-	-	-	-
APRS110Y	Rack with Shelf Bins	30110YELLO	11 $\frac{1}{8}$ "	2 $\frac{3}{4}$ "	4"	96	-
APRS120Y	Rack with Shelf Bins	30120YELLO	11 $\frac{1}{8}$ "	4 $\frac{1}{8}$ "	4"	64	8
APRS130Y	Rack with Shelf Bins	30130YELLO	11 $\frac{1}{8}$ "	6 $\frac{1}{8}$ "	4"	40	8
APRS150Y	Rack with Shelf Bins	30150YELLO	11 $\frac{1}{8}$ "	8 $\frac{1}{8}$ "	4"	32	4
APRS170Y	Rack with Shelf Bins	30170YELLO	11 $\frac{1}{8}$ "	11 $\frac{1}{8}$ "	4"	24	-
APRS040**	Rack with ShelfMax	30040	11 $\frac{1}{8}$ "	4 $\frac{1}{8}$ "	6"	64	-
APRS080**	Rack with ShelfMax	30080	11 $\frac{1}{8}$ "	8 $\frac{1}{8}$ "	6"	32	-
APRS090**	Rack with ShelfMax	30090	11 $\frac{1}{8}$ "	6 $\frac{1}{8}$ "	6"	40	-
APRSAST00**	Rack with ShelfMax	30040 / 30090	See above			32 / 20	-
APRS36442B	Rack with Indicator Bins	36442BLUE	11 $\frac{1}{8}$ "	4 $\frac{1}{4}$ "	4"	64	8
APRS36462B	Rack with Indicator Bins	36462BLUE	11 $\frac{1}{8}$ "	6 $\frac{1}{4}$ "	4"	40	8

\*Due to case pack, Bonus Bins are included at no extra charge. \*\*Specify color of bins when ordering: Red, Blue, Yellow, Green or White.

### Double-Sided 24" D x 36 $\frac{3}{4}$ " W x 60 $\frac{1}{4}$ " H

### Bin Dimensions (Inches)

Model No.	Description	Bin Model No.	L	W	H	Bin Qty.	Bonus Bins*
APRD	Double-Sided Pick Rack (no bins)	-	-	-	-	-	-
APRD110Y	Rack with Shelf Bins	30110YELLO	11 $\frac{1}{8}$ "	2 $\frac{3}{4}$ "	4"	192	-
APRD120Y	Rack with Shelf Bins	30120YELLO	11 $\frac{1}{8}$ "	4 $\frac{1}{8}$ "	4"	128	16
APRD130Y	Rack with Shelf Bins	30130YELLO	11 $\frac{1}{8}$ "	6 $\frac{1}{8}$ "	4"	80	4
APRD150Y	Rack with Shelf Bins	30150YELLO	11 $\frac{1}{8}$ "	8 $\frac{1}{8}$ "	4"	64	8
APRD170Y	Rack with Shelf Bins	30170YELLO	11 $\frac{1}{8}$ "	11 $\frac{1}{8}$ "	4"	48	-
APRD040**	Rack with ShelfMax	30040	11 $\frac{1}{8}$ "	4 $\frac{1}{8}$ "	6"	128	-
APRD080**	Rack with ShelfMax	30080	11 $\frac{1}{8}$ "	8 $\frac{1}{8}$ "	6"	64	-
APRD090**	Rack with ShelfMax	30090	11 $\frac{1}{8}$ "	6 $\frac{1}{8}$ "	6"	80	-
APRDAST00**	Rack with ShelfMax	30040 / 30090	See above			64 / 40	-
APRD36442B	Rack with Indicator Bins	36442BLUE	11 $\frac{1}{8}$ "	4 $\frac{1}{4}$ "	4"	128	16
APRD36462B	Rack with Indicator Bins	36462BLUE	11 $\frac{1}{8}$ "	6 $\frac{1}{4}$ "	4"	80	4
APRDMOBILE	Mobile Kit (Handle & Dolly) for Double-Sided Pick Rack						

\*Due to case pack, Bonus Bins are included at no extra charge. \*\*Specify color of bins when ordering: Red, Blue, Yellow, Green or White. When using the mobile kit weight capacity is 500 lbs.

### Bench Rack 12" D x 36 $\frac{3}{4}$ " W x 25" H

### Bin Dimensions (Inches)

Model No.	Description	Bin Model No.	L	W	H	Bin Qty.
APRBENCH	Bench Pick Rack, No Bins	-	-	-	-	-
APRBENCH120	Bench Pick Rack with Shelf Bins	30120YELLO	11 $\frac{1}{8}$ "	4 $\frac{1}{8}$ "	4"	24
APRBENCH150	Bench Pick Rack with Shelf Bins	30150YELLO	11 $\frac{1}{8}$ "	8 $\frac{1}{8}$ "	4"	12
APRBENCH040*	Bench Pick Rack with ShelfMax	30040	11 $\frac{1}{8}$ "	4 $\frac{1}{8}$ "	6"	24
APRBENCH090*	Bench Pick Rack with ShelfMax	30090	11 $\frac{1}{8}$ "	6 $\frac{1}{8}$ "	6"	15

\*Specify color of bins when ordering: Red, Blue, Yellow, Green or White.

## accessories



### APRDMOBILE Mobile Kit

For double-sided Pick Rack  
4" x 2" Phenolic Casters

# AkroDrawers™

storage bins, racks & hanging systems

- Available in five convenient sizes and five colors – including Crystal Clear – which keeps AkroDrawer contents highly visible!
- Colors made of high-impact polystyrene
- Crystal Clear made of durable acrylic blend
- Offered in 12" or 18" depths to work with compatible shelving
- Easy to label and color code inventory for quick identification of parts and supplies
- Drawers can be stacked to optimize space
- Wide front handle for easy gripping when AkroDrawers are loaded or contain heavy contents
- Dividers available to keep contents neatly separated in drawers
- Colors: Crystal Clear, Red, Blue, Yellow and Gray



## AkroDrawers™



## AkroDrawers

### Cover, Store, Protect & More!

- Designed for use in a variety of environments – from industrial to healthcare to other applications, AkroDrawers will help keep supplies, parts, tools and other materials secure and dust-free.
- Can be used with available shelving, racks, mobile carts or can be used by themselves

## features



Sturdy backstop tab ensures AkroDrawers can hang securely from shelves




Features a wide front handle for easy gripping when full or filled with heavy contents

AkroDrawers™ Model No.	Outside Dimensions Inches			Bottom Dimensions Inches			Weight Capacity	Ctn. Qty.	Dividers
	L	W	H	L	W	H			
31142	11 <sup>11</sup> / <sub>16</sub>	3 <sup>3</sup> / <sub>4</sub>	4 <sup>1</sup> / <sub>2</sub>	10 <sup>1</sup> / <sub>4</sub>	3	4 <sup>7</sup> / <sub>16</sub>	15 lbs.	6	41440
31162	11 <sup>11</sup> / <sub>16</sub>	5 <sup>5</sup> / <sub>16</sub>	4 <sup>1</sup> / <sub>2</sub>	10 <sup>1</sup> / <sub>4</sub>	4 <sup>7</sup> / <sub>16</sub>	4 <sup>7</sup> / <sub>16</sub>	20 lbs.	6	41460
31182	11 <sup>11</sup> / <sub>16</sub>	8 <sup>1</sup> / <sub>2</sub>	4 <sup>1</sup> / <sub>2</sub>	10 <sup>1</sup> / <sub>4</sub>	7 <sup>7</sup> / <sub>16</sub>	4 <sup>7</sup> / <sub>16</sub>	20 lbs.	4	41480
31168	17 <sup>17</sup> / <sub>16</sub>	5 <sup>5</sup> / <sub>16</sub>	4 <sup>1</sup> / <sub>2</sub>	16 <sup>1</sup> / <sub>4</sub>	4 <sup>7</sup> / <sub>16</sub>	4 <sup>7</sup> / <sub>16</sub>	25 lbs.	6	41460
31188	17 <sup>17</sup> / <sub>16</sub>	8 <sup>1</sup> / <sub>2</sub>	4 <sup>1</sup> / <sub>2</sub>	16 <sup>1</sup> / <sub>4</sub>	7 <sup>7</sup> / <sub>16</sub>	4 <sup>7</sup> / <sub>16</sub>	25 lbs.	4	41480

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear.

Dividers		Dimensions			
Model No.	W	H	D	Pkg. Qty.	Ctn. Qty.
41440	3 <sup>3</sup> / <sub>16</sub>	4 <sup>1</sup> / <sub>5</sub>	1 <sup>13</sup> / <sub>16</sub>	6	30
41460	5 <sup>21</sup> / <sub>64</sub>	4 <sup>1</sup> / <sub>5</sub>	1 <sup>13</sup> / <sub>16</sub>	6	26
41480	8 <sup>8</sup> / <sub>64</sub>	4 <sup>1</sup> / <sub>5</sub>	1 <sup>1</sup> / <sub>10</sub>	6	26



# Super Modular Cabinets

storage bins, racks & hanging systems

- Organize your AkroDrawers on specially designed stackable or wall-mountable cabinets
- Units can be safely stacked up to three high
- AkroDrawers fit snugly on each shelf so open top on each AkroDrawer is protected from dust and debris
- Drawers hang securely in place from shelves by sturdy backstop tab
- Ships fully assembled
- 11" cabinets can be mounted to wall (light assembly required for wall mounting)
- Durable powder-coated finish
- Weight capacity:  
60 lbs. 18" Modular Cabinets  
75 lbs. 24" Modular Cabinets
- Combined stack weight capacity: 100 lbs.
- Colors: Textured Charcoal Gray or Textured Putty



AD1811P62



AD1817CAST



AD2311CAST



Small and Medium Super Modular Cabinets can be mounted on two rails under ProCart. Optional two-rail hanging system (No. 30902) required.



## features



For secure stacking, special feet nest into recessed dimples in the top of the cabinets

### Super Modular Cabinets 18" W x 11" D x 16-1/2" H

Model Number	Description	Cabinet Color	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers
			L	W	H	D	L	H	
AD1811C AD1811P	Small Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	11	17	4 1/2	-
AD1811C62 AD1811P62	Small Cabinet with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11 1/2	5 1/2	4 1/2	11	17	4 1/2	9
AD1811C82 AD1811P82	Small Cabinet with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11 1/2	8 1/2	4 1/2	11	17	4 1/2	6
AD1811CAST AD1811PAST	Small Cabinet with 31162 and 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			11	17	4 1/2	6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

### Super Modular Cabinets 23" W x 11" D x 16-1/2" H


Model Number	Description	Cabinet Color	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers
			L	W	H	D	L	H	
AD2311C AD2311P	Medium Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	11	22 3/4	4 1/2	-
AD2311C42 AD2311P42	Medium Cabinet with 31142 AkroDrawers	Textured Charcoal Gray Textured Putty	11 1/2	3 3/4	4 1/2	11	22 3/4	4 1/2	18
AD2311C62 AD2311P62	Medium Cabinet with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11 1/2	5 1/2	4 1/2	11	22 3/4	4 1/2	12
AD2311CAST AD2311PAST	Medium Cabinet with 31142 and 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			11	22 3/4	4 1/2	6 / 8

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

### Super Modular Cabinets 18" W x 17" D x 16-1/2" H

Model Number	Description	Cabinet Color	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers
			L	W	H	D	L	H	
AD1817C AD1817P	17" Deep Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	17	17	4 1/2	-
AD1817C68 AD1817P68	17" Deep Cabinet with 31168 AkroDrawers	Textured Charcoal Gray Textured Putty	17 1/2	5 1/2	4 1/2	17	17	4 1/2	9
AD1817C88 AD1817P88	17" Deep Cabinet with 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	17 1/2	8 1/2	4 1/2	17	17	4 1/2	6
AD1817CAST AD1817PAST	17" Deep Cabinet with 31168 and 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			17	17	4 1/2	6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.



# Stackable Cabinets

storage bins, racks & hanging systems


- Increased storage capacity for AkroDrawers by providing more space to organize and color code inventory
- Units can be safely stacked up to three high
- Available in two sizes – one for 12" AkroDrawers and one for 18" AkroDrawers
- Optional 8" high Base Stands for each size cabinet available in matching colors for either cabinet – keeps cabinets off the floor for easier clean-up underneath
- Durable powder-coated finish
- Cabinets ship fully assembled
- Weight capacity: 120 lbs.
- Combined stacked weight capacity: 200 lbs.
- Colors for Stackable Cabinets and optional Base Stands: Textured Charcoal Gray or Textured Putty



AD3511PAST

AD3517PAST

AD3517BS



Stacking a 12" deep cabinet on top of an 18" cabinet provides additional work space for sorting and organizing

## features



For secure stacking, special feet nest into recessed dimples in the top of the cabinets



Optional Base Stands provide eight more inches of height for easier, more comfortable access to lower shelves

Stackable Cabinet 35"W x 11"D x 22"H

Model Number	Description	Cabinet Color	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers
			L	W	H	D	L	H	
AD3511C AD3511P	Stackable Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	11	34	4 <sup>1</sup> / <sub>2</sub>	-
AD3511C42 AD3511P42	Stackable Cabinet with 31142 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	3%	4%	11	34	4 <sup>1</sup> / <sub>2</sub>	32
AD3511C62 AD3511P62	Stackable Cabinet with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	5%	4%	11	34	4 <sup>1</sup> / <sub>2</sub>	24
AD3511C82 AD3511P82	Stackable Cabinet with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	8%	4%	11	34	4 <sup>1</sup> / <sub>2</sub>	16
AD3511CAST AD3511PAST	Stackable Cabinet with 31142, 31162 & 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			11	34	4 <sup>1</sup> / <sub>2</sub>	8 / 12 / 4

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

Stackable Cabinet 35"W x 17"D x 22"H

Model Number	Description	Cabinet Color	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers
			L	W	H	D	L	H	
AD3517C AD3517P	Stackable Cabinet with no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	17	34	4 <sup>1</sup> / <sub>2</sub>	-
AD3517C68 AD3517P68	Stackable Cabinet with 31168 AkroDrawers	Textured Charcoal Gray Textured Putty	17%	5%	4%	17	34	4 <sup>1</sup> / <sub>2</sub>	24
AD3517C88 AD3517P88	Stackable Cabinet with 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	17%	8%	4%	17	34	4 <sup>1</sup> / <sub>2</sub>	16
AD3517CAST AD3517PAST	Stackable Cabinet with 31168 & 31188 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			17	34	4 <sup>1</sup> / <sub>2</sub>	12 / 8

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

Color code: B=Blue, CRY=Crystal Clear, GR=Gray, R=Red, Y=Yellow

Optional Base Stands for Stackable Cabinets Dimensions



Model No.	Description	Base Stand Color	W	D	H
AD3511BS	Base Stand for 11" Stackable Cabinet	Textured Charcoal Gray or Textured Putty	35 <sup>1</sup> / <sub>2</sub>	11 <sup>1</sup> / <sub>2</sub>	8
AD3517BS	Base Stand for 17" Stackable Cabinet	Textured Charcoal Gray or Textured Putty	35 <sup>1</sup> / <sub>2</sub>	17 <sup>1</sup> / <sub>2</sub>	8




# Secure Mini-Cabinets

storage bins, racks & hanging systems



- Lockable cabinet provides secure storage for sensitive supplies
- Accommodates 12" AkroDrawers
- Made from 18-gauge steel
- Wall mountable
- Features standard four adjustable shelves with fully louvered panel built into back for hanging AkroBins®
- Available with a quick-view door to keep contents visible
- Solid door option keeps sensitive contents secure and out of sight
- Foam gasket around door frame seals out dust
- Welded frame and durable powder-coated finish
- Ships fully assembled
- Weight capacity: 350 lbs.
- Colors: Textured Charcoal Gray or Textured Putty

## features




Quick-View Door keeps cabinet contents visible



Solid Door option keeps sensitive contents out of sight



Lockable latch rotates and recesses into door when closed for flush look



Louvered back panel extends organizing options



ACQV4P62



ACS4C



### Quick-View Mini-Cabinet 19-1/4"W x 13-1/4"D x 38"H

Model Number	Description	Cabinet Color	L	W	H	Qty. of Drawers
ACQV4C ACQV4P	Secure Mini-Cabinet, Quick-View Door, no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	-
ACQV4C42 ACQV4P42	Secure Mini-Cabinet, Quick-View Door with 31142 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	3%	4%	16
ACQV4C62 ACQV4P62	Secure Mini-Cabinet, Quick-View Door with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	5%	4%	12
ACQV4C82 ACQV4P82	Secure Mini-Cabinet, Quick-View Door with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	8%	4%	8
ACQV4CAST ACQV4PAST	Secure Mini-Cabinet, Quick-View Door with 31142, 31162 & 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			4 / 6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.

### Steel Door Mini-Cabinet 19-1/4"W x 13-1/4"D x 38"H

Model Number	Description	Cabinet Color	L	W	H	Qty. of Drawers
ACS4C ACS4P	Secure Mini-Cabinet, Steel Door, no AkroDrawers	Textured Charcoal Gray Textured Putty	-	-	-	-
ACS4C42 ACS4P42	Secure Mini-Cabinet, Steel Door with 31142 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	3%	4%	16
ACS4C62 ACS4P62	Secure Mini-Cabinet, Steel Door with 31162 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	5%	4%	12
ACS4C82 ACS4P82	Secure Mini-Cabinet, Steel Door with 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	11%	8%	4%	8
ACS4CAST ACS4PAST	Secure Mini-Cabinet, Steel Door with 31142, 31162 & 31182 AkroDrawers	Textured Charcoal Gray Textured Putty	See Above			4 / 6 / 2

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear available with Gray Cabinet. Blue or Crystal Clear available with Putty Cabinet. Only one color per unit.



# 12" & 18" Enclosed Steel Shelving Systems

storage bins, racks & hanging systems



- Steel shelving will accommodate new 12" and 18" AkroDrawers
- Manufactured from high-grade, 22-gauge steel with powder-coated finish
- Can be ordered independently or purchased with AkroDrawers for a complete system
- Closed back and sides keep drawers contained to one side of shelves and further eliminate dust and debris
- Drawers can hang securely in place from shelves by sturdy backstop tab
- Easy to assemble using shelf clips
- Each shelving system can hold up to a maximum of 8,500 lbs.
  - 12" x 36" shelf holds 500 lbs.
  - 18" x 36" shelf holds 550 lbs.
- Color: Gray

## Pick Racks



- Angled shelves keep parts and supplies at the front of AkroDrawers for easy access
- Improve workspace organization and efficiency
- 16-gauge steel construction
- Durable powder-coated finish
- Weight capacity: 400 lbs. Single-Sided; Up to 800 lbs. Double-Sided
- Color: Gray



## accessories



**APRDMOBILE**  
Mobile Kit  
For double-sided  
Pick Rack



### 12" Enclosed Shelving Systems (13 Shelves)

Model Number	Description	Drawer Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers	Drawer Color
			L	W	H	D	L	H		
ASC1279	Shelving (no AkroDrawers)	-	-	-	-	12	36	79	-	-
ASC1279142	Shelving with AkroDrawers	31142	11%	3%	4%	12	36	79	96	R,B,Y,GRY,CRY
ASC1279162	Shelving with AkroDrawers	31162	11%	5%	4%	12	36	79	72	R,B,Y,GRY,CRY
ASC1279182	Shelving with AkroDrawers	31182	11%	8%	4%	12	36	79	48	R,B,Y,GRY,CRY
ASC1279AST	Shelving with AkroDrawer Mix	31142, 31162, 31182	See Above			12	36	79	27 / 36 / 12	R,B,Y,GRY,CRY

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear. Only one color per unit.

### 18" Enclosed Shelving Systems (13 Shelves)

Model Number	Description	Drawer Model No.	Bin Dimensions (Inches)			Shelf Dimensions (Inches)			Qty. of Drawers	Drawer Color
			L	W	H	D	L	H		
ASC1879	Shelving (no AkroDrawers)	-	-	-	-	18	36	79	-	-
ASC1879168	Shelving with AkroDrawers	31168	17%	5%	4%	18	36	79	72	R,B,Y,GRY,CRY
ASC1879188	Shelving with AkroDrawers	31188	17%	8%	4%	18	36	79	48	R,B,Y,GRY,CRY
ASC1879AST	Shelving with AkroDrawer Mix	31168, 31188	See Above			18	36	79	36 / 24	R,B,Y,GRY,CRY

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear. Only one color per unit.

### Single-Sided Pick Rack 12" D x 36-3/4" W x 60-1/4" H (8 Shelves)

Model Number	Description	Drawer Model No.	Drawer Dimensions			Qty. of Drawers	Drawer Color
			L	W	H		
APRS142	Rack with AkroDrawers	31142	11%	3%	4%	72	R,B,Y,GRY,CRY
APRS162	Rack with AkroDrawers	31162	11%	5%	4%	48	R,B,Y,GRY,CRY
APRS182	Rack with AkroDrawers	31182	11%	8%	4%	32	R,B,Y,GRY,CRY
APRSAST	Rack with AkroDrawer Mix	31142, 31162, 31182	See Above			18 / 24 / 8	R,B,Y,GRY,CRY

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear. Only one color per unit.

### Double-Sided Pick Rack 24" D x 36-3/4" W x 60-1/4" H (16 Shelves)

Model Number	Description	Drawer Model No.	Drawer Dimensions			Qty. of Drawers	Drawer Color
			L	W	H		
APRD142	Rack with AkroDrawers	31142	11%	3%	4%	144	R,B,Y,GRY,CRY
APRD162	Rack with AkroDrawers	31162	11%	5%	4%	96	R,B,Y,GRY,CRY
APRD182	Rack with AkroDrawers	31182	11%	8%	4%	64	R,B,Y,GRY,CRY
APRDAST	Rack with AkroDrawer Mix	31142, 31162, 31182	See Above			36 / 48 / 16	R,B,Y,GRY,CRY

Specify drawer color when ordering: Red, Blue, Yellow, Gray or Crystal Clear. Only one color per unit. Color code: B=Blue, CRY=Crystal Clear, GRY=Gray, R=Red, Y=Yellow. When using the APRD with the mobile kit, weight capacity is 500 lbs.



## Indicator Stock, Pick, Flip & Replenish

**STOCK** the Indicator Bin using the divider to designate volume for the inventory reserve.

**PICK** from the blue side of the bin until you reach the divider.

**FLIP** the bin to the orange reserve to indicate inventory levels are low.

**REPLENISH** the bin and repeat!




- Easy organization of supplies and work-in-process
- Reduces excess inventory
- Width dividers used for orange reserve to prevent stock-outs and assembly line interruptions
- Works with 14" wire shelving, 12" steel shelving or with pick rack systems

## Indicator™ Bins – Effective inventory control at a glance!

The Indicator Bin simplifies visual recognition when supplies need to be replenished. An innovative, low-cost alternative to high-end inventory control systems!

### Pick Rack Systems




- Available as single-sided or double-sided
- Angled shelves keep parts at the front of bins for easy access
- 16-gauge steel construction
- 400-800 lb. weight cap.
- See page 15 for bin quantity

### Steel Shelving Systems




- Manufactured from high-grade, 22-gauge steel with a powder-coated finish
- Easy assembly
- Holds (96) 36442BLUE bins and (60) 36462BLUE bins
- 500 lb. weight capacity per shelf, up to 8,500 lbs.

### Wire Shelving Systems



- Constructed from steel with a chrome finish for durability and strength
- Open wire design minimizes dust collection and improves visibility
- Holds (88) 36442BLUE bins and (55) 36462BLUE bins
- 2,000 lb. max. weight capacity per unit

## features



Bright orange trigger color used in Lean and 5S initiatives



Innovative double hopper bin can be filled or picked from both sides



Large label area on both sides for part identification or bar code scanning



Rolled ridge provides added strength and durability




Width dividers used for orange reserve to prevent stock-outs and assembly line interruptions

## related products

Create the perfect storage system – mix and match your selection of Indicator Bins with compatible products including:

- Pick Racks ..... pg. 15
- Wire Shelving Systems ..... pgs. 36-39
- Steel Shelving Systems ..... pgs. 40-42



### Indicator Bins

### Outside Dimensions

### Inside Bottom Dimensions

	Model No.	Description	L	W	H	L	W	H	Bin Ctn. Qty.	Divider*	Divider Pkg. Qty.
	36442BLUE	Indicator Bin (Blue/Orange)	11 $\frac{1}{2}$ "	4 $\frac{1}{4}$ "	4"	9 $\frac{9}{16}$ "	2 $\frac{9}{16}$ "	3 $\frac{3}{16}$ "	24	40120	24
	36462BLUE	Indicator Bin (Blue/Orange)	11 $\frac{1}{2}$ "	6 $\frac{3}{4}$ "	4"	9 $\frac{9}{16}$ "	5 $\frac{3}{8}$ "	3 $\frac{3}{16}$ "	12	40130	24

\*Dividers Sold Separately

\* US Patent Pending



## Efficient Organization with Customizable Storage

### Dividable VantageBin™


- Sturdy bin holds dovetailed dividers to customize compartments
- Fits on standard 24" deep or wide shelving and counters
- Bins nest when empty to conserve storage space
- 24" x 5½" x 7" bin is dividable in up to 10 sections
- Sturdy polypropylene construction
- Available in two colors: White and Gray
- Longer and taller than VantageBin
- 9 divider positions per bin



## features




Corner ribs prevent jamming when nested



Rolled rim for added strength and durability



Dovetailed design securely locks dividers in, maintaining bin shape under heavy loads



Molded-in V-grooves on the VantageBin create non-slip surface on inside bottom

### VantageBin™

- Molded-in V-groove bottom keeps items upright and prevents them from sliding without dividers
- Bins nest when empty to conserve storage space
- Durable, injection-molded polypropylene construction
- Quick, easy access and identification when organizing envelopes, bags, jewel cases, photographs and more
- Ideal for retail and material handling as well as home and office storage applications
- Available in three colors: White, Gray and Yellow

VantageBin	Model No.	Description	Outside Dimensions Inches			Inside Dimensions Inches				Ctn. Qty.	Dividers/Pk.
			L	W	H	L	W	H	X		
	30420WH16PK	Dividable Bin	24	5½	7	22¾	3½	7	22¾	6	40420/12
	30420GRY6PK	Dividable Bin	24	5½	7	22¾	3½	7	22¾	6	40420/12
	30400YEL10PK	Standard Bin	16¾	7¼	5½	15½	6¾	5½	15½	10	-
	30400WH10PK	Standard Bin	16¾	7¼	5½	15½	6¾	5½	15½	10	-
	30400GRY10PK	Standard Bin	16¾	7¼	5½	15½	6¾	5½	15½	10	-

One color per carton: Specify color when ordering. Order in carton quantities. Weight capacity per bin is 40 lbs.



## related products

Organize your VantageBin on:

- Wire Shelving Systems ..... pgs. 36-39
- Steel Shelving Systems ..... pgs. 40-42



# 1800 Series AkroBins<sup>®</sup>, ESD Containers & Economy Bins

storage bins, racks & hanging systems



## 1800 Series AkroBins

- Strong, durable copolymer polypropylene construction
- Storage systems for large, heavy and bulky items
- One black crosswise divider included per bin
- Color: Beige



## ESD Containers

- Akro-Mils ESD containers dissipate electrostatic charges, which can severely damage sensitive electronic components
- Grounding Wire 98100 – Designed to convert existing Akro-Mils rail and hanging systems (see pgs. 8-9). Conducts static charges away from the storage system

## accessories



Grounding Wire  
98100

## Economy Bins

- Versatile Economy Bins make full use of shelf depth on 12" or 18" deep shelving and stack to fill space between shelves
- The only small parts bin that can nest and stack
- Molded from copolymer polypropylene
- Generous opening allows easy access to stacked items

### 1800 Series

Model No.	Outside Dimensions Inches			Inside Dimensions Inches				Ctn. Qty.	Dividers	Pkg. Qty.	Capacity (lbs.)
	L	W	H	L	W	H	X				
30348BEIGE	20½	8¼	7	20	7¾	6½	20	6	40348 (3)	6	60
30358BEIGE	20½	11	7	20	10½	6½	20	6	40358 (3)	6	75

Available in Beige. Order in carton quantities.

### ESDs

Model No.	Outside Dimensions Inches			Inside Dimensions Inches				Cap. on Rack	Ctn. Qty.
	L	W	H	L	W	H	X		
30210ESD	5¾	4¼	3	4¾	3¼	2¾	4	10 lbs.	24
30220ESD	7¾	4¼	3	6¾	3¼	2¾	6	10 lbs.	24
30230ESD	10¾	5½	5	10¼	4¾	4¾	9	30 lbs.	12
30235ESD	10¾	11	5	10¼	10	4¾	9	50 lbs.	6
30240ESD	14¾	8¼	7	14	6¾	6¾	12	60 lbs.	12

Order in carton quantities.


### Economy Bins

Model No.	Outside Dimensions Inches			Inside Dimensions Inches			Ctn. Qty.
	L	W	H	L	W	H	
30796BLACK	8¾	6¾	5	6¾	4	4¼	10 each
30716BLACK	11¾	6¾	5	9¾	4	4¼	10 each
30776BLACK	17¾	6¾	7	14¾	3¾	6¼	10 each
30718BLACK	11¾	8¾	5	9	5¾	4¼	8 each
30778BLACK	17¾	8¾	7	14¾	5½	6¼	8 each

Order in carton quantities.



1800 Series AkroBins



ESD Container




Economy Bins



**Nests When Empty**  
 • Saves space in storage areas

## Convenient, Efficient Organization in a Single-Piece Six-Bin Unit

- Configured six across in a single unit, 33" wide x 5" high
- Available in 12" or 18" depths to fit standard shelving
- Separate and sort parts to increase efficiency, shorten assembly times and maintain accurate inventories
- A cost-efficient alternative to flimsy, individual cardboard boxes
- Can be safely stacked using a 3/8" wood dowel rod
- Available colors: Blue, Red, Yellow and Green



System Bins shown on Steel Shelving

## related products



**APRBENCH**  
 • Holds (3) 30312 System Bins

System Bins work great with:


- Pick Rack Systems ..... pg. 15
- Wire Shelving Systems ..... pgs. 36-39
- Steel Shelving Systems ..... pgs. 40-42

## features



Large label area for easy content identification  
 Smooth surfaces. Easy to fill, handle and keep clean  
 Sturdy interior double wall construction. One-piece, injection-molded for durability  
 Wide hopper front allows easy access for quick parts picking

### System Bins

Model No.	Description	Dimensions Inches			Bin Compartment Dimensions** Inches			Ctn. Qty.
		L	W	H	L	W	H	
 30312	12" System Bin	12	33	5	10%	3 <sup>13</sup> / <sub>50</sub>	4 <sup>47</sup> / <sub>50</sub>	5
30318	18" System Bin	18	33	5	16%	3 <sup>13</sup> / <sub>50</sub>	4 <sup>93</sup> / <sub>100</sub>	5
40312*	System Bin Divider (Black only)	¼	4%	4%	–	–	–	6 pk.


One color per carton: Specify Red, Blue, Yellow or Green. Order in carton quantities. \*One divider per compartment, six per unit. \*\*Inside dimension per compartment.

### Shelving Systems

Model No.	Description	Dimensions Inches				Bin Qty.
		L	W	H		
 APRBENCH	Bench Pick Rack	36¾	12	25	‡	
AS1279312	12" Shelving Unit	36	12	79	10*	
AS1879318	18" Shelving Unit	36	18	79	10**	

‡Order bins separately. Specify bin color when ordering. \*Qty. of 30312 System Bins included. \*\*Qty. of 30318 System Bins included.

### Cart Systems


Model No.	Description	Dimensions Inches				Bin Qty.
		L	W	H		
 R5SYT5HR2436	Multi-Shelf Cart (5 shelves)	36	24½	40	10*	
R5SYT8MR2436	Multi-Shelf Cart (5 shelves)	36	24½	43	10*	
R5SYT5HR3636	Multi-Shelf Cart (5 shelves)	36	36½	40	10**	
R5SYT8MR3636	Multi-Shelf Cart (5 shelves)	36	36½	43	10**	

Specify bin color when ordering. \*Qty. of 30312 System Bins included. \*\*Qty. of 30318 System Bins included.

## accessories



System Bin Divider





# Easy Flow Gravity Hopper

storage bins, racks & hanging systems

New Size!

## A Unique Way to Improve Workflow!

- Unique hopper provides exceptional product storage, while saving space through a compact vertical design
- Large, angled top opening allows easy filling, whether used on the Gravity Hopper Floor Rack or on a work platform
- Generous picking area provides easy access to the loaded product, while keeping it neatly contained and sorted
- Great for: fasteners, assembly areas, kanban, inventory stock, merchandise and work cells
- 31620 – 50 lb. capacity, 31625 – 75 lbs. capacity per hopper
- Rotational-molded for strength and durability – LLDPE
- Allows for proper lot rotation




31620 BLUE




- 31620 – New smaller size option**
- First-In-First-Out (FIFO) sliding divider shelf helps eliminate waste and spoilage of product



31625  
(31625 hopper available in Red or Blue)



### Gravity Hopper

Model No.	Description	Inches			Load Capacity			Ctn. Qty.
		L	W	H	lbs.	cu. in.	gal.	
 31620	Small Easy Flow Gravity Hopper	16	8 $\frac{1}{4}$	16	50	1400	6	1
31625	Large Easy Flow Gravity Hopper	18	10 $\frac{3}{4}$	19 $\frac{1}{2}$	75	2400	10.39	1

When ordering 31625 specify color Red or Blue. † Sliding divider shelf with 31620 hopper only.

Model No.	Description	Wt. Cap.
31625RACK	Easy Flow Gravity Hopper Rack 36" x 36" x 69"	900 lbs.
30600DOLLY	Easy Flow Gravity Hopper Dolly with 4" x 1.5" Polyolefin Casters	900 lbs.
30600BRACKET	Easy Flow Gravity Hopper Bracket	75 lbs.



- 30600BRACKET**
- Bracket available to attach either size hopper to existing louvered panel


### 31625RACK Gravity Hopper Floor Rack

- Holds 9 large/12 small Easy Flow Gravity Hoppers per side for maximum efficiency
- 13-gauge steel
- 900 lb. load capacity
- Adjustable rail heights
- Can be mobilized with optional dolly


31625RACK  
Shown with 31620 Easy Flow Gravity Hopper Bins

31625RACK  
Shown with 31625 Easy Flow Gravity Hopper Bins

## features



Large, angled top opening for easy filling



Generous picking area provides easy access to loaded product

- 30600DOLLY**
- Rack can be mobilized with optional dolly
  - Four swivel casters (two with brakes)



30600DOLLY