

MINI-BAT/12DC/1.6AH


Order No.: 2866572



<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=2866572>

Rechargeable battery module, lead AGM, VRLA technology, 12 V DC, 1.6 Ah.

Commercial data

EAN	 4 046356 476492
Pack	1
Country of Origin	CN
Catalog page information	Page 623 (IF-2011)

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Input data

Nominal input voltage	12 V DC
-----------------------	---------

Output data

Nominal output voltage	12 V DC
Output current	max. 10 A
Connection in series	No
Output fuse	10 A

General data

IQ technology	No
---------------	----

Disposal	Used batteries must not be thrown away with household waste, they should instead be disposed of in accordance with applicable national regulations. They can also be returned to Phoenix Contact or the manufacturer.
Width	67.5 mm
Height	99 mm
Depth	107 mm
Net weight	0.9 kg
Degree of protection	IP20
Protection class	III
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C

Certificates

Certifications applied for: UL-EX LIS

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;