


Item no.: 773-173
 Product description: Push-wire connector for junction boxes 3-conductor terminal blocks cover in red



Produkt kann von Bild abweichen / product may differ

Packing unit 500 10*50 pieces

RoHS compliant

Product group	7 (Push Wire Conn.)
pole count	3
Cross section [mm ²]	2.5 - 6 mm ²
Cross section [AWG]	14 - 10 AWG
Connection method	PUSH WIRE®
Measured voltage EN	400 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	41 A
Weight	5.73 g
Color	transparent
Wiring type	Side-entry
No. of connection Points	3
No. of potentials	1
Height	14.2 mm
Height	0.559 in
Width	25.6 mm
Width	1.008 in
Depth	20.1 mm

Depth	0.791 in
Strip length from	12 mm
Strip length to	13 mm
Strip length	0.49 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
773-173	CSA	154112-1059435	600	30	14-10
773-173	ENEC15	DK137981-01	400	41	2,5-4
773-173	ENEC15	DK140612-01	400	41	2,5-6
773-173	PSE	JET0695-43040-1001	600	30	14-10sol/str
773-173	RosTest	AB24 B04007			
773-173	UL listed	E69654	600	20	14-10sol/str

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected