


# DURACELL® Popular Alkaline Batteries



## MN1300

Size: D  
 Chemistry: Alkaline  
 Nominal Voltage: 1.5  
 Max. Diameter: 1.346"  
 Max. Height: 2.421"  
 Capacity (mAh): 15,000  
 Primary Usage: Flashlights,  
 Radios, Recorders, Toys



MN1300B2



MN1300B4



MN1300V8



## MN1400

Size: C  
 Chemistry: Alkaline  
 Nominal Voltage: 1.5  
 Max. Diameter: 1.031"  
 Max. Height: 1.969"  
 Capacity (mAh): 7,800  
 Primary Usage: Flashlights,  
 Radios, Recorders, Toys



MN1400B2



MN1400B4



MN1400V8



## MN1500

Size: AA  
 Chemistry: Alkaline  
 Nominal Voltage: 1.5  
 Max. Diameter: .571"  
 Max. Height: 1.988"  
 Capacity (mAh): 2,850  
 Primary Usage: Flashlights,  
 Radios, Recorders, Toys,  
 Calculators, Pagers,  
 CD Players, Electronic Games



MN1500B2



MN1500B4




MN1500B8



MN1500B12



MN1500V12



## MN1604

Size: 9V  
 Chemistry: Alkaline  
 Nominal Voltage: 9.0  
 Max. Length: .689"  
 Max. Width: 1.043"  
 Max. Height: 1.909"  
 Capacity (mAh): 580  
 Primary Usage: Radios, Toys,  
 Calculators, Smoke Alarms



MN1604B



MN1604B2



MN1604V4



## MN2400


Size: AAA  
 Chemistry: Alkaline  
 Nominal Voltage: 1.5  
 Max. Diameter: .413"  
 Max. Height: 1.752"  
 Capacity (mAh): 1,150  
 Primary Usage: Flashlights,  
 Calculators, Pagers,  
 Remote Controls



MN2400B2



MN2400B4



MN2400B8



MN2400V12

(Batteries are shown approximately actual size).